



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UBIZ0260 2P 60A Type RC3860 Replacement Breaker

Connecticut Electric

Catalog Number	UBIZ0260
Manufacturer	Connecticut Electric
Description	Zinsco Circuit Breaker By Connecticut Electric Type Ubiz. For Use In Zinsco Load Centers That Accept Type RC Circuit Breakers. Etl Listed. 10, 000 Aic 2-Pole 60a
Weight per unit	0.4000 (lbs/each)
Product Category	2 Pole Standard Trip Plug-In

Features

actuator	Handle
amperage rating	60
connection	Push On
interrupt rating	10000
Load Rating	1
Material	DMC
Phase	1
Poles	2
trip range	None
Trip Type	Thermal
Voltage Rating	120/240

Dimensions and Weight

Height	2.53
Length	5.63
Width	0.75

Descriptions

Description	2P 60A TYPE RC3860 REPLACEMENT BREAKER
extra long description	CON UBIZ0260 ZINSCO REPLACEMENT 2P
Long Description	Zinsco circuit breaker by Connecticut Electric Type UBIZ. For use in Zinsco load centers that accept type RC circuit breakers. ETL Listed. 10,000 AIC 2-pole 60A
Product Type	Zinsco Replacement 2P 60A Thin CB
Short Description	UBI Z TYPE Q THIN 2P 60A
Special Features	The only newly manufactured and Listed replacements available

Manufacturer Information

Brand	Connecticut Electric
GTIN	00094925030372
Manufacturers Part Number	UBIZ0260
UPC	094925030372



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	UBIZ TYPE RC THIN REPLACEMENT

Packaging

Carton	6
Package	24
Weight Per each	0.4

Uses, Certifications, and Standards

Application	Plug-In for use in Zinsco Load Centers
Enclosure	Appropriate OEM Panelboard i.e. Zinsco
environmental conditions	Determined by panel for product
Frequency Rating	50/60
Operating Temperature	40
standard	ETL Listed