



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## UCES24INSWW690CR 24" 11W Led Undercab 27K/3K/35K Select 620LM *Lithonia Lighting - Acuity*

Catalog Number	UCES24INSWW690CR
Manufacturer	Lithonia Lighting - Acuity
Description	Lith Uces 24IN SWW6 90CRI WH M6 Eco
Weight per unit	1.5 (lbs/each)
Product Category	Lighting

### Features

average life	50,000
dimensions	24 x 2.55 x 1.07
dimnable	Yes
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Static
Material	Steel
Maximum Operating Temperature	25
Number of Lamps	1
Power Source	Hardwired
Shape	Rectangular
Voltage Rating	120
Warranty	5
Wattage	10.6

### Material, Color, and Finish

Color	White
color rendering index (cri)	90
color temperature	2700 ,3000 ,3500 ,Variable
Finish	Gloss
Lens Color	WHITE
Lens Material	Acrylic
Style	CONTEMPORARY

### Dimensions and Weight

Height	1.07
Length	24
Width	2.55

### Descriptions

Description	24" 11W LED UNDERCAB 27K/3K/35K SELECT 620LM
Features	Contractor Select
Long Description	LITH UCES 24IN SWW6 90CRI WH M6 Eco
Product Type	Undercabinet



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	JUNO
GTIN	00196182177422
Manufacturers Part Number	UCES 24IN SWW6 90CRI WH M6
UPC	196182177422

## Taxonomies, Classifications, and Categories

Category Description	LED TRACK, RAIL, TASK & UNDERCABINET LIGHTING
Type	Undercabinet

## Availability

Manufacturer Status	Inactive
---------------------	----------

## Packaging

Carton	1
Package	6
Weight	1.5
Weight Per each	1.5

## Uses, Certifications, and Standards

Application	Hospitality,Residential,Retail
environmental conditions	Indoor
Mounting	SURFACE
standard	cULCA Title 24,ENERGY STAR,JA8