



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## UNF125NR 1-1/4" Female Union

*Appleton/Oz Gedney*

Catalog Number	UNF125NR
Manufacturer	Appleton/Oz Gedney
Description	Appleton UNF125NR Unilets Unf Union, Trade Size: 1-1/4 In, Outside Diameter: 2.81 In, Length: 2.19 In, Flexibility: Rigid and Imc, Material: Malleable Iron, Connection: Female Threaded, Finish: Triple-Coat (Zinc Electroplate, Chromate and Epoxy Powder Coa
Weight per unit	133.0 (lbs/each)
Product Category	Boxes & Covers

### Features

connection	Female Threaded
outside diameter	2.81

### Dimensions and Weight

Length	2.19
--------	------

### Descriptions

Description	1-1/4" FEMALE UNION
extra long description	APP UNF125NR 1-1/4 UNION CONN TYPE
Long Description	Appleton UNF125NR UNILETS UNF Union, Trade Size: 1-1/4 IN, Outside Diameter: 2.81 IN, Length: 2.19 IN, Flexibility: Rigid And IMC, Material: Malleable Iron, Connection: Female Threaded, Finish: Triple-Coat (Zinc Electroplate, Chromate And Epoxy Powder Coa
Product Type	1-1/4 Union Conn Type Unf
Special Features	Accurately tapped, tapered threads for tight, rigid joints and ground continuity;Concentric ring interlocked design sizes makes possible smaller diameter, allowing use in tighter spaces;Explosionproof, dust-ignitionproof;Smooth, rounded integral bushing in each hub protects conductor insulation;UNF unions are used for joining conduit and connecting conduit to enclosures, Facilitates modifications, permits removal of enclosures without turning or removal of conduit

### Manufacturer Information

Brand	Appleton
GTIN	00781381257640
Manufacturers Part Number	UNF125NR
UPC	781381257640



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... HAZARDOUS LOCATION FITTINGS  
Type ..... UNF Union

## Trade Size

Trade Size ..... 1-1/4

## Packaging

Carton ..... 5  
Package ..... 25  
Weight Per each ..... 133

## Uses, Certifications, and Standards

Application ..... For Connecting Conduit To Conduit  
standard ..... and Class II, CSA C22.2 No. 25, C22.2 No. 30, CSA 065181  
Certified;Class II, Groups E, F, G;UL 886 (1203), UL File Number  
E10444, UL Listed for Class I, Groups B, C, d