



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UNF605G Ocal 2" PVC CTD Female Union HZD Loc

Abb Installation Products, Inc

Catalog Number	UNF605G
Manufacturer	Abb Installation Products, Inc
Description	PVC Coated Explosion and Dust-Ignition Proof Unf Female Union, Pipe Size 2 Inch/53 Metric, 3 Piece, For Hazardous and Non-Hazardous Locations, Overall Length 2.50 Inch/63.50 Millimeters, Overall Diameter 3.81 Inch/96.77 Millimeters, Electrogalvanized Steel, Gray
Weight per unit	4.3 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

outside diameter	3.81
------------------	------

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Length	2.5
--------	-----

Descriptions

Description	OCAL 2" PVC CTD FEMALE UNION HZD LOC
extra long description	ABB UNF605-G PVC CTD UNF FEM UNION
Long Description	PVC Coated Explosion and Dust-Ignition Proof UNF Female Union, Pipe Size 2 Inch/53 Metric, 3 Piece, for Hazardous and Non-hazardous Locations, Overall Length 2.50 Inch/63.50 Millimeters, Overall Diameter 3.81 Inch/96.77 Millimeters, Electrogalvanized Steel, Gray
Product Type	PVC CTD Unf Fem Union 2IN Gray
Special Features	Compact Design Which Permits Assembly with a Minimum of Clearance to Other Adjacent Conduit and/or Equipment

Manufacturer Information

Brand	OCAL
GTIN	00704508413262
Manufacturers Part Number	UNF605G
UPC	704508413262

Taxonomies, Classifications, and Categories

Category Description	ALL PLASTIBOND FITTINGS
Type	Female Union

Trade Size

Trade Size	2 in
------------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	6
Weight Per each	4.32

Uses, Certifications, and Standards

Application	To Connect Conduit to Conduit, or to Provide a Means for Future Modification of the Conduit System
standard	UL 1203, CSA