

Eaton URTRS101BE

Catalog Number: URTRS101BE

Eaton meter socket, 3 5/16 in hub opening, 125A, Overhead, Hub opening, #8-2/0 kcmil, Four-jaw, Single-phase, #8-2/0 kcmil, Sockets:1, Three-wire, Ring, 600V



General specifications

Product Name

Eaton meter socket

Catalog Number

URTRS101BE

UPC

786685217826

Product Length/Depth

3.63 in

Product Height

11 in

Product Width

8.25 in

Product Weight

7 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Product specifications

Type

3 5/16 in hub opening

Amperage Rating

125A

Feed type

Overhead

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

TN : Knoxville Utility Board (KUB)

Line

#8-2/0 kcmil

Load

#8-2/0 kcmil

Number of wires

Three-wire

Hub type

Hub opening

Security

Ring

Voltage rating

600 V

Number of sockets

1

Resources

Catalogs

Residential and Light Commercial, Metering Products, Volume 1 Tab 4

Specifications and datasheets

Eaton Specification Sheet - URTRS101BE



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton URTRS101BE

Catalog Number: URTRS101BE

Eaton meter socket, 3 5/16 in hub opening, 125A, Overhead, Hub opening, #8-2/0 kcmil, Four-jaw, Single-phase, #8-2/0 kcmil, Sockets:1, Three-wire, Ring, 600V



General specifications

Product Name

Eaton meter socket

Catalog Number

URTRS101BE

UPC

786685217826

Product Length/Depth

3.63 in

Product Height

11 in

Product Width

8.25 in

Product Weight

7 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Product specifications

Type

3 5/16 in hub opening

Amperage Rating

125A

Feed type

Overhead

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

TN : Knoxville Utility Board (KUB)

Line

#8-2/0 kcmil

Load

#8-2/0 kcmil

Number of wires

Three-wire

Hub type

Hub opening

Security

Ring

Voltage rating

600 V

Number of sockets

1

Resources

Catalogs

Residential and Light Commercial, Metering Products, Volume 1 Tab 4

Specifications and datasheets

Eaton Specification Sheet - URTRS101BE



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)