



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



USB20X2BK Recep, Dup, 20A 125V, 3.8A 5V Usb Port, BK *Hubbell Wiring Devices*

Catalog Number	USB20X2BK
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Receptacles, Duplex, Dual Usb Type 2.0 Ports 3.8 Amp, 5 Volt DC, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Black
Weight per unit	0.3000 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20.000000000000000
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	3-Wire
Phase	1
Poles	2-Pole
Voltage Rating	125
Wattage	2,500
Wire Size	#14 to #10

Dimensions and Weight

Size	4.12 in x 1.75 in x 1.96 in
------	-----------------------------

Descriptions

Description	RECEP, DUP, 20A 125V,3.8A 5V USB PORT,BK
extra long description	HWDK USB20X2BK RECEP, DUP, 20A 125V
Long Description	Straight Blade Devices, Receptacles, Duplex, Dual USB Type 2.0 ports 3.8 Amp, 5 Volt DC, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Black
Product Type	Recep, Dup, 20A 125V, 3.8A 5V Usb Port, BK
Special Features	Dual USB Charger, Tamper Resistant

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00883778304866
Manufacturers Part Number	USB20X2BK
UPC	883778304866

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Duplex Receptacle

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.3

Uses, Certifications, and Standards

Application	USB Charger Hospital Grade
environmental conditions	Indoor Dry unless protected by additional means
nema rating	5-20R
standard	cULus Listed To UL498