

# Eaton USTS131L143CH

Catalog Number: USTS131L143CH

Eaton meter socket, Instrument rated socket, 20A, Over/under, 1.25 inch hub mounted, 13-jaw, Factory wired test switch, 600 Vac, 1-socket



## General specifications

### Product Name

Eaton meter socket

### Catalog Number

USTS131L143CH

### UPC

782116199976

### Product Length/Depth

4.35 in

### Product Height

20 in

### Product Width

12 in

### Product Weight

18 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## Product specifications

### Type

Instrument rated socket

### Amperage Rating

20A

### Feed type

Top/bottom

### Number of jaws

13-jaw

### Phase

Three-phase

### Utility approvals

TN : Middle Tennessee EMC

### Enclosure material

16 GA GALV STEEL

### Number of wires

Four-wire

### Hub type

1-1/4 in bolt-on hub

### Security

Ringless

### Voltage rating

600 V

### Accessories

Factory wired test switch

### Number of sockets

1

## Resources

### Catalogs

Residential and Light Commercial, Metering Products, Volume 1 Tab 4

### Specifications and datasheets

Eaton Specification Sheet - USTS131L143CH



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton USTS131L143CH

Catalog Number: USTS131L143CH

Eaton meter socket, Instrument rated socket, 20A, Over/under, 1.25 inch hub mounted, 13-jaw, Factory wired test switch, 600 Vac, 1-socket



## General specifications

### Product Name

Eaton meter socket

### Catalog Number

USTS131L143CH

### UPC

782116199976

### Product Length/Depth

4.35 in

### Product Height

20 in

### Product Width

12 in

### Product Weight

18 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## Product specifications

### Type

Instrument rated socket

### Amperage Rating

20A

### Feed type

Top/bottom

### Number of jaws

13-jaw

### Phase

Three-phase

### Utility approvals

TN : Middle Tennessee EMC

### Enclosure material

16 GA GALV STEEL

### Number of wires

Four-wire

### Hub type

1-1/4 in bolt-on hub

### Security

Ringless

### Voltage rating

600 V

### Accessories

Factory wired test switch

### Number of sockets

1

## Resources

### Catalogs

Residential and Light Commercial, Metering Products, Volume 1 Tab 4

### Specifications and datasheets

Eaton Specification Sheet - USTS131L143CH



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)