



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## USB15X2I Recep, Dup, 15A 125V, 3.8A 5V Usb Port, Iv *Hubbell Wiring Devices*

Catalog Number	USB15X2I
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Receptacles, Duplex, Dual Usb Type 2.0 Ports 3.8 Amp, 5 Volt DC, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Ivory
Weight per unit	0.3000 (lbs/each)
Product Category	Wiring Devices

### Features

amperage rating	15.000000000000000
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	3-Wire
Phase	1
Poles	2-Pole
Voltage Rating	125
Wattage	1,875
Wire Size	#14 to #10

### Dimensions and Weight

Size	4.12 in x 1.75 in x 1.96 in
------	-----------------------------

### Descriptions

Description	RECEP, DUP, 15A 125V,3.8A 5V USB PORT,IV
extra long description	HWDK USB15X2I RECEP, DUP, 15A 125V,
Long Description	Straight Blade Devices, Receptacles, Duplex, Dual USB Type 2.0 ports 3.8 Amp, 5 Volt DC, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Ivory
Product Type	Recep, Dup, 15A 125V, 3.8A 5V Usb Port, Iv
Special Features	Dual USB Charger, Tamper Resistant

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00883778304583
Manufacturers Part Number	USB15X2I
UPC	883778304583

### Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Two Type 2.0 Ports

### Availability

Status	Inactive
--------	----------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.3

## Uses, Certifications, and Standards

Application	USB Charger Hospital Grade
environmental conditions	Indoor Dry unless protected by additional means
nema rating	5-15R
standard	cULus Listed To UL498