

# Specifications

## Eaton UTE7213TCH

Eaton meter socket, Comm, 200A, Over/under, 5x5 inch hub open, #6-350 kcmil, 7-jaw, 3-ph, #6-350 kcmil, Lever bypass, Gnd con (#14-#2 Cu), Triplex, Four-wire, Ringless, 600 Vac

### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UTE7213TCH
<b>UPC</b>	786685351261
<b>PRODUCT LENGTH/DEPTH</b>	4.94 in
<b>PRODUCT HEIGHT</b>	19 in
<b>PRODUCT WIDTH</b>	13 in
<b>PRODUCT WEIGHT</b>	25 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed

## Product specifications

<b>TYPE</b>	Commercial
<b>AMPERAGE RATING</b>	200A
<b>FEED TYPE</b>	Top/bottom
<b>NUMBER OF JAWS</b>	Seven-jaw
<b>PHASE</b>	Three-phase
<b>UTILITY APPROVALS</b>	NY : Central Hudson Gas & Electric (CHG&E) ME : Central Maine Power OH : Dayton Power and Light (DP&L) MD : First Energy (Potomac Edison) VA : First Energy (Potomac Edison) WV : First Energy (Mon Power) NJ : First Energy (Jersey Central Power and Light) OH : First Energy (Ohio Edison, Toledo Edison, The Illuminating Company) PA : First Energy (Allegheny Power, MET ED, Penelec, West Penn Power) WI : WE Energies / Wisconsin Public Service (WPS) SC : South Carolina Electric and Gas (SCE&G) TX : Entergy NM : Texas-New Mexico Power (TNMP) TX : Texas-New Mexico Power (TNMP)
<b>LINE</b>	#6-350 kcmil
<b>LOAD</b>	#6-350 kcmil
<b>NUMBER OF WIRES</b>	Four-wire
<b>HUB TYPE</b>	5 x 5 hub opening
<b>SECURITY</b>	Ringless
<b>VOLTAGE RATING</b>	600 V
<b>BYPASS</b>	Lever
<b>NUMBER OF SOCKETS</b>	1

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - UTE7213TCH</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton UTE7213TCH

Eaton meter socket, Comm, 200A, Over/under, 5x5 inch hub open, #6-350 kcmil, 7-jaw, 3-ph, #6-350 kcmil, Lever bypass, Gnd con (#14-#2 Cu), Triplex, Four-wire, Ringless, 600 Vac

### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UTE7213TCH
<b>UPC</b>	786685351261
<b>PRODUCT LENGTH/DEPTH</b>	4.94 in
<b>PRODUCT HEIGHT</b>	19 in
<b>PRODUCT WIDTH</b>	13 in
<b>PRODUCT WEIGHT</b>	25 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed

## Product specifications

<b>TYPE</b>	Commercial
<b>AMPERAGE RATING</b>	200A
<b>FEED TYPE</b>	Top/bottom
<b>NUMBER OF JAWS</b>	Seven-jaw
<b>PHASE</b>	Three-phase
<b>UTILITY APPROVALS</b>	NY : Central Hudson Gas & Electric (CHG&E) ME : Central Maine Power OH : Dayton Power and Light (DP&L) MD : First Energy (Potomac Edison) VA : First Energy (Potomac Edison) WV : First Energy (Mon Power) NJ : First Energy (Jersey Central Power and Light) OH : First Energy (Ohio Edison, Toledo Edison, The Illuminating Company) PA : First Energy (Allegheny Power, MET ED, Penelec, West Penn Power) WI : WE Energies / Wisconsin Public Service (WPS) SC : South Carolina Electric and Gas (SCE&G) TX : Entergy NM : Texas-New Mexico Power (TNMP) TX : Texas-New Mexico Power (TNMP)
<b>LINE</b>	#6-350 kcmil
<b>LOAD</b>	#6-350 kcmil
<b>NUMBER OF WIRES</b>	Four-wire
<b>HUB TYPE</b>	5 x 5 hub opening
<b>SECURITY</b>	Ringless
<b>VOLTAGE RATING</b>	600 V
<b>BYPASS</b>	Lever
<b>NUMBER OF SOCKETS</b>	1

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - UTE7213TCH</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

