

Specifications



Eaton UTRS101BE

Eaton meter socket, 1-pos resi service, 125 A, Over, 3-5/16 inch hub open, #8-2/0 AWG, 4-jaw, 1-phase, #8-2/0 AWG, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton meter socket |
| CATALOG NUMBER | UTRS101BE |
| UPC | 786685217710 |
| PRODUCT LENGTH/DEPTH | 3.61 in |
| PRODUCT HEIGHT | 11.05 in |
| PRODUCT WIDTH | 8.22 in |
| PRODUCT WEIGHT | 6.46 lb |
| WARRANTY | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| CERTIFICATIONS | UL Listed |



Powering Business Worldwide

Product specifications

| | |
|--------------------------|---|
| TYPE | Single-position residential service |
| AMPERAGE RATING | 125A |
| FEED TYPE | Overhead |
| NUMBER OF JAWS | Four-jaw |
| PHASE | Single-phase |
| UTILITY APPROVALS | ME : Central Maine Power NM : El Paso Electric TX : El Paso Electric AL : Alabama Power ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company) MO : Empire District Electric OK : Empire District Electric AR : Entergy LA : Entergy MS : Entergy TX : Entergy AL : Huntsville Utilities FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) TX : Pedernales Electric |

Resources

| | |
|--------------------------------------|---|
| CATALOGS | Residential and Light Commercial, Metering Products, Volume 1 Tab 4 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - UTRS101BE |

| | |
|-------------------|---|
| | Cooperative NM : Public Service Company of New Mexico (PNM) SC : South Carolina Electric and Gas (SCE&G) |
| LINE | #8-2/0 AWG |
| LOAD | #8-2/0 AWG |
| NUMBER OF WIRES | Three-wire |
| HUB TYPE | 3-5/16 in hub opening |
| CONNECTION | Ground connection |
| SECURITY | Ringless |
| VOLTAGE RATING | 600 V |
| NUMBER OF SOCKETS | 1 |

| |
|-----------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| DATE: |



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

