

# Eaton UTRS101CE

Catalog Number: UTRS101CE

Eaton meter socket, 1-pos resi service, 125A, Over, 3-5/16 inch hub cover plate, #8-2/0 AWG, 4-jaw, 1-phase, #8-2/0 AWG, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac



## General specifications

### Product Name

Eaton meter socket

### Catalog Number

UTRS101CE

### UPC

786685217727

### Product Length/Depth

3.61 in

### Product Height

11.05 in

### Product Width

8.22 in

### Product Weight

7 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## Product specifications

### Type

Single-position residential service

### Amperage Rating

125A

### Feed type

Overhead

### Number of jaws

Four-jaw

### Phase

Single-phase

### Utility approvals

ME : Central Maine Power

ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company)

MO : Empire District Electric

OK : Empire District Electric

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NM : Public Service Company of New Mexico (PNM)

SC : South Carolina Electric and Gas (SCE&G)

### Line

#8-2/0 AWG

### Load

#8-2/0 AWG

### Number of wires

Three-wire

### Hub type

3-5/16 in hub cover plate

### Security

Ringless

## Resources

### Catalogs

[Residential and Light Commercial, Metering Products, Volume 1 Tab 4](#)

### Specifications and datasheets

[Eaton Specification Sheet - UTRS101CE](#)

Voltage rating

600 V

Number of sockets

1



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton UTRS101CE

Catalog Number: UTRS101CE

Eaton meter socket, 1-pos resi service, 125A, Over, 3-5/16 inch hub cover plate, #8-2/0 AWG, 4-jaw, 1-phase, #8-2/0 AWG, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac



## General specifications

### Product Name

Eaton meter socket

### Catalog Number

UTRS101CE

### UPC

786685217727

### Product Length/Depth

3.61 in

### Product Height

11.05 in

### Product Width

8.22 in

### Product Weight

7 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## Product specifications

### Type

Single-position residential service

### Amperage Rating

125A

### Feed type

Overhead

### Number of jaws

Four-jaw

### Phase

Single-phase

### Utility approvals

ME : Central Maine Power

ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company)

MO : Empire District Electric

OK : Empire District Electric

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NM : Public Service Company of New Mexico (PNM)

SC : South Carolina Electric and Gas (SCE&G)

### Line

#8-2/0 AWG

### Load

#8-2/0 AWG

### Number of wires

Three-wire

### Hub type

3-5/16 in hub cover plate

### Security

Ringless

## Resources

### Catalogs

[Residential and Light Commercial, Metering Products, Volume 1 Tab 4](#)

### Specifications and datasheets

[Eaton Specification Sheet - UTRS101CE](#)

Voltage rating

600 V

Number of sockets

1



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)