

# Specifications

## Eaton UTRS233CCH

Eaton meter socket, 1-pos resi service, 200A, Over/under, 3-5/16 inch hub cover plate, #8-350 kcmil, 4-jaw, 1-ph, #8-350 kcmil, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac



### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UTRS233CCH
<b>UPC</b>	782116124039
<b>PRODUCT LENGTH/DEPTH</b>	4.94 in
<b>PRODUCT HEIGHT</b>	17.13 in
<b>PRODUCT WIDTH</b>	13 in
<b>PRODUCT WEIGHT</b>	18 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed

### Product specifications

<b>TYPE</b>	Single-position residential service
<b>AMPERAGE RATING</b>	200A
<b>FEED TYPE</b>	Top/bottom
<b>NUMBER OF JAWS</b>	Four-jaw
<b>PHASE</b>	Single-phase
<b>UTILITY APPROVALS</b>	MO : Empire District Electric OK : Empire District Electric AR : Entergy LA : Entergy MS : Entergy TX : Entergy GA : Georgia Power
<b>LINE</b>	#8-350 kcmil
<b>LOAD</b>	#8-350 kcmil
<b>NUMBER OF WIRES</b>	Three-wire
<b>HUB TYPE</b>	3-5/16 in hub cover plate

### Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - UTRS233CCH</a>

<b>SECURITY</b>	Ringless
<b>VOLTAGE RATING</b>	600 V
<b>NUMBER OF SOCKETS</b>	1

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton UTRS233CCH

Eaton meter socket, 1-pos resi service, 200A, Over/under, 3-5/16 inch hub cover plate, #8-350 kcmil, 4-jaw, 1-ph, #8-350 kcmil, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac



### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UTRS233CCH
<b>UPC</b>	782116124039
<b>PRODUCT LENGTH/DEPTH</b>	4.94 in
<b>PRODUCT HEIGHT</b>	17.13 in
<b>PRODUCT WIDTH</b>	13 in
<b>PRODUCT WEIGHT</b>	18 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed

### Product specifications

<b>TYPE</b>	Single-position residential service
<b>AMPERAGE RATING</b>	200A
<b>FEED TYPE</b>	Top/bottom
<b>NUMBER OF JAWS</b>	Four-jaw
<b>PHASE</b>	Single-phase
<b>UTILITY APPROVALS</b>	MO : Empire District Electric OK : Empire District Electric AR : Entergy LA : Entergy MS : Entergy TX : Entergy GA : Georgia Power
<b>LINE</b>	#8-350 kcmil
<b>LOAD</b>	#8-350 kcmil
<b>NUMBER OF WIRES</b>	Three-wire
<b>HUB TYPE</b>	3-5/16 in hub cover plate

### Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - UTRS233CCH</a>

<b>SECURITY</b>	Ringless
<b>VOLTAGE RATING</b>	600 V
<b>NUMBER OF SOCKETS</b>	1

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

