

Specifications



Eaton UTTE4213UCH

Eaton meter socket, 1-pos commercial or resi service, 200A, Over/under, 5x5 inch hub cover plate, #6-350 kcmil, 4-jaw, 1-ph, #6-350 kcmil, Lever bypass, Two grounding conns (#14-#2 Cu), Quadplex, 3-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UTTE4213UCH
UPC	786685351322
PRODUCT LENGTH/DEPTH	4.94 in
PRODUCT HEIGHT	19 in
PRODUCT WIDTH	13 in
PRODUCT WEIGHT	25 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed
CATALOG NOTES	Ameren, Union Electric, Central Illinois Public approved

Product specifications

TYPE	Single-position commercial or residential service
AMPERAGE RATING	200A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Four-jaw
PHASE	Single-phase
GROUND	Quadplex
LINE	#6-350 kcmil
LOAD	#6-350 kcmil
NUMBER OF WIRES	Three-wire
HUB TYPE	5 x 5 hub cover plate
SECURITY	Ringless
VOLTAGE RATING	600 V
BYPASS	Lever
NUMBER OF SOCKETS	1

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UTTE4213UCH

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

Specifications



Eaton UTTE4213UCH

Eaton meter socket, 1-pos commercial or resi service, 200A, Over/under, 5x5 inch hub cover plate, #6-350 kcmil, 4-jaw, 1-ph, #6-350 kcmil, Lever bypass, Two grounding conns (#14-#2 Cu), Quadplex, 3-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UTTE4213UCH
UPC	786685351322
PRODUCT LENGTH/DEPTH	4.94 in
PRODUCT HEIGHT	19 in
PRODUCT WIDTH	13 in
PRODUCT WEIGHT	25 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed
CATALOG NOTES	Ameren, Union Electric, Central Illinois Public approved

Product specifications

TYPE	Single-position commercial or residential service
AMPERAGE RATING	200A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Four-jaw
PHASE	Single-phase
GROUND	Quadplex
LINE	#6-350 kcmil
LOAD	#6-350 kcmil
NUMBER OF WIRES	Three-wire
HUB TYPE	5 x 5 hub cover plate
SECURITY	Ringless
VOLTAGE RATING	600 V
BYPASS	Lever
NUMBER OF SOCKETS	1

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UTTE4213UCH

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.