

Eaton UTTE7213TCH

Catalog Number: UTTE7213TCH

Eaton meter socket, 1-pos commercial or resi service, 200A, Over/under, 5x5 inch hub open, #6-350 kcmil, 7-jaw, three-ph, #6-350 kcmil, Lever bypass, Two grounding conns (#14-#2 Cu), Quadplex, 4-wire, Ringless, 600 Vac



Photo is representative

General specifications

Product Name

Eaton meter socket

Catalog Number

UTTE7213TCH

UPC

786685351346

Product Length/Depth

4.94 in

Product Height

19 in

Product Width

13 in

Product Weight

25 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Product specifications

Type

Single-position commercial or residential service

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Seven-jaw

Phase

Three-phase

Utility approvals

IL : Ameren

MO : Ameren

Line

#6-350 kcmil

Load

#6-350 kcmil

Number of wires

Four-wire

Hub type

5 x 5 hub opening

Security

Ringless

Voltage rating

600 V

Bypass

Lever

Number of sockets

1

Resources

Catalogs

[Residential and Light Commercial, Metering Products, Volume 1 Tab 4](#)

Specifications and datasheets

[Eaton Specification Sheet - UTTE7213TCH](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton UTTE7213TCH

Catalog Number: UTTE7213TCH

Eaton meter socket, 1-pos commercial or resi service, 200A, Over/under, 5x5 inch hub open, #6-350 kcmil, 7-jaw, three-ph, #6-350 kcmil, Lever bypass, Two grounding conns (#14-#2 Cu), Quadplex, 4-wire, Ringless, 600 Vac



Photo is representative

General specifications

Product Name

Eaton meter socket

Catalog Number

UTTE7213TCH

UPC

786685351346

Product Length/Depth

4.94 in

Product Height

19 in

Product Width

13 in

Product Weight

25 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Product specifications

Type

Single-position commercial or residential service

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Seven-jaw

Phase

Three-phase

Utility approvals

IL : Ameren

MO : Ameren

Line

#6-350 kcmil

Load

#6-350 kcmil

Number of wires

Four-wire

Hub type

5 x 5 hub opening

Security

Ringless

Voltage rating

600 V

Bypass

Lever

Number of sockets

1

Resources

Catalogs

[Residential and Light Commercial, Metering Products, Volume 1 Tab 4](#)

Specifications and datasheets

[Eaton Specification Sheet - UTTE7213TCH](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)