

# Eaton V48M28T1516

Catalog Number: V48M28T1516

DOE 2016 Efficient Transformer, Three-phase, PV: 480V, Taps: 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 208Y/120V, 150°C, 15 kVA, Al windings



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose ventilated transformer	V48M28T1516
	UPC
	786680147517
<b>Product Length/Depth</b>	<b>Product Height</b>
17.75 in	28 in
<b>Product Width</b>	<b>Product Weight</b>
21.88 in	228 lb
<b>Warranty</b>	<b>Compliances</b>
Eaton Selling Policy 25-000, one (1) year DOE2016 Efficient from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	
	<b>Certifications</b>
	UL Listed
	<b>Catalog Notes</b>
	10 CFR Part 431 (2016) Efficient

## Physical Attributes

### Coil material

Aluminum

### Enclosure

NEMA 2

### Frame

939

### Insulation

220 °C

### Tap size

2 at +2.5% FCAN; 4 at -2.5% FCBN

### Wiring connection

280B

## Performance Ratings

### Efficiency

10 CFR Part 431-2016 (DOE 2016)

### Frequency rating

60 Hz

### Kva Rating

15 kVA

### Primary voltage

480 V

### Secondary Voltage

208Y/120 V

### Sound Level

45 dB

### Temperature rise

150 °C rise

### Volt ampere rating

15 kVA

## Miscellaneous

### Weathershield

WS57

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - V48M28T1516](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton V48M28T1516

Catalog Number: V48M28T1516

DOE 2016 Efficient Transformer, Three-phase, PV: 480V, Taps: 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 208Y/120V, 150°C, 15 kVA, Al windings



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose ventilated transformer	V48M28T1516
	UPC
	786680147517
<b>Product Length/Depth</b>	<b>Product Height</b>
17.75 in	28 in
<b>Product Width</b>	<b>Product Weight</b>
21.88 in	228 lb
<b>Warranty</b>	<b>Compliances</b>
Eaton Selling Policy 25-000, one (1) year DOE2016 Efficient from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	<b>Certifications</b>
	UL Listed
	<b>Catalog Notes</b>
	10 CFR Part 431 (2016) Efficient

## Physical Attributes

### Coil material

Aluminum

### Enclosure

NEMA 2

### Frame

939

### Insulation

220 °C

### Tap size

2 at +2.5% FCAN; 4 at -2.5% FCBN

### Wiring connection

280B

## Performance Ratings

### Efficiency

10 CFR Part 431-2016 (DOE 2016)

### Frequency rating

60 Hz

### Kva Rating

15 kVA

### Primary voltage

480 V

### Secondary Voltage

208Y/120 V

### Sound Level

45 dB

### Temperature rise

150 °C rise

### Volt ampere rating

15 kVA

## Miscellaneous

### Weathershield

WS57

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - V48M28T1516](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)