

Specifications

Photo is representative



Eaton V48M28T7516CU

Eaton General purpose ventilated transformer, Fungus proof, CU windings, DOE 2016, NEMA 2, FR942, 220°C, 75 kVA, Floor/wall mnt upright only, 3-phase, PV: 480V delta, SV: 208Y/120, NEMA ST-20, 2 at +2.5%, 4 at -2.5%, 150°C, 75 kVA

Physical Attributes

COIL MATERIAL	Copper
ENCLOSURE	NEMA
FRAME	FR942
INSULATION	220 °C
MATERIAL	Copper winding
MOUNTING	Floor or wall, upright only
TAP SIZE	2 at +2.5%, 4 at -2.5%
TYPE	Energy-efficient ventilated dry-type transformer
WIRING CONNECTION	280B

General specifications

PRODUCT NAME	Eaton General purpose ventilated transformer
CATALOG NUMBER	V48M28T7516CU
UPC	786680192012
PRODUCT LENGTH/DEPTH	24 in
PRODUCT HEIGHT	43 in
PRODUCT WIDTH	30.5 in
PRODUCT WEIGHT	632 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	DOE2016 Efficient
CERTIFICATIONS	UL Listed
CATALOG NOTES	10 CFR Part 431 (2016) Efficient

Specifications

Photo is representative



Eaton V48M28T7516CU

Eaton General purpose ventilated transformer, Fungus proof, CU windings, DOE 2016, NEMA 2, FR942, 220°C, 75 kVA, Floor/wall mnt upright only, 3-phase, PV: 480V delta, SV: 208Y/120, NEMA ST-20, 2 at +2.5%, 4 at -2.5%, 150°C, 75 kVA

Physical Attributes

COIL MATERIAL	Copper
ENCLOSURE	NEMA
FRAME	FR942
INSULATION	220 °C
MATERIAL	Copper winding
MOUNTING	Floor or wall, upright only
TAP SIZE	2 at +2.5%, 4 at -2.5%
TYPE	Energy-efficient ventilated dry-type transformer
WIRING CONNECTION	280B

General specifications

PRODUCT NAME	Eaton General purpose ventilated transformer
CATALOG NUMBER	V48M28T7516CU
UPC	786680192012
PRODUCT LENGTH/DEPTH	24 in
PRODUCT HEIGHT	43 in
PRODUCT WIDTH	30.5 in
PRODUCT WEIGHT	632 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	DOE2016 Efficient
CERTIFICATIONS	UL Listed
CATALOG NOTES	10 CFR Part 431 (2016) Efficient