

Specifications



Photo is representative

Eaton V65B-AC

Eaton Crouse-Hinds series V-Spring telescoping light pole, Aluminum, Base mount, Installed cover for locking collar

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series V-Spring telescoping light pole
CATALOG NUMBER	V65B-AC
UPC	662276522558
PRODUCT LENGTH/DEPTH	73.5 in
PRODUCT HEIGHT	6.57 in
PRODUCT WIDTH	6.57 in
PRODUCT WEIGHT	34 lb



Certifications and compliances

AREA CLASSIFICATION Ordinary/Non-Hazardous

Product specifications

MOUNTING STYLE Base

	Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4
INGRESS PROTECTION (IP) RATINGS	IP66

MATERIAL	Aluminum
SPECIAL FEATURES	Installed cover for locking collar

Resources

3D CAD DRAWING PACKAGE	Eaton Crouse-Hinds V65B-AC 3D drawing
3D MODELS	SP3D Design Package - V-Spring Telescoping Safety Light Pole
BROCHURES	Crouse-Hinds series V-Spring Telescoping Safety Light Pole brochure
CATALOGS	Crouse-Hinds series V-Spring Telescoping Safety Light Pole catalog page
CERTIFICATION REPORTS	V-Spring Telescoping Safety Light Pole Canadian certification
INSTALLATION INSTRUCTIONS	IF 1762 - V-Spring Telescoping Safety Light Pole
SPECIFICATIONS AND DATASHEETS	V-Spring Telescoping Safety Light Pole Eaton Specification Sheet - V65B-AC

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative

Eaton V65B-AC

Eaton Crouse-Hinds series V-Spring telescoping light pole, Aluminum, Base mount, Installed cover for locking collar

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series V-Spring telescoping light pole
CATALOG NUMBER	V65B-AC
UPC	662276522558
PRODUCT LENGTH/DEPTH	73.5 in
PRODUCT HEIGHT	6.57 in
PRODUCT WIDTH	6.57 in
PRODUCT WEIGHT	34 lb



Certifications and compliances

AREA CLASSIFICATION Ordinary/Non-Hazardous

Product specifications

MOUNTING STYLE Base

	Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4
INGRESS PROTECTION (IP) RATINGS	IP66

MATERIAL	Aluminum
SPECIAL FEATURES	Installed cover for locking collar

Resources

3D CAD DRAWING PACKAGE	Eaton Crouse-Hinds V65B-AC 3D drawing
3D MODELS	SP3D Design Package - V-Spring Telescoping Safety Light Pole
BROCHURES	Crouse-Hinds series V-Spring Telescoping Safety Light Pole brochure
CATALOGS	Crouse-Hinds series V-Spring Telescoping Safety Light Pole catalog page
CERTIFICATION REPORTS	V-Spring Telescoping Safety Light Pole Canadian certification
INSTALLATION INSTRUCTIONS	IF 1762 - V-Spring Telescoping Safety Light Pole
SPECIFICATIONS AND DATASHEETS	V-Spring Telescoping Safety Light Pole Eaton Specification Sheet - V65B-AC

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

