



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



VM3P170 VM3 HSG 175W MHP Quad

Hubbell--Killark

| | |
|------------------|--|
| Catalog Number | VM3P170 |
| Manufacturer | Hubbell--Killark |
| Description | VM3 Series - 175W Metal Halide Quadri-Volt Housing |
| Weight per unit | 28.0 (lbs/each) |
| Product Category | Lighting Accessories |

Features

| | |
|-----------------|--|
| amperage rating | Starting amps: 0.95/0.55/0.45/0.40; operating amps: 1.80/1.05/0.90/0.80. |
| Ballast Type | Constant wattage autotransformer |
| Lamp Type | M-137 pulse start metal halide |
| Light Source | Metal Halide Pulse |
| Material | Aluminum, Copper Free (less than 4/10 of 1%) |
| Number of Lamps | 0 |
| Power Factor | 0.9 |
| Power Rating | 175W |
| Socket Type | Mogul base, 4KV pulse rated (1500W/600V) |
| Voltage Rating | Quad - 120/277/347/480 VAC |

Material, Color, and Finish

| | |
|------------------|---|
| Color | Tan |
| fixture material | Copper-free aluminum (less than 4/10 of 1%) |
| Style | Pulse start metal halide fixture |

Dimensions and Weight

| | |
|------|--------------------------------|
| Size | 13.45" H x 13.67" W x 13.67" D |
|------|--------------------------------|

Descriptions

| | |
|------------------------|--|
| Description | VM3 HSG 175W MHP QUAD |
| extra long description | KLRK VM3P170 VM3 HSG 175W MHP QUAD |
| Long Description | VM3 Series - 175W Metal Halide Quadri-Volt Housing |
| Product Type | VM3 HSG 175W MHP Quad |
| Special Features | The VM3 Series is a low bay and high bay HID luminaire. This fixture is made with a cast copper-free aluminum housing and mount that is suitable for harsh and hazardous environments. |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | KILLARK |
| GTIN | 00783936966212 |
| Manufacturers Part Number | VM3P170 |
| series | VM3 |
| UPC | 783936966212 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | METAL HALIDE |
| Type | Aluminum pulse start metal halide fixture |

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 28 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Killark CERTILITE V Series sets a new standard for industrial grade HID luminaires. Designed for installations where moisture, dirt, dust, corrosion, and vibration may be present; these fixtures are suitable for NEMA 3 and 4X areas where wind, water, snow |
| environmental conditions | Hazardous and wet locations |
| standard | cULus, cCSAus |