



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3737 Grader Street Suite 120
75041-0000, TX Garland
Phone: 214-503-7227
Fax: 214-503-9766



WF3LED40KMWM6 3" 8W Led Wafr 4000K *Lithonia Lighting - Acuity*

Catalog Number	WF3LED40KMWM6
Manufacturer	Lithonia Lighting - Acuity
Description	The 3-Inch Wafer™ Led Is An Ultra-Thin Recessed Downlight Ideal For Shallow Ceiling Applications. Quality, Housing-Free Recessed Downlighting Is Achieved With Its Narrow Remote Driver Box. The Wafer Led Is Quick and Simple to Install From Below The Ceiling With As Little As 6-Inch Ceiling Plenum Clearance.
Weight per unit	1.6 (lbs/each)
Product Category	Led Recessed Architectural & S

Features

average life	36,000 hrs
dimmable	Yes
Lamp Included	Yes
Lamp Type	LED - Static
Material	Aluminum
Maximum Operating Temperature	25
media	Yes
pallet quantity	720
Shape	Round
Voltage Rating	120
Warranty	5
Wattage	8

Material, Color, and Finish

Color	White
color rendering index (cri)	80
Finish	Matte
Lens Color	WHITE
Lens Material	Polycarbonate

Dimensions and Weight

Height	1.1000
Length	3.4000
Width	3.4



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3737 Grader Street Suite 120
75041-0000, TX Garland
Phone: 214-503-7227
Fax: 214-503-9766

Descriptions

Construction	New Construction,Remodel
Description	3" 8W LED WAFR 4000K
extra long description	LITH WF3 LED 40K MW M6 3IN wafer-th
Long Description	The 3-inch Wafer™ LED is an ultra-thin recessed downlight ideal for shallow ceiling applications. Quality, housing-free recessed downlighting is achieved with its narrow remote driver box. The Wafer LED is quick and simple to install from below the ceiling with as little as 6-inch ceiling plenum clearance.
Product Type	Downlight

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00889804672794
Manufacturers Part Number	WF3 LED 40K MW M6
UPC	889804672794

Taxonomies, Classifications, and Categories

Category Description	LED GENERAL PURPOSE LIGHTING
Type	Downlight

Trade Size

aperture size	3 in
---------------	------

Packaging

Carton	1
Package	6
Weight	1
Weight Per each	1.6

Uses, Certifications, and Standards

Application	Education,Hospitality,Residential,Retail
environmental conditions	Indoor
Mounting	Recessed
standard	CSAENERGY STAR