



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WP3450BK Cat 5E RJ45 T568 A/B Conn BK (M20)

*Pass & Seymour/Legrand*

Catalog Number	WP3450BK
Manufacturer	Pass & Seymour/Legrand
Description	The Vertical Design Of This High Quality Insert Makes Punchdown Termination Easy. The Insert Is For Use In All Keystone Wall Plates and Is Available In Multiple Colors, As Well As Convenient Contractor Packs.
Weight per unit	0.0391 (lbs/each)
Product Category	Outlets, Jacks, & Plates

### Features

connection	RJ45 Female
Current Rating	1.5 (@ 20 degrees C)

### Material, Color, and Finish

Color	Black
Contact Material	Phosphor bronze alloy with 50 µin gold-plating over 100 µin nickel
Finish	Molded plastic chemically etched with diamond core finish

### Dimensions and Weight

Size	0.67 x 076 x 1.18 (17.02 x 19.30 x 29.97)
------	---

### Descriptions

Description	CAT 5E RJ45 T568 A/B CONN BK (M20)
extra long description	OnQ WP3450BK CAT 5E RJ45 T568 A/B C
Long Description	The vertical design of this high quality insert makes punchdown termination easy. The insert is for use in all Keystone wall plates and is available in multiple colors, as well as convenient contractor packs.
Product Type	Cat 5E RJ45 T568 A/B CNCTR BK (M20)
Special Features	Keyed, Cat 5e, RJ45, Keystone connector

### Manufacturer Information

Brand	Legrand On-Q
GTIN	00804428024897
Manufacturers Part Number	WP3450-BK
UPC	804428024897

### Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	Keyed RJ45 Female Cat 5e Keystone Insert



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	20
Package	120
Weight Per each	0.0391

## Uses, Certifications, and Standards

Application	Residential
environmental conditions	0 to 93 (relative humidity, non-condensing)
Mounting	Keystone opening
standard	CSA, cULus, RoHS, ANSI/UL 1863, Flame-Retardant Plastic UL 94V-0