



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WP3460LA Cat 6 RJ45 T568 A/B Conn La (M20)

*Pass & Seymour/Legrand*

Catalog Number	WP3460LA
Manufacturer	Pass & Seymour/Legrand
Description	Optimize Your Network Setup With This Cat 6 RJ45 Keystone Connector In Light Almond. Designed For Use In All Keystone Wall Plates, It Features A Standard Rca Front Jack That Connects to CAT5, CAT5E, or CAT6 Cables Terminated With RJ-45 Plugs. The Vertical Design Simplifies Punchdown Termination, and Rear Retention Caps Ensure Secure Wire Connections.
Weight per unit	0.0369 (lbs/each)
Product Category	Fiber-Optic Connectors

### Features

connection	RJ45 Female
Current Rating	1.5 (@ 20 degrees C)

### Material, Color, and Finish

Color	Light Almond
Contact Material	Phosphor bronze alloy with 50 µin gold-plating over 100 µin nickel
Finish	Molded plastic chemically etched with diamond core finish

### Dimensions and Weight

Size	063 x 0.87 x 1.26 (16 x 22 x 32)
------	----------------------------------

### Descriptions

Description	CAT 6 RJ45 T568 A/B CONN LA (M20)
extra long description	OnQ WP3460LA CAT 6 RJ45 T568 A/B CN
Long Description	Optimize your network setup with this Cat 6 RJ45 Keystone Connector in light almond. Designed for use in all Keystone Wall Plates, it features a standard RCA front jack that connects to Cat5, Cat5e, or Cat6 cables terminated with RJ-45 plugs. The vertical design simplifies punchdown termination, and rear retention caps ensure secure wire connections.
Product Type	Cat 6 RJ45 T568 A/B CNCTR La (M20)
Special Features	Keyed, Cat 6, RJ45, Keystone connector

### Manufacturer Information

Brand	Legrand On-Q
GTIN	00804428024378
Manufacturers Part Number	WP3460-LA
UPC	804428024378



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	RJ45 Female Cat 6 Keystone Insert

## Packaging

Carton	20
Package	120
Weight Per each	0.0369

## Uses, Certifications, and Standards

Application	Residential
environmental conditions	0 to 93 (relative humidity, non-condensing)
Mounting	Keystone opening
standard	CSA, cULus, RoHS, ANSI/UL 1863, Flame-Retardant Plastic UL 94V-0
Temperature Rating	14 to 140 F (-10 to 60 C)