



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WP3476LA Cat 6 QC A/B Keystone Con La (M10)

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | WP3476LA |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Cat 6 Quick Connect RJ45 Keystone Insert, Light Almond |
| Weight per unit | 0.0402 (lbs/each) |
| Product Category | Outlets, Jacks, & Plates |

Features

| | |
|------------|---|
| connection | RJ45 Female |
| insulation | Electrical Insulation Resistance: 500 (@ 100 VDC) |

Material, Color, and Finish

| | |
|--------|----------------|
| Color | Light Almond |
| Finish | Smooth plastic |

Dimensions and Weight

| | |
|------|--|
| Size | 0.76 x 0.67 x 1.18 (19.30 x 16.9 x 30) |
|------|--|

Descriptions

| | |
|------------------------|--|
| Description | CAT 6 QC A/B KEYSTONE CON LA (M10) |
| extra long description | OnQ WP3476LA CAT 6 QC A/B KEYSTONE |
| Long Description | Cat 6 Quick Connect RJ45 Keystone Insert, Light Almond |
| Product Type | Cat 6 QC A/B Keystone Con La (M10) |
| Special Features | Quick Connect, Cat 6, RJ45, Keystone connector |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Pass & Seymour |
| GTIN | 00804428036777 |
| Manufacturers Part Number | WP3476LA |
| UPC | 804428036777 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Datacom Wiring Devices and Accessories |
| Type | RJ45 Female Cat 6 Keystone Insert |

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Package | 60 |
| Weight Per each | 0.0402 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Residential |
| Enclosure | Housing Material: High Impact Flame Retardant Plastic |
| environmental conditions | 0 to 93 (relative humidity, non-condensing) |
| Mounting | Keystone opening |
| standard | ANSI/TIA-568-C.2 |
| Temperature Rating | 14 to 140 F (-10 to 60 C) |