



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WWCRB Red Winged Wire Connector 500/Bag

Nsi Industries

| | |
|------------------|--|
| Catalog Number | WWCRB |
| Manufacturer | Nsi Industries |
| Description | Winged Wire Connector, (3) #16 Awg Conductor Size, (5) #12 Awg Conductor Size, Insulated, Thermoplastic Insulation Material, Copper Conductor Material, Red Insulation Color, +221 °F Operating Temperature, 0.906 In Overall Width, 1.252 In Overall Height, 600 V, 3.73 LB |
| Weight per unit | 0.0070 (lbs/each) |
| Product Category | Electrical Fixture Conn (Nuts |

Features

| | |
|----------------------|---------------|
| Material | Thermoplastic |
| Number of Conductors | 1 |
| Voltage Rating | 600 |
| Warranty | 1 YEAR |
| Wire Type | CU Wire Only |

Material, Color, and Finish

| | |
|--------|---------------|
| Color | Red |
| Finish | Thermoplastic |

Dimensions and Weight

| | |
|------|---------------------------|
| Size | H=1.25 - W=.906 - ID=.354 |
|------|---------------------------|

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | RED WINGED WIRE CONNECTOR 500/BAG |
| extra long description | NSI WWC-R-B Red Winged Wire Conn w/ |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Easy-Twist |
| GTIN | 00662381141125 |
| UPC | 662381141125 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | WIRE NUTS |
| Type | Winged Wire Connectors |

Availability

| | |
|-------------|-----|
| minimum qty | 500 |
|-------------|-----|

Packaging

| | |
|-----------------|-------|
| Carton | 500 |
| Weight Per each | 0.007 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|---------------|
| Application | Splicing Wire |
| environmental conditions | 105 C |
| standard | UL 486C |
| Temperature Rating | 105 C |