



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WWHRL75 High Voltage Rubber Tape W/Liner 30 FT X .75 In

*Nsi Industries*

|                  |  |
|------------------|--|
| Catalog Number   | WWHRL75  |
| Manufacturer     | Nsi Industries   |
| Description      | Warriorwrap WW-HRL-75 Black High-Voltage Lined Rubber Splicing Tape Is Strong Enough For Professional Environments and Gets The Job Done Right The First Time, Every Time. This Tape Is 30MIL Thick, .75 Inch Wide, 30FT Long and Has An Ethylene Rubber-Based Design. The Self-Bonding Adhesive Helps Stick to Uneven Surfaces and Easily Conforms to Irregular Shapes, While The Liner Repels Dirt and Dust During Installation. Top Breaking Strength and Elasticity Make Warriorwrap An Excellent Choice For Insulating. |
| Weight per unit  | 0.1770 (lbs/each)  |
| Product Category | Markers & Marking Tapes - Tape   |

### Features

|                   |              |
|-------------------|--------------|
| maximum voltage   | 69           |
| Temperature Range | 130 C, 266 F |
| Tensile Strength  | 333.6        |
| Warranty          | 1 YEAR       |

### Material, Color, and Finish

|                  |     |
|------------------|-----|
| Backing Material | NSI |
|------------------|-----|

### Dimensions and Weight

|           |                    |
|-----------|--------------------|
| Length    | 30                 |
| Thickness | 30                 |
| Width     | 0.7500000000000000 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | HIGH VOLTAGE RUBBER TAPE W/LINER 30 FT X .75 IN  |
| extra long description | NSI WW-HRL-75 Lined Rubber Tape H  |
| Features               | Its Warrior Time. At NSI, we put our 45 years of experience in the electrical industry into WarriorWrap, electrical tape strong enough to rise to any challenge. That quality starts with strong adhesion to stick to uneven surfaces. But that's not all—it also features the best breaking strength around and unmatched elasticity. This high-voltage lined rubber splicing tape can handle the toughest jobs, like the insulation and jacketing of splices on power cables from 600-Volt up to 69,000 Volt. The self-b   |
| Long Description       | WarriorWrap WW-HRL-75 Black High-Voltage Lined Rubber Splicing Tape is strong enough for professional environments and gets the job done right the first time, every time. This tape is 30mil thick, .75 inch wide, 30ft long and has an ethylene rubber-based design. The self-bonding adhesive helps stick to uneven surfaces and easily conforms to irregular shapes, while the liner repels dirt and dust during installation. Top breaking strength and elasticity make WarriorWrap an excellent choice for insulating, |
| Product Type           | Lined Rubber Tape HV .75" 30FT   |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | NSi            |
| GTIN                      | 00662381365767 |
| Manufacturers Part Number | WW-HRL-75      |
| UPC                       | 662381365767   |

## Taxonomies, Classifications, and Categories

|                      |      |
|----------------------|------|
| Category Description | TAPE |
|----------------------|------|

## Packaging

|                 |       |
|-----------------|-------|
| Carton          | 1     |
| Weight Per each | 0.177 |