

# Eaton XBUT4D22

Catalog Number: XBUT4D22

Eaton XB IEC terminal block, Screw Connection Multi-Conductor Terminal Blocks, Gray, 10 AWG/4 mm<sup>2</sup> maximum wire, Four-wire

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton XB IEC terminal block	XBUT4D22
<b>UPC</b>	<b>Product Length/Depth</b>
782116905188	1.85 in
<b>Product Height</b>	<b>Product Width</b>
2.17 in	0.24 in
<b>Product Weight</b>	<b>Warranty</b>
0.04 lb	1 year
<b>Certifications</b>	
UL Listed	
CSA Certified	

## Product specifications

### Type

IEC-XB Series

### Amperage Rating

36A (IEC), 30A (UL)

### Voltage rating

IEC 500V, UL 150V

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - XBUT4D22](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton XBUT4D22

Catalog Number: XBUT4D22

Eaton XB IEC terminal block, Screw Connection Multi-Conductor Terminal Blocks, Gray, 10 AWG/4 mm<sup>2</sup> maximum wire, Four-wire

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton XB IEC terminal block	XBUT4D22
<b>UPC</b>	<b>Product Length/Depth</b>
782116905188	1.85 in
<b>Product Height</b>	<b>Product Width</b>
2.17 in	0.24 in
<b>Product Weight</b>	<b>Warranty</b>
0.04 lb	1 year
<b>Certifications</b>	
UL Listed	
CSA Certified	

## Product specifications

### Type

IEC-XB Series

### Amperage Rating

36A (IEC), 30A (UL)

### Voltage rating

IEC 500V, UL 150V

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - XBUT4D22](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)