

Specifications

Eaton XBUT6FBN

Eaton XB IEC terminal block, Fuse Terminal Blocks, Black, 8 AWG/6 mm² maximum wire

General specifications

PRODUCT NAME	Eaton XB IEC terminal block
CATALOG NUMBER	XBUT6FBN
UPC	782116905256
PRODUCT LENGTH/DEPTH	1.85 in
PRODUCT HEIGHT	2.17 in
PRODUCT WIDTH	0.32 in
PRODUCT WEIGHT	0.03 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	As disconnect terminal block 500V, as fuse terminal block 400V.

Product specifications

TYPE	Screw Connection Fuse
	Terminal Blocks for 6.3 x 32 mm Fuse
AMPERAGE RATING	10A (IEC), 10A (UL)
VOLTAGE RATING	UL 400V

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - XBUT6FBN](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Eaton XBUT6FBN

Eaton XB IEC terminal block, Fuse Terminal Blocks, Black, 8 AWG/6 mm² maximum wire

General specifications

PRODUCT NAME	Eaton XB IEC terminal block
CATALOG NUMBER	XBUT6FBN
UPC	782116905256
PRODUCT LENGTH/DEPTH	1.85 in
PRODUCT HEIGHT	2.17 in
PRODUCT WIDTH	0.32 in
PRODUCT WEIGHT	0.03 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	As disconnect terminal block 500V, as fuse terminal block 400V.

Product specifications

TYPE	Screw Connection Fuse
	Terminal Blocks for 6.3 x 32 mm Fuse
AMPERAGE RATING	10A (IEC), 10A (UL)
VOLTAGE RATING	UL 400V

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - XBUT6FBN](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

