

Specifications



Eaton XBUT6FBNL250

Eaton XB IEC terminal block, Fuse Terminal Blocks with LED 110-250V, 0.5-2.5 mA, Black, 8 AWG/6 mm² maximum wire

General specifications

PRODUCT NAME	Eaton XB IEC terminal block
CATALOG NUMBER	XBUT6FBNL250
UPC	782116905287
PRODUCT LENGTH/DEPTH	1.85 in
PRODUCT HEIGHT	2.17 in
PRODUCT WIDTH	0.32 in
PRODUCT WEIGHT	0.05 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	As disconnect terminal block 500V, as fuse terminal block 400V.



Powering Business Worldwide

Product specifications

TYPE	Screw Connection Fuse Terminal Blocks for 6.3 x 32 mm Fuse
AMPERAGE RATING	10A (IEC), 10A (UL)
VOLTAGE RATING	UL 400V

Resources

SPECIFICATIONS AND
DATASHEETS

[Eaton Specification Sheet -
XBUT6FBNL250](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the
latest product and support
information.



© 2025 Eaton. All Rights Reserved.

Specifications



Eaton XBUT6FBNL250

Eaton XB IEC terminal block, Fuse Terminal Blocks with LED 110-250V, 0.5-2.5 mA, Black, 8 AWG/6 mm² maximum wire

General specifications

PRODUCT NAME	Eaton XB IEC terminal block
CATALOG NUMBER	XBUT6FBNL250
UPC	782116905287
PRODUCT LENGTH/DEPTH	1.85 in
PRODUCT HEIGHT	2.17 in
PRODUCT WIDTH	0.32 in
PRODUCT WEIGHT	0.05 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	As disconnect terminal block 500V, as fuse terminal block 400V.



Powering Business Worldwide

Product specifications

TYPE	Screw Connection Fuse Terminal Blocks for 6.3 x 32 mm Fuse
AMPERAGE RATING	10A (IEC), 10A (UL)
VOLTAGE RATING	UL 400V

Resources

SPECIFICATIONS AND
DATASHEETS

[Eaton Specification Sheet -
XBUT6FBNL250](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.