

Specifications



Photo is representative



Eaton XTOE005CCS

Eaton C440 electronic overload relay, XT IEC Electronic Overload Relay, 1-5A overload range, 45 mm frame, NO-NC contact configuration, Direct to contactor mounting, Selectable - 10A, 10, 20, 30 trip type

General specifications

PRODUCT NAME	Eaton C440 electronic overload relay
---------------------	--------------------------------------

CATALOG NUMBER	XTOE005CCS
-----------------------	------------

UPC	786685416465
------------	--------------

PRODUCT LENGTH/DEPTH	1.8 in
-----------------------------	--------

PRODUCT HEIGHT	4.3 in
-----------------------	--------

PRODUCT WIDTH	1.42 in
----------------------	---------

PRODUCT WEIGHT	1 lb
-----------------------	------

COMPLIANCES	CE Marked ATEX Compliant RoHS Compliant
--------------------	---

CERTIFICATIONS	EN 60947 UL Listed CSA Certified IEC 60947
-----------------------	---

Product specifications

OVERLOAD RANGE	1-5A
TYPE	Electronic overload relay
FRAME SIZE	45 mm
MOUNTING METHOD	Direct
CONTACT CONFIGURATION	NO, NC
TRIP TYPE	Selectable 10 A, class 10 ,20, 30

Resources

BROCHURES	C440 Electronic Overload Relay
CATALOGS	Motor Control and Protection, NEMA Contactors and Starters, Volume 5, Tab 2
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - XTOE005CCS

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton XTOE005CCS

Eaton C440 electronic overload relay, XT IEC Electronic Overload Relay, 1-5A overload range, 45 mm frame, NO-NC contact configuration, Direct to contactor mounting, Selectable - 10A, 10, 20, 30 trip type

General specifications

PRODUCT NAME	Eaton C440 electronic overload relay
---------------------	--------------------------------------

CATALOG NUMBER	XTOE005CCS
-----------------------	------------

UPC	786685416465
------------	--------------

PRODUCT LENGTH/DEPTH	1.8 in
-----------------------------	--------

PRODUCT HEIGHT	4.3 in
-----------------------	--------

PRODUCT WIDTH	1.42 in
----------------------	---------

PRODUCT WEIGHT	1 lb
-----------------------	------

COMPLIANCES	CE Marked ATEX Compliant RoHS Compliant
--------------------	---

CERTIFICATIONS	EN 60947 UL Listed CSA Certified IEC 60947
-----------------------	---

Product specifications

OVERLOAD RANGE	1-5A
TYPE	Electronic overload relay
FRAME SIZE	45 mm
MOUNTING METHOD	Direct
CONTACT CONFIGURATION	NO, NC
TRIP TYPE	Selectable 10 A, class 10 ,20, 30

Resources

BROCHURES	C440 Electronic Overload Relay
CATALOGS	Motor Control and Protection, NEMA Contactors and Starters, Volume 5, Tab 2
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - XTOE005CCS

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

