

# Specifications

Photo is representative

## Eaton XTCR009B21TD

Eaton XT IEC contactor, 9A, 24 Vdc, 2NO-2NO, 9A, Frame B, 45 mm, 0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @115, 230/200, 230, 460, 575 V), Three-pole, Reversing, XT IEC series, Screw terminals, Full voltage reversing contactor

### General specifications

<b>PRODUCT NAME</b>	Eaton XT IEC contactor
<b>CATALOG NUMBER</b>	XTCR009B21TD
<b>UPC</b>	782116884896
<b>PRODUCT LENGTH/DEPTH</b>	117 mm
<b>PRODUCT HEIGHT</b>	68 mm
<b>PRODUCT WIDTH</b>	90 mm
<b>PRODUCT WEIGHT</b>	0.28 kg
<b>WARRANTY</b>	1 year
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	CSA Certified EN 60947 UL Listed IEC 60947
<b>CATALOG NOTES</b>	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)



Powering Business Worldwide

## Product specifications

<b>AMPERAGE RATING</b>	9A
<b>HP RATING - MAX</b>	0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @115,230/200,230,460,575 V)
<b>NUMBER OF POLES</b>	Three-pole
<b>TYPE</b>	Full voltage reversing contactor
<b>FRAME SIZE</b>	45 mm
<b>TERMINALS</b>	Screw terminals
<b>COIL VOLTAGE</b>	24 Vdc
<b>CONTACT CONFIGURATION</b>	2 NO, 2 NO
<b>CONTINUOUS AMPERE RATING</b>	9 A
<b>SERIES</b>	XT IEC
<b>OPERATION</b>	Reversing

## Resources

<b>CATALOGS</b>	<a href="#">Motor Control and Protection, IEC Contactors and Starters, Volume 5, Tab 1</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - XTCR009B21TD</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications

Photo is representative

## Eaton XTCR009B21TD

Eaton XT IEC contactor, 9A, 24 Vdc, 2NO-2NO, 9A, Frame B, 45 mm, 0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @115, 230/200, 230, 460, 575 V), Three-pole, Reversing, XT IEC series, Screw terminals, Full voltage reversing contactor

### General specifications

<b>PRODUCT NAME</b>	Eaton XT IEC contactor
<b>CATALOG NUMBER</b>	XTCR009B21TD
<b>UPC</b>	782116884896
<b>PRODUCT LENGTH/DEPTH</b>	117 mm
<b>PRODUCT HEIGHT</b>	68 mm
<b>PRODUCT WIDTH</b>	90 mm
<b>PRODUCT WEIGHT</b>	0.28 kg
<b>WARRANTY</b>	1 year
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	CSA Certified EN 60947 UL Listed IEC 60947
<b>CATALOG NOTES</b>	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)



Powering Business Worldwide

## Product specifications

<b>AMPERAGE RATING</b>	9A
<b>HP RATING - MAX</b>	0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @115,230/200,230,460,575 V)
<b>NUMBER OF POLES</b>	Three-pole
<b>TYPE</b>	Full voltage reversing contactor
<b>FRAME SIZE</b>	45 mm
<b>TERMINALS</b>	Screw terminals
<b>COIL VOLTAGE</b>	24 Vdc
<b>CONTACT CONFIGURATION</b>	2 NO, 2 NO
<b>CONTINUOUS AMPERE RATING</b>	9 A
<b>SERIES</b>	XT IEC
<b>OPERATION</b>	Reversing

## Resources

<b>CATALOGS</b>	<a href="#">Motor Control and Protection, IEC Contactors and Starters, Volume 5, Tab 1</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - XTCR009B21TD</a>

---

**PROJECT NAME:**

---

**PROJECT NUMBER:**

---

**PREPARED BY:**

---

**DATE:**

---



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

