



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## YA25LBOX 1/0 Cu 1H Short 5/16 Burndy LLC

Catalog Number	YA25LBOX
Manufacturer	Burndy LLC
Description	Cu Compression Terminal Code Conductor, Beveled Entry, 1 Hole W/Inspwindow, 1/0AWG (Code) 100 (Navy), 600V-35KV, 5/16" Stud, Standard Barrel, Electro-Tin Plated.
Weight per unit	0.0500 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Die Index	12
Material	Copper

### Material, Color, and Finish

Color Code	PINK
------------	------

### Descriptions

Description	1/0 CU 1H SHORT 5/16
extra long description	BUR YA25LBOX 1/0 CU 1-HOLE SHORT 5/
Long Description	CU Compression Terminal Code Conductor, Beveled Entry, 1 Hole W/InspWindow, 1/0AWG (Code) 100 (Navy), 600V-35kV, 5/16" Stud, Standard Barrel, Electro-Tin Plated.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Package: Box, Finish: Electro-Tin Plated, Die Index: 12, Wire Strip Length: 15/16 IN, Temperature Rating: 90 DEG C, Tongue Angle: Straight, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W25VT, W25RT, X25RT Die, (2), Hydraulic: BCT500HS, Y500CTHS Tool, W25VT, W25RT, X25RT Die, (2), Y35, Y39, Y750, PAT750 Tool, U25RT, U2CABT Die, (1), Y46 Tool, U25RT, U2CABT Die With PUADP-1 Ad

### Manufacturer Information

Brand	BURNDY
GTIN	00781810553251
Manufacturers Part Number	YA25LBOX
UPC	781810553251

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel, Tin Plated



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.05

## Uses, Certifications, and Standards

Application	For Code Conductor
standard	UL 486A-486B