



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## YA2CL2BOX 2AWG 1H Cop Lug

Burndy LLC

Catalog Number	YA2CL2BOX
Manufacturer	Burndy LLC
Description	2 Awg Cu, One Hole, 1/4 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UI/Csa 90 Up to 35KV, Brown Color Code, 10 Die Index.
Weight per unit	0.0300 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Die Index	10
Material	Copper
Voltage Rating	35

### Material, Color, and Finish

Color Code	BROWN
------------	-------

### Descriptions

Description	2AWG 1H COP LUG
extra long description	BUR YA2CL2BOX 2STR CU 1-HOLE SHORT
Long Description	2 AWG CU, One Hole, 1/4 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA 90 Up to 35kV, BROWN Color Code, 10 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Wire Strip Length: 15/16 IN, Package: Box, Tongue Angle: Straight, Finish: Electro-Tin Plated, Temperature Rating: 90 DEG C, Die Index: 10, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W2CVT, W2CRT, X2CRT Die, (1), Hydraulic: BCT500HS, Y500CTHS Tool, W2CVT, W2CRT, X2CRT Die, (1), Y35, Y39, Y750, PAT750 Tool, U2CRT Die, (1), Y46 Tool, U2CRT Die With PUADP-1 Adapter, (1), Colo

### Manufacturer Information

Brand	BURNDY
GTIN	00781810551752
Manufacturers Part Number	YA2CL2BOX
UPC	781810551752

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel, Tin Plated



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	25
Weight Per each	0.03

## Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B