

Specifications



Eaton XTOE020CCS

Eaton C440 electronic overload relay, XT IEC, 4-20A overload range, 45 mm Frame size, NO-NC contact configuration, Direct to contactor mounting, Selectable - 10A, 10, 20, 30 trip type

General specifications

| | |
|----------------------|---|
| PRODUCT NAME | Eaton C440 electronic overload relay |
| CATALOG NUMBER | XTOE020CCS |
| UPC | 786685416472 |
| PRODUCT LENGTH/DEPTH | 1.8 in |
| PRODUCT HEIGHT | 4.3 in |
| PRODUCT WIDTH | 1.42 in |
| PRODUCT WEIGHT | 0.87 lb |
| COMPLIANCES | ATEX Compliant RoHS Compliant CE Marked |
| CERTIFICATIONS | IEC 60947 CSA Certified EN 60947 UL Listed |

| Product specifications | |
|------------------------|-----------------------------------|
| OVERLOAD RANGE | 4-20A |
| TYPE | Electronic overload relay |
| FRAME SIZE | 45 mm |
| MOUNTING METHOD | Direct |
| CONTACT CONFIGURATION | NO, NC |
| TRIP TYPE | Selectable 10 A, class 10 ,20, 30 |

| Resources | |
|-------------------------------|---|
| BROCHURES | C440 Electronic Overload Relay |
| CATALOGS | Motor Control and Protection, NEMA Contactors and Starters, Volume 5, Tab 2 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - XTOE020CCS |

| |
|-----------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| DATE: |



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.



Specifications



Eaton XTOE020CCS

Eaton C440 electronic overload relay, XT IEC, 4-20A overload range, 45 mm Frame size, NO-NC contact configuration, Direct to contactor mounting, Selectable - 10A, 10, 20, 30 trip type

General specifications

| | |
|----------------------|---|
| PRODUCT NAME | Eaton C440 electronic overload relay |
| CATALOG NUMBER | XTOE020CCS |
| UPC | 786685416472 |
| PRODUCT LENGTH/DEPTH | 1.8 in |
| PRODUCT HEIGHT | 4.3 in |
| PRODUCT WIDTH | 1.42 in |
| PRODUCT WEIGHT | 0.87 lb |
| COMPLIANCES | ATEX Compliant RoHS Compliant CE Marked |
| CERTIFICATIONS | IEC 60947 CSA Certified EN 60947 UL Listed |

| Product specifications | |
|------------------------|-----------------------------------|
| OVERLOAD RANGE | 4-20A |
| TYPE | Electronic overload relay |
| FRAME SIZE | 45 mm |
| MOUNTING METHOD | Direct |
| CONTACT CONFIGURATION | NO, NC |
| TRIP TYPE | Selectable 10 A, class 10 ,20, 30 |

| Resources | |
|-------------------------------|---|
| BROCHURES | C440 Electronic Overload Relay |
| CATALOGS | Motor Control and Protection, NEMA Contactors and Starters, Volume 5, Tab 2 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - XTOE020CCS |

| |
|-----------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| DATE: |



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

