



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YA27LBOX 3/0 Cu 1H Short 1/2 Burndy LLC

| | |
|------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | YA27LBOX |
| Manufacturer | Burndy LLC |
| Description | 3/0 Awg Cu, One Hole, 1/2 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UI/Csa 90 Up to 35KV, Orange Color Code, 14 Die Index. |
| Weight per unit | 0.0800 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|----------------|--------|
| Die Index | 14 |
| Material | Copper |
| Voltage Rating | 35 |

Material, Color, and Finish

| | |
|------------|--------|
| Color Code | ORANGE |
|------------|--------|

Descriptions

| | |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | 3/0 CU 1H SHORT 1/2 |
| extra long description | BUR YA27LBOX 3/0 CU 1-HOLE SHORT 1/2 |
| Long Description | 3/0 AWG CU, One Hole, 1/2 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA 90 Up to 35kV, ORANGE Color Code, 14 Die Index. |
| Product Type | Terminal |
| Special Features | Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Temperature Rating: 90 DEG C, Finish: Electro-Tin Plated, Tongue Angle: Straight, Die Index: 14, Package: Box, Wire Strip Length: 1-1/16 IN, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W27VT, W27RT Die, (2), X27RT Die, (3), Hydraulic: BCT500HS, Y500CTHS Tool, W27VT, W27RT Die, (2), X27RT Die, (3), Y35, Y39, Y750, PAT750 Tool, U27RT Die, (1), Y46 Tool, U27RT Die With PUADP-1 |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | BURNDY |
| GTIN | 00781810553800 |
| Manufacturers Part Number | YA27LBOX |
| UPC | 781810553800 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | Standard Barrel, Tin Plated |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.08 |

Uses, Certifications, and Standards

| | |
|-------------|------------------|
| Application | Wire Termination |
| standard | UL 486A-486B |