



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1455A6503 30' Reflex Light Operate Ac/DC Connector

Eaton Corp

Catalog Number	1455A6503
Manufacturer	Eaton Corp
Description	Eaton Photoelectric Sensor, Retroreflective, Forward Viewing, Light, Output Status, Mini, 300 Ma Ac/DC At 20-264 Vac/15-30 VDC, 3 Pin, Ac: L1 Switched, DC: NPN Open Collector, 20-264 Vac/15-30 VDC
Weight per unit	0.4200 (lbs/each)
Product Category	Photoelectric Sensors

Features

connection	Mini
dimensions	3.1900 IN X 1.8300 IN X 1.6400 IN

Dimensions and Weight

Height	1.64
Length	3.19
Width	1.83

Descriptions

Description	30' REFLEX LIGHT OPERATE AC/DC CONNECTOR
extra long description	ETN 1455A-6503 30' REFLEX,LIGHT OPE
Features	55 series photoelectric sensors are identical to the 50 series except without the interchangeable outputs or logic functions. They offer durability and high optical performance in a cost-effective, self-contained package. The 55 Series features sensors with AC and DC operation in a single unit. A relay option is available on these models that provides a 3 Amp SPDT relay output for high current switching.
Long Description	Eaton Photoelectric Sensor, Retroreflective, Forward Viewing, Light, Output status, Mini, 300 mA AC/DC at 20-264 Vac/15-30 Vdc, 3 pin, AC: L1 switched, DC: NPN open collector, 20-264 Vac/15-30 Vdc
Product Type	30' Reflex, Light Operate, Ac/dc, Connector

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782114106785
Manufacturers Part Number	1455A-6503
UPC	782114106785

Taxonomies, Classifications, and Categories

Type	Photoelectric Sensor
------	----------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.42

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Operating Temperature	-40° to 158°F (-40° to 70°C)
standard	CSA Certified,UL Listed