

Seoprene® 105 Black—Large Sizes



| PART NUMBER | DESCRIPTION | STRANDING | NOMINAL INSULATION THICKNESS | NOMINAL JACKET THICKNESS | NOMINAL OD | AMPACITY | WT/M' |
|-------------|-------------|--------------|------------------------------|--------------------------|------------|----------|-------|
| 22320 | 8/3 SEOW | 96/28 | .048 | .095 | .700 | 40 | 282 |
| 22420 | 8/4 SEOW | 96/28 | .048 | .100 | .783 | 35 | 368 |
| 22470 | 8/5 SEOW | 96/28 | .048 | .100 | .850 | 28 | 442 |
| 22321 | 6/3 SEOW | 96/26 | .048 | .100 | .818 | 55 | 451 |
| 22421 | 6/4 SEOW | 96/26 | .048 | .100 | .892 | 45 | 573 |
| 22521 | 6/5 SEOW | 96/26 | .048 | .110 | .992 | 36 | 720 |
| 22322 | 4/3 SEOW | 96/24 | .048 | .110 | .982 | 70 | 668 |
| 22422 | 4/4 SEOW | 96/24 | .048 | .125 | 1.104 | 60 | 882 |
| 22552 | 4/5 SEOW | 96/24 | .048 | .125 | 1.203 | 48 | 1091 |
| 22323 | 2/3 SEOW | 7 X 17/.0223 | .050 | .125 | 1.158 | 95 | 932 |
| 22423 | 2/4 SEOW | 7 X 17/.0223 | .050 | .125 | 1.267 | 80 | 1152 |
| 22553 | 2/5 SEOW | 7 X 17/.0223 | .050 | .135 | 1.389 | 64 | 1414 |

UL constructions available

Applications: Heavy machine tools; compressors; portable tools; robotics; motor controls.

Suprene™ 105 Yellow

For use in the toughest environments. Offers a temperature rating of -60°C to 105°C and 25% more abrasion resistance. Use on heavy-duty industrial applications where chemicals and/or abrasion present a problem. Safety yellow color provides high visibility.



| PART NUMBER | DESCRIPTION | STRANDING | NOMINAL INSULATION THICKNESS | NOMINAL JACKET THICKNESS | NOMINAL OD | AMPACITY | WT/M' |
|-------------|-------------|-----------|------------------------------|--------------------------|------------|----------|-------|
| 23345 | 18/3 SJEOOW | 16/30 | .031 | .032 | .318 | 10 | 52 |
| 23346 | 16/3 SJEOOW | 26/30 | .031 | .032 | .348 | 13 | 65 |
| 23446 | 16/4 SJEOOW | 26/30 | .031 | .032 | .376 | 10 | 76 |
| 23347 | 14/3 SJEOOW | 41/30 | .031 | .032 | .391 | 18 | 81 |
| 23447 | 14/4 SJEOOW | 41/30 | .031 | .032 | .418 | 15 | 103 |
| 23348 | 12/3 SJEOOW | 65/30 | .031 | .047 | .460 | 25 | 122 |
| 23349 | 10/3 SJEOOW | 104/30 | .031 | .062 | .599 | 30 | 216 |
| 22345 | 18/3 SEOW | 16/30 | .031 | .062 | .388 | 10 | 69 |
| 22445 | 18/4 SEOW | 16/30 | .031 | .062 | .407 | 7 | 78 |
| 22346 | 16/3 SEOW | 26/30 | .031 | .062 | .414 | 13 | 80 |
| 22446 | 16/4 SEOW | 26/30 | .031 | .062 | .446 | 10 | 96 |
| 22347 | 14/3 SEOW | 41/30 | .031 | .082 | .556 | 18 | 149 |
| 22447 | 14/4 SEOW | 41/30 | .031 | .082 | .591 | 15 | 180 |
| 22348 | 12/3 SEOW | 65/30 | .031 | .097 | .635 | 25 | 197 |
| 22448 | 12/4 SEOW | 65/30 | .031 | .097 | .674 | 20 | 240 |
| 22349 | 10/3 SEOW | 104/30 | .031 | .095 | .695 | 30 | 257 |
| 22449 | 10/4 SEOW | 104/30 | .031 | .095 | .735 | 25 | 313 |

Applications: Indoor and outdoor temporary power; wherever high visibility is needed for safety; high abrasion and chemical exposure.



Seoprene®

Seoprene® 105 Black—Large Sizes



| PART NUMBER | DESCRIPTION | STRANDING | NOMINAL INSULATION THICKNESS | NOMINAL JACKET THICKNESS | NOMINAL OD | AMPACITY | WT/M' |
|-------------|-------------|--------------|------------------------------|--------------------------|------------|----------|-------|
| 22320 | 8/3 SEOWW | 96/28 | .048 | .095 | .700 | 40 | 282 |
| 22420 | 8/4 SEOWW | 96/28 | .048 | .100 | .783 | 35 | 368 |
| 22470 | 8/5 SEOWW | 96/28 | .048 | .100 | .850 | 28 | 442 |
| 22321 | 6/3 SEOWW | 96/26 | .048 | .100 | .818 | 55 | 451 |
| 22421 | 6/4 SEOWW | 96/26 | .048 | .100 | .892 | 45 | 573 |
| 22521 | 6/5 SEOWW | 96/26 | .048 | .110 | .992 | 36 | 720 |
| 22322 | 4/3 SEOWW | 96/24 | .048 | .110 | .982 | 70 | 668 |
| 22422 | 4/4 SEOWW | 96/24 | .048 | .125 | 1.104 | 60 | 882 |
| 22552 | 4/5 SEOWW | 96/24 | .048 | .125 | 1.203 | 48 | 1091 |
| 22323 | 2/3 SEOWW | 7 X 17/.0223 | .050 | .125 | 1.158 | 95 | 932 |
| 22423 | 2/4 SEOWW | 7 X 17/.0223 | .050 | .125 | 1.267 | 80 | 1152 |
| 22553 | 2/5 SEOWW | 7 X 17/.0223 | .050 | .135 | 1.389 | 64 | 1414 |

UL constructions available

Applications: Heavy machine tools; compressors; portable tools; robotics; motor controls.

Suprene™ 105 Yellow

For use in the toughest environments. Offers a temperature rating of -60°C to 105°C and 25% more abrasion resistance. Use on heavy-duty industrial applications where chemicals and/or abrasion present a problem. Safety yellow color provides high visibility.



| PART NUMBER | DESCRIPTION | STRANDING | NOMINAL INSULATION THICKNESS | NOMINAL JACKET THICKNESS | NOMINAL OD | AMPACITY | WT/M' |
|-------------|-------------|-----------|------------------------------|--------------------------|------------|----------|-------|
| 23345 | 18/3 SJEOOW | 16/30 | .031 | .032 | .318 | 10 | 52 |
| 23346 | 16/3 SJEOOW | 26/30 | .031 | .032 | .348 | 13 | 65 |
| 23446 | 16/4 SJEOOW | 26/30 | .031 | .032 | .376 | 10 | 76 |
| 23347 | 14/3 SJEOOW | 41/30 | .031 | .032 | .391 | 18 | 81 |
| 23447 | 14/4 SJEOOW | 41/30 | .031 | .032 | .418 | 15 | 103 |
| 23348 | 12/3 SJEOOW | 65/30 | .031 | .047 | .460 | 25 | 122 |
| 23349 | 10/3 SJEOOW | 104/30 | .031 | .062 | .599 | 30 | 216 |
| 22345 | 18/3 SEOWW | 16/30 | .031 | .062 | .388 | 10 | 69 |
| 22445 | 18/4 SEOWW | 16/30 | .031 | .062 | .407 | 7 | 78 |
| 22346 | 16/3 SEOWW | 26/30 | .031 | .062 | .414 | 13 | 80 |
| 22446 | 16/4 SEOWW | 26/30 | .031 | .062 | .446 | 10 | 96 |
| 22347 | 14/3 SEOWW | 41/30 | .031 | .082 | .556 | 18 | 149 |
| 22447 | 14/4 SEOWW | 41/30 | .031 | .082 | .591 | 15 | 180 |
| 22348 | 12/3 SEOWW | 65/30 | .031 | .097 | .635 | 25 | 197 |
| 22448 | 12/4 SEOWW | 65/30 | .031 | .097 | .674 | 20 | 240 |
| 22349 | 10/3 SEOWW | 104/30 | .031 | .095 | .695 | 30 | 257 |
| 22449 | 10/4 SEOWW | 104/30 | .031 | .095 | .735 | 25 | 313 |

Applications: Indoor and outdoor temporary power; wherever high visibility is needed for safety; high abrasion and chemical exposure.



Seoprene®