

# #184 Flexible Duct



**Product Description**

Model 184 is a flexible duct with factory installed insulation and vapor barrier. Manufactured in sizes from 4" through 20" in 25 foot lengths and compactly packaged to reduce storage space and ease handling. Our flexible duct offers great versatility and substantial savings in installation time and initial cost. Available in bags or box.

**Model 184 Flexible Duct Components**

**Internal Core (Duct) Material:**

Polyester (Manufactured to ASTM Specifications)

**Internal Core Reinforcement:**

High Carbon, Hard Drawn, Spring Steel Wire (Manufactured to ASTM Specifications)

**Insulation:**

Fiber Glass Wool, Continuous Blanket, Thermal Resistance (R-Value) (Test Method, ASTM C 518)

**Vapor Barrier:**

Metalized Polyester with Fiberglass Yarn Reinforcement

**Surface Burn Characteristics:**

Flame Spread: 25 or less  
Smoke Developed: 50 or less  
(Test Method: UL procedure 723)

Maximum Positive Pressure: 10" Water Column  
Maximum Negative Pressure: 0.5" Water Column  
Water Vapor Permeance 0.17 grains per sq. ft. per hour per inch of Hg. (Test Method: ASTM E 96, Procedure A)

**Submittal Approval:**

Job: \_\_\_\_\_  
Location: \_\_\_\_\_  
Engineer \_\_\_\_\_

PO No: \_\_\_\_\_  
Job No: \_\_\_\_\_  
Representative: \_\_\_\_\_

**APPROVED for CONSTRUCTION:**

By: \_\_\_\_\_ Title: \_\_\_\_\_ Date: \_\_\_\_\_

4200 I 45, P.O. Box 1320, Ennis, TX 75120 Tel. (972) 875-5884 Fax (972) 875-0308  
7951 East Evans Rd., San Antonio, TX 78266 Tel. (210) 651-5305 Fax (210) 651-5660

# #184 Flexible Duct



**Product Description**

Model 184 is a flexible duct with factory installed insulation and vapor barrier. Manufactured in sizes from 4" through 20" in 25 foot lengths and compactly packaged to reduce storage space and ease handling. Our flexible duct offers great versatility and substantial savings in installation time and initial cost. Available in bags or box.

**Model 184 Flexible Duct Components**

**Internal Core (Duct) Material:**

Polyester (Manufactured to ASTM Specifications)

**Internal Core Reinforcement:**

High Carbon, Hard Drawn, Spring Steel Wire (Manufactured to ASTM Specifications)

**Insulation:**

Fiber Glass Wool, Continuous Blanket, Thermal Resistance (R-Value) (Test Method, ASTM C 518)

**Vapor Barrier:**

Metalized Polyester with Fiberglass Yarn Reinforcement

**Surface Burn Characteristics:**

Flame Spread: 25 or less  
Smoke Developed: 50 or less  
(Test Method: UL procedure 723)

Maximum Positive Pressure: 10" Water Column  
Maximum Negative Pressure: 0.5" Water Column  
Water Vapor Permeance 0.17 grains per sq. ft. per hour per inch of Hg. (Test Method: ASTM E 96, Procedure A)

**Submittal Approval:**

Job: \_\_\_\_\_  
Location: \_\_\_\_\_  
Engineer \_\_\_\_\_

PO No: \_\_\_\_\_  
Job No: \_\_\_\_\_  
Representative: \_\_\_\_\_

**APPROVED for CONSTRUCTION:**

By: \_\_\_\_\_ Title: \_\_\_\_\_ Date: \_\_\_\_\_

4200 I 45, P.O. Box 1320, Ennis, TX 75120 Tel. (972) 875-5884 Fax (972) 875-0308  
7951 East Evans Rd., San Antonio, TX 78266 Tel. (210) 651-5305 Fax (210) 651-5660