



SAFETY DATA SHEET

1. Identification

Product identifier	Dielectric Grease Compound
Other means of identification	
Product Code	No. 02085 (Item# 1003199)
Recommended use	Lubricates, protects and insulates electrical connections
Recommended restrictions	None known.
Manufacturer/Importer/Supplier/Distributor information	
Manufactured or sold by:	
Company name	CRC Industries, Inc.
Address	885 Louis Dr. Warminster, PA 18974 US
Telephone	
General Information	215-674-4300
Technical Assistance	800-521-3168
Customer Service	800-272-4620
24-Hour Emergency	800-424-9300 (US)
(CHEMTREC)	703-527-3887 (International)
Website	www.crcindustries.com

2. Hazard(s) identification

Physical hazards	Gases under pressure	Compressed gas
Health hazards	Not classified.	
Environmental hazards	Not classified.	
OSHA defined hazards	Not classified.	

Label elements



Signal word	Warning
Hazard statement	Contains gas under pressure; may explode if heated.
Precautionary statement	
Prevention	Do not puncture or incinerate container. Do not expose to heat or store at temperatures above 49°C/120°F. Use with adequate ventilation. Open doors and windows or use other means to ensure a fresh air supply during use and while product is drying. Observe good industrial hygiene practices.
Response	Wash hands after handling.
Storage	Protect from sunlight. Store in a well-ventilated place. Exposure to high temperature may cause can to burst.
Disposal	Dispose of contents/container in accordance with local/regional/national regulations.
Hazard(s) not otherwise classified (HNOC)	None known.

Supplemental information

When exposed to extreme heat or hot surfaces, vapors may decompose to harmful or fatal corrosive gases such as hydrogen fluoride.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
polydimethylsiloxane		63148-62-9	80 - 90
amorphous fumed silica		112945-52-5	5 - 10
nitrogen		7727-37-9	1 - 3
polytetrafluoroethylene		9002-84-0	1 - 3

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	Move to fresh air. Call a physician if symptoms develop or persist.
Skin contact	Wash off with soap and water. Get medical attention if irritation develops and persists.
Eye contact	Rinse with water. Get medical attention if irritation develops and persists.
Ingestion	If swallowed, do NOT induce vomiting. Get medical attention if symptoms occur.
Most important symptoms/effects, acute and delayed	Direct contact with eyes may cause temporary irritation.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

5. Fire-fighting measures

Suitable extinguishing media	Water spray. Foam. Dry chemical powder. Carbon dioxide (CO ₂).
Unsuitable extinguishing media	None known.
Specific hazards arising from the chemical	During fire, gases hazardous to health may be formed. When exposed to extreme heat or hot surfaces, vapors may decompose to harmful or fatal corrosive gases such as hydrogen fluoride.
Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire-fighting equipment/instructions	In case of fire: Stop leak if safe to do so. Move containers from fire area if you can do so without risk. Use water spray to cool unopened containers.
General fire hazards	Contents under pressure. Pressurized container may rupture when exposed to heat or flame.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Keep out of low areas. Many gases are heavier than air and will spread along ground and collect in low or confined areas (sewers, basements, tanks). Wear appropriate protective equipment and clothing during clean-up. Emergency personnel need self-contained breathing equipment. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ventilate closed spaces before entering them. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
Methods and materials for containment and cleaning up	Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil, etc.) away from spilled material. Wipe up with absorbent material (e.g. cloth, fleece, vermiculite). Sweep up or vacuum up spillage and collect in suitable container for disposal. The product is immiscible with water and will spread on the water surface. Stop the flow of material, if this is without risk. For waste disposal, see section 13 of the SDS. Prevent entry into waterways, sewer, basements or confined areas.
Environmental precautions	Avoid discharge into drains, water courses or onto the ground. Use appropriate containment to avoid environmental contamination.

7. Handling and storage

Precautions for safe handling	Pressurized container: Do not pierce or burn, even after use. Do not use if spray button is missing or defective. Do not spray on a naked flame or any other incandescent material. Do not smoke while using or until sprayed surface is thoroughly dry. Do not cut, weld, solder, drill, grind, or expose containers to heat, flame, sparks, or other sources of ignition. Use caution around energized equipment. The metal container will conduct electricity if it contacts a live source. This may result in injury to the user from electrical shock and/or flash fire. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Observe good industrial hygiene practices. For product usage instructions, see the product label.
--------------------------------------	--

Conditions for safe storage, including any incompatibilities

Level 1 Aerosol.

Contents under pressure. Do not expose to heat or store at temperatures above 120°F/49°C as can may burst. Do not puncture, incinerate or crush. Do not handle or store near an open flame, heat or other sources of ignition. Store in tightly closed original container. Store in a well-ventilated place. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection**Occupational exposure limits****US. OSHA Table Z-3 (29 CFR 1910.1000)**

Components	Type	Value
amorphous fumed silica (CAS 112945-52-5)	TWA	0.8 mg/m3
		20 mppcf

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
amorphous fumed silica (CAS 112945-52-5)	TWA	6 mg/m3

Biological limit values

No biological exposure limits noted for the ingredient(s).

Exposure guidelines

Occupational Exposure Limits are not relevant to the current physical form of the product.

Appropriate engineering controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.

Individual protection measures, such as personal protective equipment**Eye/face protection**

Wear safety glasses with side shields (or goggles).

Skin protection**Hand protection**

Wear protective gloves such as: Nitrile.

Other

Wear suitable protective clothing.

Respiratory protection

If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels.

Thermal hazards

Wear appropriate thermal protective clothing, when necessary.

General hygiene considerations

When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties**Appearance****Physical state**

Solid.

Form

Aerosol. Paste.

Color

Off-white.

Odor

Mild.

Odor threshold

Not available.

pH

Not available.

Melting point/freezing point

> 572 °F (> 300 °C)

Initial boiling point and boiling range

> 392 °F (> 200 °C)

Flash point

> 572 °F (> 300 °C) Cleveland Open Cup

Evaporation rate

Not available.

Flammability (solid, gas)

Not available.

Upper/lower flammability or explosive limits**Flammability limit - lower (%)**

Not available.

Flammability limit - upper (%)	Not available.
Vapor pressure	156152.2 hPa estimated
Vapor density	> 1 (air = 1)
Relative density	0.97
Solubility (water)	Insoluble.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	> 572 °F (> 300 °C)
Decomposition temperature	> 302 °F (> 150 °C)
Viscosity (kinematic)	Not available.
Percent volatile	< 2 %

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Conditions to avoid	Heat, flames and sparks. Avoid temperatures exceeding the decomposition temperature. When exposed to extreme heat or hot surfaces, vapors may decompose to harmful or fatal corrosive gases such as hydrogen fluoride. Contact with incompatible materials.
Incompatible materials	Fluorine. Chlorine.
Hazardous decomposition products	Hydrogen fluoride. Perfluoroisobutylene. Perfluorinated acid fluorides. Formaldehyde. Silicone dioxide. Traces of incompletely burned carbon compounds.

11. Toxicological information

Information on likely routes of exposure

Inhalation	Inhalation of fumes may result in metal fume fever, a flu-like illness with symptoms of metallic taste, fever and chills, aches, chest tightness, and cough.
Skin contact	Prolonged skin contact may cause temporary irritation.
Eye contact	Direct contact with eyes may cause temporary irritation.
Ingestion	Health injuries are not known or expected under normal use.
Symptoms related to the physical, chemical and toxicological characteristics	Direct contact with eyes may cause temporary irritation.

Information on toxicological effects

Acute toxicity

Components	Species	Test Results
amorphous fumed silica (CAS 112945-52-5)		
Acute		
Oral		
LD50	Rat	> 5000 mg/kg
polydimethylsiloxane (CAS 63148-62-9)		
Acute		
Dermal		
LD50	Rabbit	> 2000 mg/kg
Oral		
LD50	Rat	> 10000 mg/kg
polytetrafluoroethylene (CAS 9002-84-0)		
Acute		
Oral		
LD50	Rat	> 10000 mg/kg

* Estimates for product may be based on additional component data not shown.

Skin corrosion/irritation	Prolonged skin contact may cause temporary irritation.
Serious eye damage/eye irritation	Direct contact with eyes may cause temporary irritation.
Respiratory sensitization	Not a respiratory sensitizer.
Skin sensitization	This product is not expected to cause skin sensitization.
Germ cell mutagenicity	No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.
Carcinogenicity	This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA.

IARC Monographs. Overall Evaluation of Carcinogenicity

amorphous fumed silica (CAS 112945-52-5)	3 Not classifiable as to carcinogenicity to humans.
polytetrafluoroethylene (CAS 9002-84-0)	3 Not classifiable as to carcinogenicity to humans.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not regulated.

US. National Toxicology Program (NTP) Report on Carcinogens

Not listed.

Reproductive toxicity	This product is not expected to cause reproductive or developmental effects.
Specific target organ toxicity - single exposure	Not classified.
Specific target organ toxicity - repeated exposure	Not classified.
Aspiration hazard	Not expected to be an aspiration hazard.

12. Ecological information

Ecotoxicity The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

Components	Species	Test Results
amorphous fumed silica (CAS 112945-52-5)		
Aquatic		
<i>Acute</i>		
Fish	LC50	Zebra danio (Danio rerio) > 10000 mg/l, 96 hours
polydimethylsiloxane (CAS 63148-62-9)		
Aquatic		
Fish	LC50	Channel catfish (Ictalurus punctatus) 2.36 - 4.15 mg/l, 96 hours

* Estimates for product may be based on additional component data not shown.

Persistence and degradability	No data is available on the degradability of this product.
Bioaccumulative potential	No data available.
Mobility in soil	No data available.
Other adverse effects	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal of waste from residues / unused products	This product is not a RCRA hazardous waste (See 40 CFR Part 261.20 – 261.33). Empty containers may be recycled. Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Contents under pressure. Do not puncture, incinerate or crush. Dispose in accordance with all applicable regulations.
Hazardous waste code	Not regulated.
Contaminated packaging	Empty containers should be taken to an approved waste handling site for recycling or disposal. Since emptied containers may retain product residue, follow label warnings even after container is emptied.

14. Transport information

DOT	
UN number	UN1950
UN proper shipping name	Aerosols, non-flammable, Limited Quantity
Transport hazard class(es)	
Class	2.2

Subsidiary risk	-
Label(s)	2.2
Packing group	Not applicable.
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
Packaging exceptions	306
Packaging non bulk	None
Packaging bulk	None

IATA

UN number	UN1950
UN proper shipping name	Aerosols, non-flammable, Limited Quantity
Transport hazard class(es)	
Class	2.2
Subsidiary risk	-
Packing group	Not applicable.
ERG Code	2L
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
Other information	
Passenger and cargo aircraft	Allowed with restrictions.
Cargo aircraft only	Allowed with restrictions.

IMDG

UN number	UN1950
UN proper shipping name	AEROSOLS, Limited Quantity
Transport hazard class(es)	
Class	2
Subsidiary risk	-
Packing group	Not applicable.
Environmental hazards	
Marine pollutant	No.
EmS	Not available.
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

15. Regulatory information

US federal regulations This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.
All components are on the U.S. EPA TSCA Inventory List.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

SARA 304 Emergency release notification

Not regulated.

TSCA Chemical Action Plans, Chemicals of Concern

polytetrafluoroethylene (CAS 9002-84-0) Long-Chain Perfluorinated Chemicals (PFCs) Action Plan

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not regulated.

US EPCRA (SARA Title III) Section 313 - Toxic Chemical: Listed substance

Not listed.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

CERCLA Hazardous Substances: Reportable quantity

Not listed.

Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.

Food and Drug Administration (FDA) Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Section 311/312 Hazard categories
Immediate Hazard - No
Delayed Hazard - No
Fire Hazard - No
Pressure Hazard - Yes
Reactivity Hazard - No

SARA 302 Extremely hazardous substance No

US state regulations

US. New Jersey Worker and Community Right-to-Know Act

Not listed.

US. Massachusetts RTK - Substance List

amorphous fumed silica (CAS 112945-52-5)

US. Pennsylvania Worker and Community Right-to-Know Law

amorphous fumed silica (CAS 112945-52-5)

polytetrafluoroethylene (CAS 9002-84-0)

US. Rhode Island RTK

polytetrafluoroethylene (CAS 9002-84-0)

US. California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins.

Volatile organic compounds (VOC) regulations

EPA

VOC content (40 CFR 51.100(s)) < 1 %

Consumer products (40 CFR 59, Subpt. C) Not regulated

State

Consumer products Not regulated

VOC content (CA) < 1 %

VOC content (OTC) < 1 %

International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	Yes
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	No
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	Yes
New Zealand	New Zealand Inventory	Yes
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	Yes
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date 06-25-2015

Revision date 10-16-2017

Material name: Dielectric Grease Compound

No. 02085 (Item# 1003199) Version #: 02 Revision date: 10-16-2017 Issue date: 06-25-2015

SDS US

7 / 8

Prepared by Allison Yoon
Version # 02
Further information Not available.
HMIS® ratings Health: 1
Flammability: 1
Physical hazard: 0
Personal protection: B
NFPA ratings Health: 1
Flammability: 1
Instability: 0

NFPA ratings



Disclaimer

The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC's knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries, Inc..

Revision Information

Product and Company Identification: Product Codes
Composition / Information on Ingredients: Ingredients
Composition/information on ingredients: Component information
Fire-fighting measures: Specific hazards arising from the chemical
Handling and storage: Precautions for safe handling
Physical & Chemical Properties: Multiple Properties
Stability and reactivity: Conditions to avoid
Toxicological information: Respiratory sensitization
Transport Information: Proper Shipping Name/Packing Group
Other information, including date of preparation or last revision: Disclaimer
GHS: Classification