



SNA Terminal Blocks
T&B Catalog Number:

029006107

UPC Number:

66201997013

Status:

Active

Description:

Gray feed through terminal block with 6 mm spacing, 25 amp rated UL current and spring clamp connection

Features

Top entry wire connection

Touch-safe IP20 protection

Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

General

Style	Feed Through
Color	Gray
Mounting	DIN 3
Series	D 4/6.2L
Connection Technology	Spring Clamp
UL Wire Range (AWG)	24-10
Rated IEC Wire Range (Solid) (mm ²)	0.2 - 6
Rated IEC Wire Range (Stranded) (mm ²)	0.2 - 4

Dimension Information

L x W x H (mm)	62.5 x 6 x 38
Spacing (mm)	6
L x W x H (in)	2.46 x .238 x 1.49
Spacing (inches)	.238

Specifications

UL Current (Amps)	25
UL Voltage (VAC)	600
Rated UL Wire Size (AWG)	10

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	750
T&B Sold in UOM	Each
T&B Weight Per UOM	2.13 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com