



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



4RLAG206LM30K90C 4" 11W Led Gimbal 30K 600LM 120V 90cri *Lithonia Lighting - Acuity*

Catalog Number	4RLAG206LM30K90C
Manufacturer	Lithonia Lighting - Acuity
Description	The 4RLA Trim By Juno Utilizes A Led Light Engine Mounted Directly to The Housing For Superior Thermal Management. The Gimbal Trim With Built-In Flange Is Made Of Durable Die Cast Aluminum.
Weight per unit	1.8 (lbs/each)
Product Category	Led Recessed Architectural & S

Features

average life	50,000
Hardware	Yes
Lamp Type	LED - Static
lumens	600 LM
Material	Aluminum
Maximum Operating Temperature	25
media	Yes
Power Source	Plug-In
Shape	Round
Voltage Rating	120
Wattage	10.5

Material, Color, and Finish

Color	White
color rendering index (cri)	90
color temperature	3000
Lens Color	WHITE
Lens Material	Polycarbonate

Dimensions and Weight

Height	3
Length	6
Width	6



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Construction	Retrofit
Description	4" 11W LED GIMBAL 30K 600LM 120V 90CRI
extra long description	LITH 4RLA G2 06LM 30K 90CRI NFL 120
Long Description	The 4RLA Trim by Juno utilizes a LED light engine mounted directly to the housing for superior thermal management. The gimbal trim with built-in flange is made of durable die cast aluminum.
Product Type	Trim

Manufacturer Information

Brand	JUNO
GTIN	00661209652577
Manufacturers Part Number	4RLA G2 06LM 30K 90CRI NFL 120
UPC	661209652577

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
----------------------	--

Trade Size

aperture size	4 in
---------------	------

Packaging

Carton	1
Weight	1.14
Weight Per each	1.75

Uses, Certifications, and Standards

Application	Residential,Retrofit
environmental conditions	Indoor
standard	cUL,ULCA Title 24,ENERGY STAR,JA8