



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 66412CHC Encl 6X6X4 N12 CH Clamp CVR

*Cooper B-Line/Cable Tray*

|                  |   |
|------------------|---|
| Catalog Number   | 66412CHC  |
| Manufacturer     | Cooper B-Line/Cable Tray  |
| Description      | Hinge Cover Enclosure, Steel, Type 12 Continuous Hinge, Wall Mount, Gray, Polyester Powder Coated;Phosphate Undercoat, 4 In Overall Width, 6 In Overall Length, 6 In Overall Height, 5 LB |
| Weight per unit  | 5.0 (lbs/each)  |
| Product Category | Nema Types 12 & 13 Metallic En  |

### Features

dimensions 4.0000 IN X 6.0000 IN X 6.0000 IN

### Material, Color, and Finish

Color Gray

### Dimensions and Weight

Size 6.00 In Width X 4.00 In Depth X 6.00 In Height

### Descriptions

|                        |   |
|------------------------|---|
| Description            | ENCL 6X6X4 N12 CH CLAMP CVR   |
| extra long description | B-LINE 664-12CHC TYPE 12 JIC CONTIN   |
| Features               | Eaton's B-Line series JIC panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments, but are also commonly used as industrial wiring, junction, pull, and termination boxes. |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Eaton          |
| GTIN  | 00782051750409 |
| UPC   | 782051750409   |

### Taxonomies, Classifications, and Categories

|                      |                      |
|----------------------|----------------------|
| Category Description | STEEL JUNCTION BOXES |
| Type                 | JIC panel enclosure  |

### Packaging

|                 |   |
|-----------------|---|
| Carton          | 1 |
| Weight Per each | 5 |

### Uses, Certifications, and Standards

|          |                          |
|----------|--------------------------|
| Mounting | EXTERNAL FEET, WALL      |
| standard | CSA C22.2, NEMA, UL 508A |