



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



690G Combo 2SW 1P 15A 120/277V W/GRD BN

Pass & Seymour/Legrand

Catalog Number	690G
Manufacturer	Pass & Seymour/Legrand
Description	Combination Switch, 1 Pole, 15 A, 120/277 V Ac, Brown, 1.32 (L) X 0.94 (W) X 3.28 (H) In, Toggle Actuator, Wall Mount, 0.22 LB
Weight per unit	0.2162 (lbs/each)
Product Category	Combination Devices

Features

action	(2) SP
actuator	Toggle
amperage rating	15
connection	Side wire
Contact Rating	15amp, 120/277vac
indoor/outdoor	Indoor
Load Rating	15 A @ 120/277 VAC
Load Type	CFL, Fluorescent, Halogen, Xenon, Incandescent, LED, Universal
Material	Thermoplastic
Number of Gangs	1
Number of Switches	2.0
operating cycles	30k.0
Poles	1
Switch Type	Toggle
throw type	Single Throw
Voltage	120 VAC, 277 VAC
Wall Plate Included	NO
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	SATIN
--------	-------

Dimensions and Weight

Size	1.32 L x 0.94 W x 4.06 H
------	--------------------------

Descriptions

Description	COMBO 2SW 1P 15A 120/277V W/GRD BN
extra long description	P&S 690G COMBO 2SW 1P 15A 120/277V
Special Features	Easily accessible break-off for separate or common feed. Side wire #12 and #14 AWG. Two devices fit into the space of one. Grounding combination devices meet NEC Requirements.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007690026
Manufacturers Part Number	690G
UPC	785007690026

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Combination, Tamper-Resistant, Switch

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.2162

Uses, Certifications, and Standards

environmental conditions	Flammability: UL94 V2
Mounting	WALL
Operating Temperature	Maximum continuous +60°C, minimum -30°C
standard	CULUS, UL20