

## FEATURES & SPECIFICATIONS

### INTENDED USE

For use with housings LC6, LI6, L7X, L7XR and LP6.

### CONSTRUCTION

Aluminum white sphere.

Polyester powder coat paint.

40 degree vertical tilt standard.

350 degree horizontal rotation.

White finish has integral flange.

### INSTALLATION

Socket to trim interface.

Retaining clips riveted to top of reflector hold trim inside housing.

Rough-ins with clips retain trims.

### LISTINGS

UL Listed to US and Canadian safety standards.

Damp location listed.

### WARRANTY

1-year limited warranty. Complete warranty terms located at

[www.acuitybrands.com/CustomerResources/Terms\\_and\\_conditions.aspx](http://www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx)

Actual performance may differ as a result of end-user environment and application.

Note: Specifications subject to change without notice.


Catalog Number
Notes
Type

6" Finishing Trim

# 6E1

PREMIUM EYEBALL

Narrow Flange



### Specifications


Height: 6-1/2 (16.5)

Lamp opening: 5-7/8 (14.9)

Diameter: 7-5/8 (19.4)

Trim height when used with Non-IC incandescent rough-in

All dimensions are inches (centimeters) unless otherwise indicated.



### ORDERING INFORMATION

For shortest lead times, configure product using **bolded options**.

Example: 6E1

6E1	
Series	Finish
6E1	<b>(blank)</b> White

<b>Accessories:</b> Order as separate catalog number.	
CRT6	6" goof ring, white

Housing Compatibility: Housing and trim ordered separately.			
Application	Source	Maximum wattage	Housing
IC	Incandescent	75 PAR30	LC6, LI6, L7X, L7XR
		65 BR30	
Non-IC	Incandescent	75 PAR30	LP6
		65 BR30	

# 6E1 6" Premium Eyeball Full Reflector Trim

---

For BR and PAR reflector lamps, see lamp manufacturer's published raw lamp data for photometrics.

## FEATURES & SPECIFICATIONS

### INTENDED USE

For use with housings LC6, LI6, L7X, L7XR and LP6.

### CONSTRUCTION

- Aluminum white sphere.
- Polyester powder coat paint.
- 40 degree vertical tilt standard.
- 350 degree horizontal rotation.
- White finish has integral flange.

### INSTALLATION

- Socket to trim interface.
- Retaining clips riveted to top of reflector hold trim inside housing.
- Rough-ins with clips retain trims.

### LISTINGS

- UL Listed to US and Canadian safety standards.
- Damp location listed.

### WARRANTY


- 1-year limited warranty. Complete warranty terms located at [www.acuitybrands.com/CustomerResources/Terms\\_and\\_conditions.aspx](http://www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx)
- Actual performance may differ as a result of end-user environment and application.
- Note: Specifications subject to change without notice.

Catalog Number
Notes
Type

6" Finishing Trim

# 6E1


**PREMIUM EYEBALL**  
Narrow Flange



### Specifications

- Height: 6-1/2 (16.5)
- Lamp opening: 5-7/8 (14.9)
- Diameter: 7-5/8 (19.4)
- Trim height when used with Non-IC incandescent rough-in

All dimensions are inches (centimeters) unless otherwise indicated.



### ORDERING INFORMATION

For shortest lead times, configure product using **bolded options**.

**Example: 6E1**

6E1	
Series	Finish
<b>6E1</b>	<b>(blank)</b> White

<b>Accessories:</b> Order as separate catalog number.	
CRT6	6" goof ring, white

Housing Compatibility: Housing and trim ordered separately.			
Application	Source	Maximum wattage	Housing
IC	Incandescent	75 PAR30	LC6, LI6, L7X, L7XR
		65 BR30	
Non-IC	Incandescent	75 PAR30	LP6
		65 BR30	

# 6E1 6" Premium Eyeball Full Reflector Trim

---

For BR and PAR reflector lamps, see lamp manufacturer's published raw lamp data for photometrics.