

Heavy-Duty Spec Grade Duplex Receptacle Back and Side-Wire 15A 250V



Features & Benefits

- Heavy-duty, brass strap for added strength and ground conductivity. .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around face to prevent strap from separating from face and back body. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- High strength nylon face. Internal screw-pressure-plate back and side wired to accept #14 and #10 AWG stranded or solid copper or copper-clad conductors.
- Eight back wire holes. Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents. For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
 Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
UPC Number	785007566208	Country Of Origin	Mexico
Number of Receptacles	2	Features	Brass Mounting Strap
Outlet Type	Straight Blade	Application Sector	Commercial

Wall Plate Included	No	Standard	cULus UL498, CSA C22.2 No. 42, FEDSPEC
---------------------	----	----------	--

Warranty Type	1-Year Limited Warranty
---------------	-------------------------

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
------------------	----------	------------------	---------

Product Height US	2.635 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Operating Temperature Min	-40 °C	Dielectric Strength	Withstands 2000V minimum
---------------------------	--------	---------------------	--------------------------

Connection Location	Back and Side	Number of Wires	3
---------------------	---------------	-----------------	---

Operating Temperature Max	60 °C	Amperage	15 A
---------------------------	-------	----------	------

Number of Poles	Double Pole	Wire Size	14 - 10 AWG
-----------------	-------------	-----------	-------------

NEMA Configuration Code	6-15R	Operating Temperature	-40°-60°C
-------------------------	-------	-----------------------	-----------

Wire Connection Type	Screw Terminals	Voltage	250.0 V
----------------------	-----------------	---------	---------

Environmental Conditions	Flammability: UL94 V2
--------------------------	-----------------------

Heavy-Duty Spec Grade Duplex Receptacle Back and Side-Wire 15A 250V



Features & Benefits

Heavy-duty, brass strap for added strength and ground conductivity.

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

High strength nylon face.

Internal screw-pressure-plate back and side wired to accept #14 and #10 AWG stranded or solid copper or copper-clad conductors.

Eight back wire holes.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.

Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
UPC Number	785007566208	Country Of Origin	Mexico
Number of Receptacles	2	Features	Brass Mounting Strap
Outlet Type	Straight Blade	Application Sector	Commercial

Wall Plate Included	No	Standard	cULus UL498, CSA C22.2 No. 42, FEDSPEC
---------------------	----	----------	--

Warranty Type	1-Year Limited Warranty
---------------	-------------------------

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
------------------	----------	------------------	---------

Product Height US	2.635 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Operating Temperature Min	-40 °C	Dielectric Strength	Withstands 2000V minimum
---------------------------	--------	---------------------	--------------------------

Connection Location	Back and Side	Number of Wires	3
---------------------	---------------	-----------------	---

Operating Temperature Max	60 °C	Amperage	15 A
---------------------------	-------	----------	------

Number of Poles	Double Pole	Wire Size	14 - 10 AWG
-----------------	-------------	-----------	-------------

NEMA Configuration Code	6-15R	Operating Temperature	-40°-60°C
-------------------------	-------	-----------------------	-----------

Wire Connection Type	Screw Terminals	Voltage	250.0 V
----------------------	-----------------	---------	---------

Environmental Conditions	Flammability: UL94 V2
--------------------------	-----------------------
