

Project Name

Location

Prepared By



NUVO 65-1083

2FT LED CEILING WRAP

Notes

(review) 08-09-2023 03:31:03

General

Status	Discontinued
Substitute	65-1210
Fixture Type	Ceiling Wrap
Finish	White
Wattage	20W
Lumen Output	1600L
CCT (Kelvin)	3000K
Indoor or Outdoor Fixture	Indoor

Smart Product Info

IOT Enabled	No
Integrated Camera	No

Specifications

Technology	LED
Color Temperature	Warm White
CRI	90+
Voltage	120V-277V
Rated Hours	50000
Operating Temperature	-20C (-4F) to +45C (+113F)
Dimmable	Non-Dimmable
Weight (lb.)	2.38
Material	Steel

Dimensions

Height (in.)	2.63
Width (in.)	5.5
Length (in.)	24.5

Compliance

Safety Listing	cETLus - Listed
Location Rating	Damp
ENERGY STAR	No
DLC Approved	No
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
NEC Compliance	Clothes Closet Certified - Reg: 410.16 (A)(3) and 410.16 (C)(5)
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information

Warranty	5-Years
----------	---------

Project Name

Location

Prepared By



NUVO 65-1083

2FT LED CEILING WRAP

Notes

(review) 08-09-2023 03:31:03

General

Status	Discontinued
Substitute	65-1210
Fixture Type	Ceiling Wrap
Finish	White
Wattage	20W
Lumen Output	1600L
CCT (Kelvin)	3000K
Indoor or Outdoor Fixture	Indoor

Smart Product Info

IOT Enabled	No
Integrated Camera	No

Specifications

Technology	LED
Color Temperature	Warm White
CRI	90+
Voltage	120V-277V
Rated Hours	50000
Operating Temperature	-20C (-4F) to +45C (+113F)
Dimmable	Non-Dimmable
Weight (lb.)	2.38
Material	Steel

Dimensions

Height (in.)	2.63
Width (in.)	5.5
Length (in.)	24.5

Compliance

Safety Listing	cETLus - Listed
Location Rating	Damp
ENERGY STAR	No
DLC Approved	No
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
NEC Compliance	Clothes Closet Certified - Reg: 410.16 (A)(3) and 410.16 (C)(5)
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information

Warranty	5-Years
----------	---------