

LEDVANCE LUMINAIRES

STRING LIGHT

LEDVANCE LUMINAIRE SPECIFICATION DATA

Catalog #	Comments
Project	
Type	
Prepared by	

PERFORMANCE CLASS™



APPLICATION

The LEDVANCE String Lights are ideal for temporary lighting with a versatile and a durable design for indoor construction and job site applications to replace HID and incandescent lights.

BENEFITS & FEATURES

- Strong and durable construction with integrated hook for mounting
- Integrated 100ft power cord on with 10 lamp heads
- Linkable up to 40 lights
- IP65 rating ensures product durability
- Lasts up to 5x longer than HID lamps
- No warm-up time, instant on with full light output and stable color
- High CRI when compared to traditional lighting technologies
- Consumes up to 72% less energy than equivalent HID lamps while delivering same light output
- When linked, these strands utilize parallel wiring to sustain light
- Even if one lamp in the series becomes damaged or fails, all others will remain illuminated
- Replacement for 175W-400W HID applications
- Up to 123 LPW
- 5000K color temperature
- CRI 80+



ELECTRICAL

- 120 Vac 18 AWG cord with straight plug
- Power Factor > 90%
- THD < 20%

OPERATING TEMPERATURE

- -40°F to +104°F
(-40°C to +40°C)

CERTIFICATIONS & LISTINGS

- ETLus listed to UL1598 standards
- RoHS
- FCC
- IP65: wet location

WARRANTY

- Standard 5 year lamp warranty
- NLB Trusted Warranty Program

RATED LIFE

- 50,000 hours (L_{70})

INSTALLATION

- Hang the lamp up with a pre-installed hook
- Lamp operates directly on line voltage, 120Vac
- For linking additional lamps, connect the power cable to the expansion outlet on the lamp.

ORDERING GUIDE

STRLIGHT	130	PLG	8	50	G2
PRODUCT NAME	WATTAGE	VOLTAGE	CRI	COLOR TEMP	GENERATION
STRLIGHT = Temporary String Light	130 = 130 Watts	PLG = 120V straight plug	8 = >80	50 = 5000K	G2 = 2nd generation

ORDERING INFORMATION

ITEM #	ORDERING ABBREVIATION	TOTAL WATTAGE (W)	LAMP WATTAGE* (W)	INPUT VOLTAGE (V)	DIM.	CRI	COLOR TEMP.	CONNECT.	CORD LENGTH (FT)	MAXIMUM LINKABILITY	TOTAL FIXTURE LUMENS (LM)	LPW	AVE. LIFE (HRS)	CASE QTY
66574	LEDSTRLIGHT130PLG850G2	130	13	120V	No	>80	5000K	Plug	100ft (10 lamps)	40 lights (4 sets)	16000	Up to 123	50,000	2


WATTAGE COMPARISON

TRADITIONAL SOURCE	TRADITIONAL SYSTEM WATTAGE	LED SYSTEM WATTAGE	ENERGY SAVINGS
175 W MH	210	130	38%
250 W MH	290	130	55%
250 W HPS	295	130	56%
250 W MH	290	130	55%
250 W HPS	295	130	56%
320 W MH	370	130	65%
400 W HPS	460	130	72%
400 W MH	450	130	71%


PHYSICAL INFORMATION

PRODUCT DESCRIPTION	LENGTH	DIAMETER
LEDSTRLIGHT (per lamp)	2.56" (65mm)	3.94" (100mm)
Cord Length	100ft	

H5-12LV-100FT



H5-12LV-SINGLE HEAD



ADDITIONAL SPECIFICATIONS



- The LEDVANCE Performance Class™ String Light is an integrated LED fixture with no replaceable components
- Not intended for use in dimming applications

PHOTOMETRIC INFORMATION

LUMINOUS INTENSITY DISTRIBUTION / ILLUMINANCE INFORMATION

13W

LUMINOUS INTENSITY DISTRIBUTION DIAGRAM



LEDVANCE LLC
181 Ballardvale Street, Suite 203
Wilmington, MA 01887 USA
Phone: 1-800-LIGHTBULB (1-800-544-4828)
www.ledvanceUS.com

LEDVANCE is a registered trademark.
All other trademarks are those of their respective owners.
Specifications subject to change without notice.



SCAN TO FOLLOW US
ON SOCIAL MEDIA

LEDVANCE LUMINAIRES

STRING LIGHT

LEDVANCE LUMINAIRE SPECIFICATION DATA

Catalog #	Comments
Project	
Type	
Prepared by	

PERFORMANCE CLASS™



APPLICATION

The LEDVANCE String Lights are ideal for temporary lighting with a versatile and a durable design for indoor construction and job site applications to replace HID and incandescent lights.

BENEFITS & FEATURES

- Strong and durable construction with integrated hook for mounting
- Integrated 100ft power cord on with 10 lamp heads
- Linkable up to 40 lights
- IP65 rating ensures product durability
- Lasts up to 5x longer than HID lamps
- No warm-up time, instant on with full light output and stable color
- High CRI when compared to traditional lighting technologies
- Consumes up to 72% less energy than equivalent HID lamps while delivering same light output
- When linked, these strands utilize parallel wiring to sustain light
- Even if one lamp in the series becomes damaged or fails, all others will remain illuminated
- Replacement for 175W-400W HID applications
- Up to 123 LPW
- 5000K color temperature
- CRI 80+



ELECTRICAL

- 120 Vac 18 AWG cord with straight plug
- Power Factor > 90%
- THD < 20%

OPERATING TEMPERATURE

- -40°F to +104°F
(-40°C to +40°C)

CERTIFICATIONS & LISTINGS

- ETLus listed to UL1598 standards
- RoHS
- FCC
- IP65: wet location

WARRANTY

- Standard 5 year lamp warranty
- NLB Trusted Warranty Program

RATED LIFE

- 50,000 hours (L_{70})

INSTALLATION

- Hang the lamp up with a pre-installed hook
- Lamp operates directly on line voltage, 120Vac
- For linking additional lamps, connect the power cable to the expansion outlet on the lamp.

ORDERING GUIDE

STRLIGHT	130	PLG	8	50	G2
PRODUCT NAME	WATTAGE	VOLTAGE	CRI	COLOR TEMP	GENERATION
STRLIGHT = Temporary String Light	130 = 130 Watts	PLG = 120V straight plug	8 = >80	50 = 5000K	G2 = 2nd generation

ORDERING INFORMATION

ITEM #	ORDERING ABBREVIATION	TOTAL WATTAGE (W)	LAMP WATTAGE* (W)	INPUT VOLTAGE (V)	DIM.	CRI	COLOR TEMP.	CONNECT.	CORD LENGTH (FT)	MAXIMUM LINKABILITY	TOTAL FIXTURE LUMENS (LM)	LPW	AVE. LIFE (HRS)	CASE QTY
66574	LEDSTRLIGHT130PLG850G2	130	13	120V	No	>80	5000K	Plug	100ft (10 lamps)	40 lights (4 sets)	16000	Up to 123	50,000	2


WATTAGE COMPARISON

TRADITIONAL SOURCE	TRADITIONAL SYSTEM WATTAGE	LED SYSTEM WATTAGE	ENERGY SAVINGS
175 W MH	210	130	38%
250 W MH	290	130	55%
250 W HPS	295	130	56%
250 W MH	290	130	55%
250 W HPS	295	130	56%
320 W MH	370	130	65%
400 W HPS	460	130	72%
400 W MH	450	130	71%


PHYSICAL INFORMATION

PRODUCT DESCRIPTION	LENGTH	DIAMETER
LEDSTRLIGHT (per lamp)	2.56" (65mm)	3.94" (100mm)
Cord Length	100ft	

H5-12LV-100FT



H5-12LV-SINGLE HEAD



ADDITIONAL SPECIFICATIONS



- The LEDVANCE Performance Class™ String Light is an integrated LED fixture with no replaceable components
- Not intended for use in dimming applications

PHOTOMETRIC INFORMATION

LUMINOUS INTENSITY DISTRIBUTION / ILLUMINANCE INFORMATION

13W

LUMINOUS INTENSITY DISTRIBUTION DIAGRAM



LEDVANCE LLC
181 Ballardvale Street, Suite 203
Wilmington, MA 01887 USA
Phone: 1-800-LIGHTBULB (1-800-544-4828)
www.ledvanceUS.com

LEDVANCE is a registered trademark.
All other trademarks are those of their respective owners.
Specifications subject to change without notice.



SCAN TO FOLLOW US
ON SOCIAL MEDIA