



LEDVANCE LUMINAIRES

DOWNLIGHT RT

DUAL SELECTABLE

LEDVANCE LUMINAIRE SPECIFICATION DATA

Catalog #	Comments
Project	
Type	
Prepared by	

PERFORMANCE CLASS™



CERTIFICATIONS & LISTINGS

- UL listed for US & Canada
- RoHS Compliant
- FCC Compliant
- Wet Location
- Certified airtight as per ASTM E283-04
- IC Rated for insulation contact
- IP44
- Title 24
- TAA Compliant
- ENERGY STAR®

AMBIENT OPERATING TEMPERATURE

- -4°F to 104°F (-20°C to 40°C)
- 32°F to 104°F (0°C to 40°C) with battery

ELECTRICAL

- Input voltage: 120-277V or 120-347V
- Surge Protection: 2.5 kV
- THD: ≤20%
- 16 inches of input wires
- Power Factor: >0.9 @120V, >0.7 @277V or 347V
- Univ. Dimming TRIAC/ELV/0-10V, down to 10%

LENS

Uniform, glare free illumination

HIGH PERFORMANCE

Up to 120 LPW

UNIFORM LIGHT

85° beam angle, source cut-off
60°-80°

CUSTOMIZATION

Optional Field Installed Trim Rings

FLEXIBILITY

Selectable CCT:
2700/3000/3500/4000/5000K
Selectable Output: 3 Step Dimming

QUALITY LIGHT

CRI >90, R9 >50

PIR SENSOR

Integrated occupancy sensing available on select models for enhanced energy savings

DIMMING

100-10% Phase-cut & 0-10V dimming in the same product

EMERGENCY BATTERY BACKUP READY

(Field installable) kit provides up to 2hr illumination

ENERGY EFFICIENT

IC & Air Tight rated

INSTALLATION

Max Ceiling Thickness: 1.97" (50mm)

DESCRIPTION

The PERFORMANCE CLASS DOWNLIGHT RT DUAL SELECTABLE luminaires are offered in 4", 6", 8", and 10" sizes, and provide high-performing light optimized for both new construction and retrofit applications where pin-based compact fluorescent lamps have previously been used. Easily fits in most standard frames and offers care-free universal 120V Phase-cut or 0-10V dimming. Integrated PIR sensor options are available for enhanced occupancy-based lighting control and energy savings. The RT family is emergency battery backup ready and can be customized with optional color finish trims.

APPLICATION

- Commercial applications
- Office
- Public & commercial buildings
- New installations or retrofit of existing installations
- Schools
- Big box retail
- Hotels, shops, hospitality, residential interiors

RATED LIFE

- 100,000 hours (L₇₀) @77°F/25°C

WARRANTY

- 5-Year Limited Warranty
- NLB Trusted Warranty Program



ORDERING GUIDE

RT	XX	SXXXX	XXX	D	9	SC3	WH	XXX
PRODUCT NAME	SIZE	SELECTABLE LUMENS	VOLTAGE	DIMMING	CRI	COLOR TEMP	FINISH	CONTROLS
RT = LED Downlight	4 = 4" 6 = 6" 8 = 8" 10 = 10"	S900 = 500/700/900lm S1000 = 600/800/1000lm S1500 = 900/1200/1500lm S2500 = 1000/1800/2500lm S3500 = 1800/2700/3500lm S4500 = 2800/3500/4500lm	UNV = 120-277V UNH = 120-347V	D = TRIAC / ELV / 0-10V	9 = >90, R9>50	SC3 = Selectable 2700, 3000, 3500, 4000 or 5000K	WH = White	BLANK = No Sensor PIR = Integrated PIR Sensor


ORDERING INFORMATION

ITEM #	ORDERING ABBREVIATION	WATTAGE (W)	INPUT VOLTAGE (V)	CCT (K)	TOTAL LUMENS (LM)	LPW	FINISH	CONTROLS	ENVIRONMENT	MTD/PTD
67685	RT4S1000UNVD9SC3WH	6/8/10	120-277	2700/3000/3500/4000/5000	600/800/1000	100	WH	—	Indoor Wet (IP44)	—
67686	RT6S900UNVD9SC3WH	5/7/9	120-277	2700/3000/3500/4000/5000	500/700/900	100	WH	—	Indoor Wet (IP44)	—
67687	RT6S2500UNVD9SC3WH	10/17/21	120-277	2700/3000/3500/4000/5000	1000/1800/2500	119	WH	—	Indoor Wet (IP44)	—
67688	RT8S1500UNVD9SC3WH	9/12/15	120-277	2700/3000/3500/4000/5000	900/1200/1500	100	WH	—	Indoor Wet (IP44)	—
67689	RT8S3500UNVD9SC3WH	16/24/30	120-277	2700/3000/3500/4000/5000	1800/2700/3500	117	WH	—	Indoor Wet (IP44)	—
67690	RT10S4500UNVD9SC3WH	24/30/37	120-277	2700/3000/3500/4000/5000	2800/3500/4500	122	WH	—	Indoor Wet (IP44)	—
67691	RT4S1000UNHD9SC3WH	6/8/10	120-347	2700/3000/3500/4000/5000	600/800/1000	100	WH	—	Indoor Wet (IP44)	—
67692	RT6S2500UNHD9SC3WH	10/17/21	120-347	2700/3000/3500/4000/5000	1000/1800/2500	119	WH	—	Indoor Wet (IP44)	—
67693	RT8S3500UNHD9SC3WH	16/24/30	120-347	2700/3000/3500/4000/5000	1800/2700/3500	117	WH	—	Indoor Wet (IP44)	—
67694	RT4S1000UNVD9SC3WHPIR	6/8/10	120-277	2700/3000/3500/4000/5000	600/800/1000	100	WH	PIR	Indoor Damp (IP20)	✓
67695	RT6S2500UNVD9SC3WHPIR	10/17/21	120-277	2700/3000/3500/4000/5000	1000/1800/2500	119	WH	PIR	Indoor Damp (IP20)	—
67696	RT8S3500UNVD9SC3WHPIR	16/24/30	120-277	2700/3000/3500/4000/5000	1800/2700/3500	116	WH	PIR	Indoor Damp (IP20)	—
67697	RT10S4500UNVD9SC3WHPIR	24/30/37	120-277	2700/3000/3500/4000/5000	2800/3500/4500	121	WH	PIR	Indoor Damp (IP20)	✓


PHYSICAL INFORMATION







DESCRIPTION	DIAMETER	HEIGHT	WEIGHT
RT4S1000UNVD9SC3WH	5.51in (140mm)	3.72in (94.5mm)	0.86lb (0.39kg)
RT6S900UNVD9SC3WH	7.36in (187mm)	4.08in (103.6mm)	1.08lb (0.49kg)
RT6S2500UNVD9SC3WH	7.36in (187mm)	4.08in (103.6mm)	1.08lb (0.49kg)
RT8S1500UNVD9SC3WH	9.45in (240mm)	4.45in (113mm)	1.37lb (0.62kg)
RT8S3500UNVD9SC3WH	9.45in (240mm)	4.45in (113mm)	1.37lb (0.62kg)
RT10S4500UNVD9SC3WH	11.26in (286mm)	4.45in (113mm)	1.61lb (0.73kg)
RT4S1000UNHD9SC3WH	5.51in (140mm)	3.72in (94.5mm)	0.86lb (0.39kg)
RT6S2500UNHD9SC3WH	7.36in (187mm)	4.08in (103.6mm)	1.08lb (0.49kg)
RT8S3500UNHD9SC3WH	9.45in (240mm)	4.45in (113mm)	1.37lb (0.62kg)
RT4S1000UNVD9SC3WHPIR	5.51 in (140mm)	3.78 in (97.90 mm)	0.73 lb (0.33kg)
RT6S2500UNVD9SC3WHPIR	7.36 in (187mm)	4.19in (106.60mm)	0.89lb (0.40kg)
RT8S3500UNVD9SC3WHPIR	9.45in (240mm)	4.56in (116.05mm)	1.13lb (0.51kg)
RT10S4500UNVD9SC3WHPIR	11.26in (286mm)	4.56in (116.05mm)	1.36lb (0.62kg)

4 INCH



6 INCH



8 INCH**10 INCH****4 INCH PIR****6 INCH PIR****8 INCH PIR****10 INCH PIR**

OPTIONAL ACCESSORIES

ITEM #	ORDERING ABBREVIATION	PRODUCT DESCRIPTION	
TRIM RINGS*			
67426	RT4TRIMSSWH	4" Semi-Specular Trim Ring White Flange	
67427	RT6TRIMSSWH	6" Semi-Specular Trim Ring White Flange	
67428	RT8TRIMSSWH	8" Semi-Specular Trim Ring White Flange	
67429	RT10TRIMSSWH	10" Semi-Specular Trim Ring White Flange	
65710	RT4TRIM5ADKBZ	4" Dark Bronze Trim Ring	
65711	RT4TRIM5ASN	4" Satin Nickel Trim Ring	
65712	RT4TRIM5ABLK	4" Black Trim Ring	
65713	RT6TRIM5ADKBZ	6" Dark Bronze Trim Ring	
65714	RT6TRIM5ASN	6" Satin Nickel Trim Ring	
65715	RT6TRIM5ABLK	6" Black Trim Ring	
65716	RT8TRIM5ADKBZ	8" Dark Bronze Trim Ring	
65717	RT8TRIM5ASN	8" Satin Nickel Trim Ring	
65718	RT8TRIM5ABLK	8" Black Trim Ring	
65719	RT10TRIM5ADKBZ	10" Dark Bronze Trim Ring	
65720	RT10TRIM5ASN	10" Satin Nickel Trim Ring	
65721	RT10TRIM5ABLK	10" Black Trim Ring	

*These finish trims will NOT work with PIR versions

OPTIONAL ACCESSORIES (CONTINUED)

ITEM #	ORDERING ABBREVIATION	PRODUCT DESCRIPTION
--------	-----------------------	---------------------

TRIM RING EXTENDERS

62788	RT685ATRIMEXT	6-8" Trim Ring Extender (Goof Ring) for 8" cans
62789	RT8105ATRIMEXT	8-10" Trim Ring Extender (Goof Ring) for 10" cans
62790	RT8125ATRIMEXT	8-12" Trim Ring Extender (Goof Ring) for 12" cans
62791	RT10125ATRIMEXT	10-12" Trim Ring Extender (Goof Ring) for 12" cans



EMERGENCY BATTERY BACKUP

62367	EMBB2A8WUNVDC	100-277V 2A 8W Emergency Battery Backup 90min.
62368	EMBB2A8WUNHDC	100-347V 2A 8W Emergency Battery Backup 90min.




RECESSED ROUGH-IN FRAME

63883	LEDRT4FRAME	4" Recessed rough-in frame with Junction Box (RT4)
71708	LEDRT6HOFAME	6" Recessed rough-in frame with Junction Box (RT6)
71709	LEDRT8FRAME	8" Recessed rough-in frame with Junction Box (RT8/10)




TRIM RING EXTENDER DIMENSIONS

DESCRIPTION	OUTER DIAMETER (A)	INNER DIAMETER (B)	THICKNESS (C)
62788	9.44in (240.00mm)	5.44 (138.73mm)	0.375in (9.50mm)
62789	11.44in (290.80mm)	7.125 (180.75mm)	0.438in (10.50mm)
62790	13.44in (341.60mm)	7.125 (180.75mm)	0.438in (10.80mm)
62366	13.44in (341.60mm)	8.125 (205.83mm)	0.438in (10.80mm)




RECESSED ROUGH-IN FRAME DIMENSIONS


63883



71708



71709




EMBB COMPATIBILITY


ITEM #	ORDERING ABBREVIATION	EMBB ITEM #	EMBB DESCRIPTION	EMBB WATTAGE (W)†	EM LUMENS (LM)*
67685	RT4S1000UNVD9SC3WH	62367 / 62368	EMBB2A8WUNVDC / EMBB2A8WUNHDC	10	960*
67686	RT6S900UNVD9SC3WH	62367 / 62368	EMBB2A8WUNVDC / EMBB2A8WUNHDC	9	870**
67687	RT6S2500UNVD9SC3WH	62367 / 62368	EMBB2A8WUNVDC / EMBB2A8WUNHDC	16	1940
67688	RT8S1500UNVD9SC3WH	62367 / 62368	EMBB2A8WUNVDC / EMBB2A8WUNHDC	14	1350
67689	RT8S3500UNVD9SC3WH	62367 / 62368	EMBB2A8WUNVDC / EMBB2A8WUNHDC	16	1850
67690	RT10S4500UNVD9SC3WH	62367 / 62368	EMBB2A8WUNVDC / EMBB2A8WUNHDC	16	1940
67691	RT4S1000UNHD9SC3WH	62368	EMBB2A8WUNHDC	10	960*
67692	RT6S2500UNHD9SC3WH	62368	EMBB2A8WUNHDC	16	1940
67693	RT8S3500UNHD9SC3WH	62368	EMBB2A8WUNHDC	16	1850
67694	RT4S1000UNVD9SC3WHPIR	62367 / 62368	EMBB2A8WUNVDC / EMBB2A8WUNHDC	10	960*
67695	RT6S2500UNVD9SC3WHPIR	62367 / 62368	EMBB2A8WUNVDC / EMBB2A8WUNHDC	16	1940
67697	RT10S4500UNVD9SC3WHPIR	62367 / 62368	EMBB2A8WUNVDC / EMBB2A8WUNHDC	16	1940
67696	RT8S3500UNVD9SC3WHPIR	62367 / 62368	EMBB2A8WUNVDC / EMBB2A8WUNHDC	16	1850

† At the highest wattage. *Not compatible with 6W (lowest) setting. **Not compatible with 5W (lowest) setting

EMBB WIRING DIAGRAM



EMBB PHYSICAL INFORMATION



DIMMER COMPATIBILITY

MAKE	DIMMER TYPE	MODEL
PHASECUT DIMMERS		
Leviton SureSlide	L	6674
Lutron Maestro C-L	L	MACL-153M
Lutron Diva	L	DVCL-153P
Lutron Caseta*	L	PD-6WCL*
Lutron Diva	T	DVELV-300P
Lutron Maestro	T	MAELV-600
0-10V DIMMERS		
Leviton	0-10V	DS710
Leviton	0-10V	IP710
Lutron	0-10V	NTSTV-DV
Lutron	0-10V	DVTV
Lutron	0-10V	DVSTV
Legrand	0-10V	H4FBL3PW

*Not compatible with 67685 & 67686

PIR DETECTION RANGE

INSTALLATION HEIGHT	RADIUS/AREA
2.8m	3m
4.5m	2.5m

INSTALLATION

- Recessed ceiling mount
- Optional frame-in kits for new construction applications
- Factory settings: 2700K, Highest Lumens, PIR 30S, Auto



INSTALLATION
GUIDE


WATTAGE COMPARISON

TRADITIONAL SOURCE	TRADITIONAL LAMP ORIENTATION	TRADITIONAL SYSTEM WATTAGE	LED SYSTEM WATTAGE	ENERGY SAVINGS
4" Twin Tube	13W Vertical	15W	6W	60%
4" Twin Tube	18W Vertical	20W	7W	65%
4" Twin Tube	26W Vertical	28W	7W	71%
4" Triple Tube	18W Vertical	20W	9W	55%
4" Triple Tube	26W Vertical	28W	10W	64%
6" Triple Tube	18W Vertical	20W	7W	65%
6" Triple Tube	26W Vertical	28W	9W	68%
6" Triple Tube	32W Vertical	34W	10W	71%
6" Triple Tube	42W Vertical	48W	17W	65%
6" Double Tube	13W Vertical	15W	5W	67%
6" Double Tube	18W Vertical	20W	7W	65%
6" Double Tube	26W Vertical	28W	9W	68%
6" Double Tube	13W Horizontal	15W	5W	67%
6" Double Tube	18W Horizontal	20W	7W	65%

TRADITIONAL SOURCE	TRADITIONAL LAMP ORIENTATION	TRADITIONAL SYSTEM WATTAGE	LED SYSTEM WATTAGE	ENERGY SAVINGS
6" Double Tube	26W Horizontal	28W	9W	68%
6" Double Tube	2x13W Horizontal	28W	5W	75%
8" Triple Tube	26W Vertical	28W	12W	57%
8" Triple Tube	32W Vertical	34W	9W	74%
8" Triple Tube	42W Vertical	48W	15W	69%
8" Triple Tube	2x26W Horizontal	54W	16W	70%
8" Triple Tube	2x32W Horizontal	68W	24W	65%
8" Triple Tube	42W Horizontal	48W	15W	69%
8" Triple Tube	2x42W Horizontal	100W	30W	70%
8" Double Tube	2x13W Horizontal	28W	9W	68%
8" Double Tube	2x18W Horizontal	38W	12W	68%
8" Double Tube	2x26W Horizontal	54W	16W	70%


PHOTOMETRIC INFORMATION

RT4S1000UNVD9SC3WH (2700K)




Illuminance at a Distance		Beam Width	
Center Beam Fc	Beam Width	Zone	Lumens % Luminaire
1.7R	217 fc	3.0 ft	3.0 ft
2.3R	57.6 fc	5.8 ft	5.8 ft
3.3R	25.1 fc	8.8 ft	8.8 ft
5.0R	14 fc	11.8 ft	11.8 ft
6.7R	9.11 fc	14.6 ft	14.6 ft
8.3R	6.27 fc	17.6 ft	17.6 ft
10.0R			
■ Vert. Spread: 82.7°		■ Horiz. Spread: 62.7°	

RT6S900UNVD9SC3WH (5000K)




Illuminance at a Distance		Beam Width	
Center Beam Fc	Beam Width	Zone	Lumens % Luminaire
1.7R	175 fc	3.3 ft	3.3 ft
2.3R	46.4 fc	6.4 ft	6.4 ft
3.3R	20.2 fc	9.7 ft	9.7 ft
5.0R	11.3 fc	13.0 ft	13.0 ft
6.7R	7.33 fc	16.1 ft	16.1 ft
8.3R	5.05 fc	19.4 ft	19.4 ft
10.0R			
■ Vert. Spread: 88.1°		■ Horiz. Spread: 88.2°	

RT6S2500UNVD9SC3WH (2700K)




Illuminance at a Distance		Beam Width	
Center Beam Fc	Beam Width	Zone	Lumens % Luminaire
1.7R	447 fc	3.2 ft	3.2 ft
2.3R	119 fc	6.3 ft	6.3 ft
3.3R	51.7 fc	9.5 ft	9.5 ft
5.0R	28.8 fc	12.8 ft	12.7 ft
6.7R	18.8 fc	15.8 ft	15.8 ft
8.3R	12.9 fc	19.0 ft	19.0 ft
10.0R			
■ Vert. Spread: 87.2°		■ Horiz. Spread: 87.1°	

RT8S1500UNVD9SC3WH (5000K)




Illuminance at a Distance		Beam Width	
Center Beam Fc	Beam Width	Zone	Lumens % Luminaire
1.7R	264 fc	3.5 ft	3.5 ft
2.3R	70 fc	6.8 ft	6.8 ft
3.3R	30.5 fc	10.4 ft	10.4 ft
5.0R	17 fc	13.9 ft	13.9 ft
6.7R	11.1 fc	17.2 ft	17.2 ft
8.3R	7.62 fc	20.7 ft	20.7 ft
10.0R			
■ Vert. Spread: 92.0°		■ Horiz. Spread: 92.1°	

RT8S3500UNVD9SC3WH (2700K)



Illuminance at a Distance		Beam Width	
Center Beam Fc	Beam Width	Zone	Lumens % Luminaire
1.7R	617 fc	3.4 ft	3.4 ft
2.3R	164 fc	6.6 ft	6.6 ft
3.3R	71.3 fc	10.1 ft	10.0 ft
5.0R	39.7 fc	13.5 ft	13.4 ft
6.7R	25.9 fc	16.7 ft	16.7 ft
8.3R	17.8 fc	20.1 ft	20.1 ft
10.0R			
■ Vert. Spread: 90.3°		■ Horiz. Spread: 90.2°	



RT10S4500UNVD9SC3WH (2700K)



Illuminance at a Distance		Beam Width	
Center Beam Fc	Beam Width	Zone	Lumens % Luminaire
1.7R	728 fc	3.6 ft	3.6 ft
2.3R	193 fc	7.0 ft	7.0 ft
3.3R	84.1 fc	10.6 ft	10.6 ft
5.0R	46.6 fc	14.2 ft	14.2 ft
6.7R	30.5 fc	17.6 ft	17.6 ft
8.3R	21 fc	21.2 ft	21.2 ft
10.0R			
■ Vert. Spread: 93.4°		■ Horiz. Spread: 93.4°	



PHOTOMETRIC INFORMATION (CONTINUED)

RT4S1000UNHD9SC3WH (2700K)





Zone	Lumens	% Luminaire
0-30	439.4	42.1%
0-40	675.4	64.8%
0-60	953.4	91.4%
60-90	89.3	8.6%
0-90	1,042.7	100%

RT6S2500UNHD9SC3WH (5000K)





Zone	Lumens	% Luminaire
0-30	902.2	40%
0-40	1,407.5	62.4%
0-60	2,082.1	92.3%
60-90	174.5	7.7%
0-90	2,256.6	100%

RT8S3500UNHD9SC3WH (2700K)





Zone	Lumens	% Luminaire
0-30	1,279.2	38.2%
0-40	2,013.5	60.1%
0-60	3,097.3	92.4%
60-90	254.7	7.6%
0-90	3,352.0	100%

RT4S1000UNVD9SC3WHP PIR (2700K)





Zone	Lumens	% Luminaire
0-30	1,585.7	35.1%
0-40	2,534.9	56.1%
0-60	4,082.3	90.3%
60-90	438.8	9.7%
70-100	131.7	2.9%
90-120	0.1	0%
0-90	4,521.1	100%
90-180	0.3	0%
0-180	4,521.4	100%

RT6S2500UNVD9SC3WHP PIR (2700K)





Zone	Lumens	% Luminaire
0-30	420.1	39.9%
0-40	644.9	61.2%
0-60	940.4	89.3%
60-90	113.0	10.7%
70-100	42.9	4.1%
90-120	0.0	0%
0-90	1,053.4	100%
90-180	0.0	0%
0-180	1,053.4	100%

RT8S3500UNVD9SC3WHP PIR (2700K)



Zone	Lumens	% Luminaire
0-30	974.7	38.6%
0-40	1,527.5	60.5%
0-60	2,288.3	90.6%
60-90	236.3	9.4%
70-100	89.0	3.5%
90-120	0.0	0%
0-90	2,524.6	100%
90-180	0.0	0%
0-180	2,524.6	100%


RT10S4500UNVD9SC3WH PIR (2700K)




Zone	Lumens	% Luminaire
0-30	1,585.7	35.1%
0-40	2,534.9	56.1%
0-60	4,082.3	90.3%
60-90	438.8	9.7%
70-100	131.7	2.9%
90-120	0.1	0%
0-90	4,521.1	100%
90-180	0.3	0%
0-180	4,521.4	100%


HOLE CUT TEMPLATES

RT4 HOLE CUT TEMPLATE




RT6 HOLE CUT TEMPLATE





HOLE CUT TEMPLATES

RT10 Hole Cut Template



LEDVANCE NORTH AMERICAN HEADQUARTERS

LEDVANCE LLC.
181 Ballardvale Street, Suite 203
Wilmington, MA 01887
Phone: +1 978 753 5000

LEDVANCE CANADIAN HEADQUARTERS

LEDVANCE LTD./LTE.
5450 Explorer Drive, Suite 100
Mississauga, Ontario L4W 5N1
Phone: +1 905 361 93 33

LEDVANCE.COM/EN-US

LEDVANCE is a registered trademark.
All other trademarks are those of their respective owners.
Specifications subject to change without notice.

© 2026 LEDVANCE LLC

LEDVANCE LUMINAIRES

DOWNLIGHT RT

DUAL SELECTABLE

LEDVANCE LUMINAIRE SPECIFICATION DATA

Catalog #	Comments
Project	
Type	
Prepared by	

PERFORMANCE CLASS™



CERTIFICATIONS & LISTINGS

- UL listed for US & Canada
- RoHS Compliant
- FCC Compliant
- Wet Location
- Certified airtight as per ASTM E283-04
- IC Rated for insulation contact
- IP44
- Title 24
- TAA Compliant
- ENERGY STAR®

AMBIENT OPERATING TEMPERATURE

- -4°F to 104°F (-20°C to 40°C)
- 32°F to 104°F (0°C to 40°C) with battery

ELECTRICAL

- Input voltage: 120-277V or 120-347V
- Surge Protection: 2.5 kV
- THD: ≤20%
- 16 inches of input wires
- Power Factor: >0.9 @120V, >0.7 @277V or 347V
- Univ. Dimming TRIAC/ELV/0-10V, down to 10%

LENS

Uniform, glare free illumination

HIGH PERFORMANCE

Up to 120 LPW

UNIFORM LIGHT

85° beam angle, source cut-off
60°-80°

CUSTOMIZATION

Optional Field Installed Trim Rings

FLEXIBILITY

Selectable CCT:
2700/3000/3500/4000/5000K
Selectable Output: 3 Step Dimming

QUALITY LIGHT

CRI >90, R9 >50

PIR SENSOR

Integrated occupancy sensing available on select models for enhanced energy savings

DIMMING

100-10% Phase-cut & 0-10V dimming in the same product

EMERGENCY BATTERY BACKUP READY

(Field installable) kit provides up to 2hr illumination

ENERGY EFFICIENT

IC & Air Tight rated

INSTALLATION

Max Ceiling Thickness: 1.97" (50mm)

DESCRIPTION

The PERFORMANCE CLASS DOWNLIGHT RT DUAL SELECTABLE luminaires are offered in 4", 6", 8", and 10" sizes, and provide high-performing light optimized for both new construction and retrofit applications where pin-based compact fluorescent lamps have previously been used. Easily fits in most standard frames and offers care-free universal 120V Phase-cut or 0-10V dimming. Integrated PIR sensor options are available for enhanced occupancy-based lighting control and energy savings. The RT family is emergency battery backup ready and can be customized with optional color finish trims.

APPLICATION

- Commercial applications
- Office
- Public & commercial buildings
- New installations or retrofit of existing installations
- Schools
- Big box retail
- Hotels, shops, hospitality, residential interiors

RATED LIFE

- 100,000 hours (L₇₀) @77°F/25°C

WARRANTY

- 5-Year Limited Warranty
- NLB Trusted Warranty Program



ORDERING GUIDE

RT	XX	SXXXX	XXX	D	9	SC3	WH	XXX
PRODUCT NAME	SIZE	SELECTABLE LUMENS	VOLTAGE	DIMMING	CRI	COLOR TEMP	FINISH	CONTROLS
RT = LED Downlight	4 = 4" 6 = 6" 8 = 8" 10 = 10"	S900 = 500/700/900lm S1000 = 600/800/1000lm S1500 = 900/1200/1500lm S2500 = 1000/1800/2500lm S3500 = 1800/2700/3500lm S4500 = 2800/3500/4500lm	UNV = 120-277V UNH = 120-347V	D = TRIAC / ELV / 0-10V	9 = >90, R9>50	SC3 = Selectable 2700, 3000, 3500, 4000 or 5000K	WH = White	BLANK = No Sensor PIR = Integrated PIR Sensor


ORDERING INFORMATION

ITEM #	ORDERING ABBREVIATION	WATTAGE (W)	INPUT VOLTAGE (V)	CCT (K)	TOTAL LUMENS (LM)	LPW	FINISH	CONTROLS	ENVIRONMENT	MTD/PTD
67685	RT4S1000UNVD9SC3WH	6/8/10	120-277	2700/3000/3500/4000/5000	600/800/1000	100	WH	—	Indoor Wet (IP44)	—
67686	RT6S900UNVD9SC3WH	5/7/9	120-277	2700/3000/3500/4000/5000	500/700/900	100	WH	—	Indoor Wet (IP44)	—
67687	RT6S2500UNVD9SC3WH	10/17/21	120-277	2700/3000/3500/4000/5000	1000/1800/2500	119	WH	—	Indoor Wet (IP44)	—
67688	RT8S1500UNVD9SC3WH	9/12/15	120-277	2700/3000/3500/4000/5000	900/1200/1500	100	WH	—	Indoor Wet (IP44)	—
67689	RT8S3500UNVD9SC3WH	16/24/30	120-277	2700/3000/3500/4000/5000	1800/2700/3500	117	WH	—	Indoor Wet (IP44)	—
67690	RT10S4500UNVD9SC3WH	24/30/37	120-277	2700/3000/3500/4000/5000	2800/3500/4500	122	WH	—	Indoor Wet (IP44)	—
67691	RT4S1000UNHD9SC3WH	6/8/10	120-347	2700/3000/3500/4000/5000	600/800/1000	100	WH	—	Indoor Wet (IP44)	—
67692	RT6S2500UNHD9SC3WH	10/17/21	120-347	2700/3000/3500/4000/5000	1000/1800/2500	119	WH	—	Indoor Wet (IP44)	—
67693	RT8S3500UNHD9SC3WH	16/24/30	120-347	2700/3000/3500/4000/5000	1800/2700/3500	117	WH	—	Indoor Wet (IP44)	—
67694	RT4S1000UNVD9SC3WHPIR	6/8/10	120-277	2700/3000/3500/4000/5000	600/800/1000	100	WH	PIR	Indoor Damp (IP20)	✓
67695	RT6S2500UNVD9SC3WHPIR	10/17/21	120-277	2700/3000/3500/4000/5000	1000/1800/2500	119	WH	PIR	Indoor Damp (IP20)	—
67696	RT8S3500UNVD9SC3WHPIR	16/24/30	120-277	2700/3000/3500/4000/5000	1800/2700/3500	116	WH	PIR	Indoor Damp (IP20)	—
67697	RT10S4500UNVD9SC3WHPIR	24/30/37	120-277	2700/3000/3500/4000/5000	2800/3500/4500	121	WH	PIR	Indoor Damp (IP20)	✓


PHYSICAL INFORMATION







DESCRIPTION	DIAMETER	HEIGHT	WEIGHT
RT4S1000UNVD9SC3WH	5.51in (140mm)	3.72in (94.5mm)	0.86lb (0.39kg)
RT6S900UNVD9SC3WH	7.36in (187mm)	4.08in (103.6mm)	1.08lb (0.49kg)
RT6S2500UNVD9SC3WH	7.36in (187mm)	4.08in (103.6mm)	1.08lb (0.49kg)
RT8S1500UNVD9SC3WH	9.45in (240mm)	4.45in (113mm)	1.37lb (0.62kg)
RT8S3500UNVD9SC3WH	9.45in (240mm)	4.45in (113mm)	1.37lb (0.62kg)
RT10S4500UNVD9SC3WH	11.26in (286mm)	4.45in (113mm)	1.61lb (0.73kg)
RT4S1000UNHD9SC3WH	5.51in (140mm)	3.72in (94.5mm)	0.86lb (0.39kg)
RT6S2500UNHD9SC3WH	7.36in (187mm)	4.08in (103.6mm)	1.08lb (0.49kg)
RT8S3500UNHD9SC3WH	9.45in (240mm)	4.45in (113mm)	1.37lb (0.62kg)
RT4S1000UNVD9SC3WHPIR	5.51 in (140mm)	3.78 in (97.90 mm)	0.73 lb (0.33kg)
RT6S2500UNVD9SC3WHPIR	7.36 in (187mm)	4.19in (106.60mm)	0.89lb (0.40kg)
RT8S3500UNVD9SC3WHPIR	9.45in (240mm)	4.56in (116.05mm)	1.13lb (0.51kg)
RT10S4500UNVD9SC3WHPIR	11.26in (286mm)	4.56in (116.05mm)	1.36lb (0.62kg)

4 INCH



6 INCH



8 INCH**10 INCH****4 INCH PIR****6 INCH PIR****8 INCH PIR****10 INCH PIR**

OPTIONAL ACCESSORIES

ITEM #	ORDERING ABBREVIATION	PRODUCT DESCRIPTION	
TRIM RINGS*			
67426	RT4TRIMSSWH	4" Semi-Specular Trim Ring White Flange	
67427	RT6TRIMSSWH	6" Semi-Specular Trim Ring White Flange	
67428	RT8TRIMSSWH	8" Semi-Specular Trim Ring White Flange	
67429	RT10TRIMSSWH	10" Semi-Specular Trim Ring White Flange	
65710	RT4TRIM5ADKBZ	4" Dark Bronze Trim Ring	
65711	RT4TRIM5ASN	4" Satin Nickel Trim Ring	
65712	RT4TRIM5ABLK	4" Black Trim Ring	
65713	RT6TRIM5ADKBZ	6" Dark Bronze Trim Ring	
65714	RT6TRIM5ASN	6" Satin Nickel Trim Ring	
65715	RT6TRIM5ABLK	6" Black Trim Ring	
65716	RT8TRIM5ADKBZ	8" Dark Bronze Trim Ring	
65717	RT8TRIM5ASN	8" Satin Nickel Trim Ring	
65718	RT8TRIM5ABLK	8" Black Trim Ring	
65719	RT10TRIM5ADKBZ	10" Dark Bronze Trim Ring	
65720	RT10TRIM5ASN	10" Satin Nickel Trim Ring	
65721	RT10TRIM5ABLK	10" Black Trim Ring	

*These finish trims will NOT work with PIR versions

OPTIONAL ACCESSORIES (CONTINUED)

ITEM #	ORDERING ABBREVIATION	PRODUCT DESCRIPTION
TRIM RING EXTENDERS		

62788	RT685ATRIMEXT	6-8" Trim Ring Extender (Goof Ring) for 8" cans
62789	RT8105ATRIMEXT	8-10" Trim Ring Extender (Goof Ring) for 10" cans
62790	RT8125ATRIMEXT	8-12" Trim Ring Extender (Goof Ring) for 12" cans
62791	RT10125ATRIMEXT	10-12" Trim Ring Extender (Goof Ring) for 12" cans



EMERGENCY BATTERY BACKUP		
--------------------------	--	--

62367	EMBB2A8WUNVDC	100-277V 2A 8W Emergency Battery Backup 90min.
62368	EMBB2A8WUNHDC	100-347V 2A 8W Emergency Battery Backup 90min.




RECESSED ROUGH-IN FRAME		
-------------------------	--	--

63883	LEDRT4FRAME	4" Recessed rough-in frame with Junction Box (RT4)
71708	LEDRT6HOFAME	6" Recessed rough-in frame with Junction Box (RT6)
71709	LEDRT8FRAME	8" Recessed rough-in frame with Junction Box (RT8/10)




TRIM RING EXTENDER DIMENSIONS

DESCRIPTION	OUTER DIAMETER (A)	INNER DIAMETER (B)	THICKNESS (C)
62788	9.44in (240.00mm)	5.44 (138.73mm)	0.375in (9.50mm)
62789	11.44in (290.80mm)	7.125 (180.75mm)	0.438in (10.50mm)
62790	13.44in (341.60mm)	7.125 (180.75mm)	0.438in (10.80mm)
62366	13.44in (341.60mm)	8.125 (205.83mm)	0.438in (10.80mm)




RECESSED ROUGH-IN FRAME DIMENSIONS


63883



71708



71709




EMBB COMPATIBILITY

ITEM #	ORDERING ABBREVIATION	EMBB ITEM #	EMBB DESCRIPTION	EMBB WATTAGE (W)†	EM LUMENS (LM)*
67685	RT4S1000UNVD9SC3WH	62367 / 62368	EMBB2A8WUNVDC / EMBB2A8WUNHDC	10	960*
67686	RT6S900UNVD9SC3WH	62367 / 62368	EMBB2A8WUNVDC / EMBB2A8WUNHDC	9	870**
67687	RT6S2500UNVD9SC3WH	62367 / 62368	EMBB2A8WUNVDC / EMBB2A8WUNHDC	16	1940
67688	RT8S1500UNVD9SC3WH	62367 / 62368	EMBB2A8WUNVDC / EMBB2A8WUNHDC	14	1350
67689	RT8S3500UNVD9SC3WH	62367 / 62368	EMBB2A8WUNVDC / EMBB2A8WUNHDC	16	1850
67690	RT10S4500UNVD9SC3WH	62367 / 62368	EMBB2A8WUNVDC / EMBB2A8WUNHDC	16	1940
67691	RT4S1000UNHD9SC3WH	62368	EMBB2A8WUNHDC	10	960*
67692	RT6S2500UNHD9SC3WH	62368	EMBB2A8WUNHDC	16	1940
67693	RT8S3500UNHD9SC3WH	62368	EMBB2A8WUNHDC	16	1850
67694	RT4S1000UNVD9SC3WHPIR	62367 / 62368	EMBB2A8WUNVDC / EMBB2A8WUNHDC	10	960*
67695	RT6S2500UNVD9SC3WHPIR	62367 / 62368	EMBB2A8WUNVDC / EMBB2A8WUNHDC	16	1940
67697	RT10S4500UNVD9SC3WHPIR	62367 / 62368	EMBB2A8WUNVDC / EMBB2A8WUNHDC	16	1940
67696	RT8S3500UNVD9SC3WHPIR	62367 / 62368	EMBB2A8WUNVDC / EMBB2A8WUNHDC	16	1850


† At the highest wattage. *Not compatible with 6W (lowest) setting. **Not compatible with 5W (lowest) setting

EMBB WIRING DIAGRAM

Wiring diagram



EMBB PHYSICAL INFORMATION



DIMMER COMPATIBILITY

MAKE	DIMMER TYPE	MODEL
PHASECUT DIMMERS		
Leviton SureSlide	L	6674
Lutron Maestro C-L	L	MACL-153M
Lutron Diva	L	DVCL-153P
Lutron Caseta*	L	PD-6WCL*
Lutron Diva	T	DVELV-300P
Lutron Maestro	T	MAELV-600
0-10V DIMMERS		
Leviton	0-10V	DS710
Leviton	0-10V	IP710
Lutron	0-10V	NTSTV-DV
Lutron	0-10V	DVTV
Lutron	0-10V	DVSTV
Legrand	0-10V	H4FBL3PW

*Not compatible with 67685 & 67686

PIR DETECTION RANGE

INSTALLATION HEIGHT	RADIUS/AREA
2.8m	3m
4.5m	2.5m

INSTALLATION

- Recessed ceiling mount
- Optional frame-in kits for new construction applications
- Factory settings: 2700K, Highest Lumens, PIR 30S, Auto



INSTALLATION
GUIDE


WATTAGE COMPARISON

TRADITIONAL SOURCE	TRADITIONAL LAMP ORIENTATION	TRADITIONAL SYSTEM WATTAGE	LED SYSTEM WATTAGE	ENERGY SAVINGS
4" Twin Tube	13W Vertical	15W	6W	60%
4" Twin Tube	18W Vertical	20W	7W	65%
4" Twin Tube	26W Vertical	28W	7W	71%
4" Triple Tube	18W Vertical	20W	9W	55%
4" Triple Tube	26W Vertical	28W	10W	64%
6" Triple Tube	18W Vertical	20W	7W	65%
6" Triple Tube	26W Vertical	28W	9W	68%
6" Triple Tube	32W Vertical	34W	10W	71%
6" Triple Tube	42W Vertical	48W	17W	65%
6" Double Tube	13W Vertical	15W	5W	67%
6" Double Tube	18W Vertical	20W	7W	65%
6" Double Tube	26W Vertical	28W	9W	68%
6" Double Tube	13W Horizontal	15W	5W	67%
6" Double Tube	18W Horizontal	20W	7W	65%

TRADITIONAL SOURCE	TRADITIONAL LAMP ORIENTATION	TRADITIONAL SYSTEM WATTAGE	LED SYSTEM WATTAGE	ENERGY SAVINGS
6" Double Tube	26W Horizontal	28W	9W	68%
6" Double Tube	2x13W Horizontal	28W	5W	75%
8" Triple Tube	26W Vertical	28W	12W	57%
8" Triple Tube	32W Vertical	34W	9W	74%
8" Triple Tube	42W Vertical	48W	15W	69%
8" Triple Tube	2x26W Horizontal	54W	16W	70%
8" Triple Tube	2x32W Horizontal	68W	24W	65%
8" Triple Tube	42W Horizontal	48W	15W	69%
8" Triple Tube	2x42W Horizontal	100W	30W	70%
8" Double Tube	2x13W Horizontal	28W	9W	68%
8" Double Tube	2x18W Horizontal	38W	12W	68%
8" Double Tube	2x26W Horizontal	54W	16W	70%


PHOTOMETRIC INFORMATION

RT4S1000UNVD9SC3WH (2700K)




Illuminance at a Distance		Beam Width	
Center Beam fc	Beam Width	Zone	Lumens % Luminaire
1.7R	217 fc	3.0 ft	3.0 ft
2.3R	57.6 fc	5.8 ft	5.8 ft
3.3R	25.1 fc	8.8 ft	8.8 ft
5.0R	14 fc	11.8 ft	11.8 ft
6.7R	9.11 fc	14.6 ft	14.6 ft
8.3R	6.27 fc	17.6 ft	17.6 ft
10.0R			
■ Vert. Spread: 82.7°		■ Horiz. Spread: 62.7°	

RT6S900UNVD9SC3WH (5000K)




Illuminance at a Distance		Beam Width	
Center Beam fc	Beam Width	Zone	Lumens % Luminaire
1.7R	175 fc	3.3 ft	3.3 ft
2.3R	46.4 fc	6.4 ft	6.4 ft
3.3R	20.2 fc	9.7 ft	9.7 ft
5.0R	11.3 fc	13.0 ft	13.0 ft
6.7R	7.33 fc	16.1 ft	16.1 ft
8.3R	5.05 fc	19.4 ft	19.4 ft
10.0R			
■ Vert. Spread: 88.1°		■ Horiz. Spread: 88.2°	

RT6S2500UNVD9SC3WH (2700K)




Illuminance at a Distance		Beam Width	
Center Beam fc	Beam Width	Zone	Lumens % Luminaire
1.7R	447 fc	3.2 ft	3.2 ft
2.3R	119 fc	6.3 ft	6.3 ft
3.3R	51.7 fc	9.5 ft	9.5 ft
5.0R	28.8 fc	12.8 ft	12.7 ft
6.7R	18.8 fc	15.8 ft	15.8 ft
8.3R	12.9 fc	19.0 ft	19.0 ft
10.0R			
■ Vert. Spread: 87.2°		■ Horiz. Spread: 87.1°	

RT8S1500UNVD9SC3WH (5000K)




Illuminance at a Distance		Beam Width	
Center Beam fc	Beam Width	Zone	Lumens % Luminaire
1.7R	264 fc	3.5 ft	3.5 ft
2.3R	70 fc	6.8 ft	6.8 ft
3.3R	30.5 fc	10.4 ft	10.4 ft
5.0R	17 fc	13.9 ft	13.9 ft
6.7R	11.1 fc	17.2 ft	17.2 ft
8.3R	7.62 fc	20.7 ft	20.7 ft
10.0R			
■ Vert. Spread: 92.0°		■ Horiz. Spread: 92.1°	

RT8S3500UNVD9SC3WH (2700K)



Illuminance at a Distance		Beam Width	
Center Beam fc	Beam Width	Zone	Lumens % Luminaire
1.7R	617 fc	3.4 ft	3.4 ft
2.3R	164 fc	6.6 ft	6.6 ft
3.3R	71.3 fc	10.1 ft	10.0 ft
5.0R	39.7 fc	13.5 ft	13.4 ft
6.7R	25.9 fc	16.7 ft	16.7 ft
8.3R	17.8 fc	20.1 ft	20.1 ft
10.0R			
■ Vert. Spread: 90.3°		■ Horiz. Spread: 90.2°	


RT10S4500UNVD9SC3WH (2700K)




Illuminance at a Distance		Beam Width	
Center Beam fc	Beam Width	Zone	Lumens % Luminaire
1.7R	728 fc	3.6 ft	3.6 ft
2.3R	193 fc	7.0 ft	7.0 ft
3.3R	84.1 fc	10.6 ft	10.6 ft
5.0R	46.6 fc	14.2 ft	14.2 ft
6.7R	30.5 fc	17.6 ft	17.6 ft
8.3R	21 fc	21.2 ft	21.2 ft
10.0R			
■ Vert. Spread: 93.4°		■ Horiz. Spread: 93.4°	

PHOTOMETRIC INFORMATION (CONTINUED)


RT4S1000UNHD9SC3WH (2700K)




RT6S2500UNHD9SC3WH (5000K)




RT8S3500UNHD9SC3WH (2700K)




RT4S1000UNVD9SC3WHP PIR (2700K)




RT6S2500UNVD9SC3WHP PIR (2700K)



RT8S3500UNVD9SC3WHP PIR (2700K)




RT10S4500UNVD9SC3WH PIR (2700K)





HOLE CUT TEMPLATES

RT4 HOLE CUT TEMPLATE




RT6 HOLE CUT TEMPLATE





HOLE CUT TEMPLATES

RT10 Hole Cut Template



LEDVANCE NORTH AMERICAN HEADQUARTERS

LEDVANCE LLC.
181 Ballardvale Street, Suite 203
Wilmington, MA 01887
Phone: +1 978 753 5000

LEDVANCE CANADIAN HEADQUARTERS

LEDVANCE LTD./LTE.
5450 Explorer Drive, Suite 100
Mississauga, Ontario L4W 5N1
Phone: +1 905 361 93 33

LEDVANCE.COM/EN-US

LEDVANCE is a registered trademark.
All other trademarks are those of their respective owners.
Specifications subject to change without notice.

© 2026 LEDVANCE LLC