


Switch Boxes and Accessories

Steel City® Super Deep 4" Square Wall Boxes

- Increased capacity accommodates large devices in commercial and industrial applications, such as fire alarm systems
- Red-painted version available for quick and easy identification of life safety electrical systems
- Available with or without integrally mounted support bracket

NEW!



Boxes & Covers — Steel City® Metallic Boxes

| CAT. NO. | DESCRIPTION | EARS | BRACKETS | EACH SIDE KO | EACH END KO | BOTTOM KO | CU. IN. CAPACITY | STD. CTN. |
|---------------|--|------|----------|-------------------|-------------------|-------------------|------------------|-----------|
| 521911234RD | 3½"-Deep, 4"-Square Red Box | — | — | (4) ½" & ¾" Combo | (2) ½" & ¾" Combo | (4) ½" & ¾" Combo | 46 | 24 |
| 521911234CVRD | 3½"-Deep, 4"-Square Red Box with Side Mounting Bracket | — | CV | (4) ½" & ¾" Combo | (2) ½" & ¾" Combo | (4) ½" & ¾" Combo | 46 | 10 |
| 521911234 | 3½"-Deep, 4"-Square Box | — | — | (4) ½" & ¾" Combo | (2) ½" & ¾" Combo | (4) ½" & ¾" Combo | 46 | 24 |
| 521911234CV | 3½"-Deep, 4"-Square Box with Side Mounting Bracket | — | CV | (4) ½" & ¾" Combo | (2) ½" & ¾" Combo | (4) ½" & ¾" Combo | 46 | 10 |

Switch Boxes and Accessories

Easy Depth Adjustment After Wall Covering Installation.

Adjust-A-Box®


The Adjust-A-Box System adapts to a variety of wall coverings. Its unique design enables the installer to adjust the box to various depths with the turn of a screw.

Features:

- Unique design allows for adjustment of depth after the wall covering has been installed
- Adjusts to any wall covering
- Mounts square and secure every time
- Removes easily to enable inner-wall access
- Accommodates high- and low-voltage applications
- Pre-installed ground screw
- Accommodates non-metallic cable, flexible metal cable and EMT



MB120ADJ



MB238ADJ

Installation:

Screw bracket to stud



Single-Gang



Two-Gang

Adjust box in or out to any wall thickness



Single-Gang



Two-Gang



| CAT. NO. | VOLUME (CU. IN.) | DESCRIPTION | KNOCKOUTS | SIZE (IN.) | STD. CTN. | STD. WT. (LBS.) |
|----------|------------------|------------------------------|-----------|-----------------------|-----------|-----------------|
| MB120ADJ | 20 | One-Gang Adjustable Wall Box | ½" (5) | 2.20W x 3.28H x 3.52D | 18 | 19.25 |
| MB238ADJ | 38 | Two-Gang Adjustable Wall Box | ½" (8) | 4.01W x 3.28H x 3.52D | 12 | 17.60 |

3¾" x 2" Switch Boxes

| CAT. NO. | DEPTH (IN.) | CU. IN. CAPACITY | CLAMPS | EARS | BRKTS. | KNOCKOUTS | STD. CTN. |
|---------------------|-------------|------------------|--------|------|--------|---|-----------|
| Non-Gangable | | | | | | | |
| SSV | 1 | 6.5 | — | — | Flat | 2 pry-outs one end | 25 |
| SSQV | 1 | 6.5 | Yes | — | Flat | 2 pry-outs one end with non-metallic cable clamps | 25 |

Not UL Listed.




SSV

Switch Boxes and Accessories

3" x 2" Switch Boxes



SWB-25
Ears flush
for old work



811-SW-25
S bracket recessed 5/8"



LXMWOW-25
Ears flush
for old work



LCOW-25
Ears flush
old work




LCOWC
Adapts to any wall
thickness up to 3/4"




LCLE-25



LCV-25
CV bracket
recessed 3/4"



LCNOW-25
Ears flush
for old work




802-S
S bracket recessed 5/8"



A12-25



A12E-25
Ears flush



A16-25
With nails



LXWOW-25
Ears flush
for old work



LXWOWP



LXWLE-25



LXWOWC-25
Adapts to any wall
thickness up to 3/4"



LXWSV
SV bracket
recessed 1/8"



LXWV-25
CV bracket
recessed 5/8"


With Non-Metallic Sheathed Cable Clamps

| CAT. NO. | DEPTH (IN.) | GANGABLE | CU. IN. CAPACITY | CLAMPS | EARS | BRKTS. | KNOCKOUTS (IN.) | | | | | STD. CTN. |
|-----------|-------------|----------|------------------|--------|------|--------|-----------------|---------------|-------|--------------|----------------|-----------|
| | | | | | | | EA. END CONDUIT | EA. END CABLE | CABLE | BOTTOM CABLE | BOTTOM CONDUIT | |
| SWB-25 | 1½ | — | 7.5 | C-5 | Yes | — | — | 2 | — | 2 | — | 25 |
| 811 SW-25 | 1½ | — | 7.5 | C-5 | — | S | — | 2 | — | 2 | — | 50 |
| LXMWOW-25 | 2 | Yes | 10.5 | C-5 | Yes | — | — | 2 | — | — | 1-½ | 25 |
| LCOW-25* | 2¼ | Yes | 10.5 | C-1 | Yes | — | 1-½ | — | 2 | — | 1-½ | 25 |
| LCOWC* | 2¼ | Yes | 10.5 | C-1 | Yes | — | 1-½ | — | 2 | — | 1-½ | 25 |
| LCLE-25* | 2¼ | Yes | 10.5 | C-1 | — | — | 1-½ | — | 2 | — | 1-½ | 25 |
| LCV-25* | 2¼ | Yes | 10.5 | C-1 | — | CV | 1-½ | — | 2 | — | 1-½ | 25 |
| LCNOW-25* | 2¼ | Yes | 10.5 | C-1 | Yes | — | 1-½ | — | 2 | — | 1-½ | 25 |
| 802 S* | 2¼ | Yes | 10.5 | C-1 | — | S | 1-½ | — | 2 | — | 1-½ | 25 |
| A12-25 | 2¼ | — | 10.5 | C-1 | — | — | 1-½ | — | 2 | — | 1-½ | 25 |
| A12E-25 | 2¼ | — | 10.5 | C-1 | Yes | — | 1-½ | — | 2 | — | 1-½ | 25 |
| A16-25 | 2¼ | — | 10.5 | C-1 | — | — | 1-½ | — | 2 | — | 1-½ | 25 |
| LXWOW-25 | 2½ | Yes | 12.5 | C-5 | Yes | — | 1-½ | — | 2 | — | 1-½ | 25 |
| LXWOWP | 2½ | Yes | 12.5 | C-5 | Yes | — | 1-½ | — | 2 | — | 1-½ | 25 |
| LXWLE-25 | 2½ | Yes | 12.5 | C-5 | — | — | 1-½ | 1-½ | 2 | — | 1-½ | 25 |
| LXWOWC-25 | 2½ | Yes | 12.5 | C-5 | Yes | — | 1-½ | — | 2 | — | 1-½ | 25 |
| LXWSV | 2½ | Yes | 12.5 | C-5 | — | SV | 1-½ | 1-½ | 2 | — | 1-½ | 25 |
| LXWV-25 | 2½ | Yes | 12.5 | C-5 | — | CV | 1-½ | 1-½ | 2 | — | 1-½ | 25 |

* Beveled corners.

Switch Boxes and Accessories


3" x 2" Switch Boxes (continued)




LXWV 2G
2-gang with CV
bracket recessed 7/8"




806 SW
S bracket recessed 5/8"



806 SW 1/4
S bracket recessed 1/4"



A254-25



A257-25
With nails slanted
for easy drive-in




A-258
Without nails




CWN-25
Ears flush



CWNLE




CWNV-25
CV bracket
recessed 7/8"




CXWLE



CXWOW
Ears flush
for old work



CXWOWP



CXWV
CV bracket
recessed 1/8"



CXWVP

With Non-Metallic Sheathed Cable Clamps (continued)

| CAT. NO. | DEPTH (IN.) | GANGABLE | CU. IN. CAPACITY | CLAMPS | EARS | BRKTS. | KNOCKOUTS (IN.) | | | | | STD. CTN. |
|------------|----------------|----------|---------------------|--------|------|--------|--------------------|------------------|-------|-----------------|-------------------|--------------|
| | | | | | | | EA. END CONDUIT | EA. END CABLE | CABLE | BOTTOM CABLE | BOTTOM CONDUIT | |
| LXWV 2G | 2½ | Yes | 12.5 | C-5 | — | CV | 1-½ | 2-½ | 4 | — | 2-½ | 25 |
| 806 SW | 2½ | Yes | 12.5 | C-5 | — | S | 1-½ | 1-½ | 2 | — | 1-½ | 25 |
| 806 SW 1/4 | 2½ | Yes | 12.5 | C-5 | — | S | 1-½ | 1-1½ | 2 | — | 1-½ | 25 |
| A254-25 | 2½ | — | 12.5 | C-5 | — | — | — | 1-½ | 2 | — | 1-½ | 25 |
| A257-25 | 2½ | — | 12.5 | C-5 | — | — | — | 1-½ | 2 | — | 1-½ | 25 |
| A-258 | 2½ | — | 12.5 | C-5 | — | — | — | 1-½ | 2 | — | 1-½ | 25 |
| CWN-25 | 2¾ | Yes | 14.0 | C-5 | Yes | — | 1-½ | — | 2 | — | 1-½ | 25 |
| CWNLE | 2¾ | Yes | 14.0 | C-5 | — | — | 1-½ | — | 2 | — | 1-½ | 25 |
| CWNV-25 | 2¾ | Yes | 14.0 | C-5 | — | CV | 1-½ | — | 2 | — | 1-½ | 25 |
| CXWLE | 3½ | Yes | 18.0 | C-5 | — | — | 2-½ | 1-½ | 2 | — | 1-½ | 25 |
| CXWOW | 3½ | Yes | 18.0 | C-5 | Yes | — | 2-½ | 1-½ | 2 | — | 1-½ | 25 |
| CXWOWP | 3½ | Yes | 18.0 | C-5 | Yes | — | 2-½ | 1-½ | 2 | — | 1-½ | 25 |
| CXWV | 3½ | Yes | 18.0 | C-5 | — | CV | 2-1½ | 1-½ | 2 | — | 1-½ | 25 |
| CXWVP | 3½ | Yes | 18.0 | C-5 | — | CV | 2-½ | 1-½ | 2 | — | 1-1½ | 25 |

Switch Boxes and Accessories

3" x 2" Switch Boxes (continued)




CDOW
Ears flush




CDOWTG-25
Ears flush



CDLE-25



CDV-25
CV bracket
recessed 7/8"



804 S
S bracket recessed 5/8"



CW 1/2
Ears flush



CW3/4-25
Ears flush



CWLE1/2-25




CWLE 3/4




CWV 1/2
CV bracket
recessed 7/8"




CY 1/2
Ears flush



CY 3/4
Ears flush



CYLE 1/2



CYLE 3/4

With Conduit KOs

| CAT. NO. | DEPTH (IN.) | GANGABLE | CU. IN. CAPACITY | EARS | BRKTS. | KNOCKOUTS (IN.) | | | STD. CTN. |
|------------|-------------|----------|------------------|------|--------|-----------------|---------------|----------------|-----------|
| | | | | | | EA. END CONDUIT | EA. END CABLE | BOTTOM CONDUIT | |
| CDOW | 2½ | Yes | 12.5 | Yes | — | 1½ | 1½ | 2½ | 50 |
| CDOWTG-25 | 2½ | Yes | 12.5 | Yes | — | 1½ | 1½ | 2½ | 25 |
| CDLE-25 | 2½ | Yes | 12.5 | — | — | 1½ | 1½ | 2½ | 25 |
| CDV-25 | 2½ | Yes | 12.5 | — | CV | 1½ | 1½ | 2½ | 25 |
| 804 S | 2½ | Yes | 12.5 | — | S | 1½ | 1½ | 2½ | 25 |
| CW 1/2 | 2¾ | Yes | 14.0 | Yes | — | 1-½ | 1-½ | 1-½ | 50 |
| CW3/4-25 | 2¾ | Yes | 14.0 | Yes | — | 1-¾ | 1-¾ | 1-¾ | 25 |
| CWLE1/2-25 | 2¾ | Yes | 14.0 | — | — | 1-½ | 1-½ | 1-½ | 25 |
| CWLE 3/4 | 2¾ | Yes | 14.0 | — | — | 1-¾ | 1-¾ | 1-¾ | 25 |
| CWV 1/2 | 2¾ | Yes | 14.0 | — | CV | 1-½ | 1-½ | 1-½ | 25 |
| CY 1/2 | 3½ | Yes | 18.0 | Yes | — | 2-½ | 2-½ | 1-½ | 25 |
| CY 3/4 | 3½ | Yes | 18.0 | Yes | — | 2-¾ | 2-¾ | 1-½ | 25 |
| CYLE 1/2 | 3½ | Yes | 18.0 | — | — | 2-½ | 2-½ | 1-½ | 25 |
| CYLE 3/4 | 3½ | Yes | 18.0 | — | — | 2-¾ | 2-¾ | 1-½ | 25 |

Switch Boxes and Accessories

3" x 2" Switch Boxes (continued)



LXMOV-25
Ears flush
for old work



LXOW-25
Ears flush
for old work




LXOWC-25
Adapts to 3/4"
wall thickness




LXLE




LXV-25
CV bracket
recessed 1/8"



LXVP



806 S
S bracket recessed 3/8"



A-256
With nails slanted
for easy drive-in




CWX-25
Ears flush




CWXV-25
CV bracket
recessed 1/2"



CX
Ears flush



CXLE-SSX
For metal stud



CXP



CXV
CV bracket
recessed 1/8"

With Armored Cable/Metal Clad Clamps


| CAT. NO. | DEPTH (IN.) | GANGABLE | CU. IN. CAPACITY | CLAMPS | EARS | BRKTS. | KNOCKOUTS (IN.) | | | | STD. CTN. |
|----------|-------------|----------|------------------|--------|------|--------|-----------------|---------------|-------|----------------|-----------|
| | | | | | | | EA. END CONDUIT | EA. END CABLE | CABLE | BOTTOM CONDUIT | |
| LXMOV-25 | 2 | Yes | 10.5 | C-3 | Yes | — | — | 2 | — | 1-1/2 | 25 |
| LXOW-25 | 2 1/2 | Yes | 12.5 | C-3 | Yes | — | 1-1/2 | — | 2 | 1-1/2 | 25 |
| LXOWC-25 | 2 1/2 | Yes | 12.5 | C-3 | Yes | — | 1-1/2 | — | 2 | 1-1/2 | 25 |
| LXLE | 2 1/2 | Yes | 12.5 | C-3 | — | — | 1-1/2 | 1-1/2 | 2 | 1-1/2 | 25 |
| LXV-25 | 2 1/2 | Yes | 12.5 | C-3 | — | CV | 1-1/2 | 1-1/2 | 2 | 1-1/2 | 25 |
| LXVP | 2 1/2 | Yes | 12.5 | C-3 | — | CV | 1-1/2 | 1-1/2 | 2 | 1-1/2 | 25 |
| 806 S | 2 1/2 | Yes | 12.5 | C-3 | — | S | 1-1/2 | 1-1/2 | 2 | 1-1/2 | 25 |
| A-256 | 2 1/2 | — | 12.5 | C-3 | — | — | — | 1-1/2 | 2 | 1-1/2 | 25 |
| CWX-25 | 2 3/4 | Yes | 14.0 | C-3 | Yes | — | 1-1/2 | — | 2 | 1-1/2 | 25 |
| CWXV-25 | 2 3/4 | Yes | 14.0 | C-3 | — | CV | 1-1/2 | — | 2 | 1-1/2 | 25 |
| CX | 3 1/2 | Yes | 18.0 | C-3 | Yes | — | 2-1/2 | 1-1/2 | 2 | 1-1/2 | 25 |
| CXLE-SSX | 3 1/2 | Yes | 18.0 | C-3 | No | SSX | 2-1/2 | 1-1/2 | 2 | 1-1/2 | 25 |
| CXP | 3 1/2 | Yes | 18.0 | C-3 | Yes | — | 2-1/2 | 1-1/2 | 2 | 1-1/2 | 25 |
| CXV | 3 1/2 | Yes | 18.0 | C-3 | — | CV | 2-1/2 | 1-1/2 | 2 | 1-1/2 | 25 |

Switch Boxes and Accessories


Gangable Switch Boxes — 2" Deep




51



51-NE



51-LC




51-FB


| CAT. NO. | CU. IN. CAPACITY | DESCRIPTION | STD. CTN. |
|----------|------------------|---|-----------|
| 51 | 10.0 | 2" deep x 3" long x 2" wide Two ½" KOs in each of two sides, one ½" KO in each end and two ½" KOs in bottom. Two nail holes in sides. Furnished with plaster ears* | 50 |
| 51-NE | 10.0 | 2" deep x 3" long x 2" wide Two ½" KOs in each of two sides, one ½" KO in each end and two ½" KOs in bottom. Two nail holes in sides* | 50 |
| 51-LC | 10.0 | For Non-Metallic Cable, 2" deep x 3" long x 2" wide Two ½" KOs in each of two sides, two Loom KOs in each end and one ½" KO in bottom. Furnished with plaster ears. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled. Two nail holes in sides* | 50 |
| 51-FB | 10.0 | 2" deep x 3" long x 2" wide Two ½" KOs in one side, flat bracket on other side, one ½" KO in each end and two ½" KOs in bottom. Bracket offset ⅞" from face* | 50 |

*Uses Steel City® 100 series covers.


Gangable Switch Boxes — 2½" Deep




52




52-3/4-BW




52-NE




52-NE-3/4



52-LCNE



52-FB-3/4




52-FBC

| CAT. NO. | CU. IN. CAPACITY | DESCRIPTION | STD. CTN. |
|-----------|------------------|---|-----------|
| 52 | 12.5 | 2½" deep x 3" long x 2" wide Two ½" KOs in each of two sides, one ½" KO in each end and two ½" KOs in bottom. Furnished with plaster ears. Four nail holes in sides* | 50 |
| 52-3/4-BW | 12.5 | 2½" deep x 3" long x 2" wide Two ½" KOs in each of two sides, one ¾" KO in each end and two ½" KOs in bottom. Furnished with plaster ears. Four nail holes in sides* | 50 |
| 52-NE | 12.5 | 2½" deep x 3" long x 2" wide Two ½" KOs in each of two sides, one ½" KO in each end and two ½" KOs in bottom. Four nail holes in sides* | 50 |
| 52-NE-3/4 | 12.5 | 2½" deep x 3" long x 2" wide Two ½" KOs in each of two sides, one ¾" KO in each end and two ½" KOs in bottom. Four nail holes in sides* | 50 |
| 52-LCNE | 12.5 | For Non-Metallic Cable, 2½" deep x 3" long x 2" wide Two ½" KOs in each side, two Loom KOs and one ½" KO in each end. One ½" KO in bottom. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled. Four nail holes in sides* | 50 |
| 52-FB-3/4 | 12.5 | 2½" deep x 3" long x 2" wide Two ½" KOs in one side, flat bracket on other side, one KO in each end and two ¾" KOs in bottom. Flat bracket offset ⅞" from face* | 50 |
| 52-FBC | 12.5 | For Non-Metallic Cable, 2½" deep x 3" long x 2" wide Two ½" KOs in one side, flat bracket on other side, two Loom KOs and one ½" KO in each end and one ½" KO in bottom. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled. Flat bracket offset ⅞" from face* | 50 |

*Uses Steel City® 100 series covers.

Switch Boxes and Accessories

Gangable Switch Boxes — 2¾" Deep




| CAT. NO. | CU. IN. CAPACITY | DESCRIPTION | STD. CTN. |
|------------|------------------|--|-----------|
| 53 | 14.0 | 2¾" deep x 3" long x 2" wide Two ½" KOs in each side, one ½" KO in each end and two ½" KOs in bottom. Furnished with plaster ears. Four nail holes in sides* | 50 |
| 53-3/4-BW | 14.0 | 2¾" deep x 3" long x 2" wide Two ½" KOs in each side, one ¾" KO in each end and two ½" KOs in bottom. Furnished with plaster ears. Four nail holes in sides* | 50 |
| 53-NE | 14.0 | 2¾" deep x 3" long x 2" wide Two ½" KOs in each side, one ½" KO in each end and two ½" KOs in bottom. Four nail holes in sides* | 50 |
| 53-NE-3/4 | 14.0 | 2¾" deep x 3" long x 2" wide Two ½" KOs in each side, one ¾" KO in each end and two ½" KOs in bottom. Four nail holes in sides* | 50 |
| 53-LCNE | 14.0 | For Non-Metallic Cable, 2¾" deep x 3" long x 2" wide Two ½" KOs in each side, two Loom KOs and one ½" KO in each end and one ½" KO in bottom. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled. Four nail holes in sides* | 50 |
| 53-FB | 14.0 | 2¾" deep x 3" long x 2" wide Two ½" KOs in one side, flat bracket on other side, one ½" KO in each end and two ½" KOs in bottom. Flat bracket offset ⅞" from face* | 50 |
| 53-FBC | 14.0 | For Non-Metallic Cable, 2¾" deep x 3" long x 2" wide Two ½" KOs in one side, flat bracket on other side, two Loom KOs and one ½" KO in each end and one ½" KO in bottom. Flat offset ⅞" from face. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled* | 50 |
| 53-FB-MXN | 14.0 | For Metal Clad Cable, 2¾" deep x 3" long x 2" wide Two ½" KOs in one side, flat bracket on other side, two Loom KOs and one ½" KO in each end, and one ½" KO in bottom. One MXN clamp for MC, AC/BX, and non-metallic sheathed cable (NM) included with 10/32 deep-slotted screw. Clamp is UL Listed for use with cable sizes 14/2 through 10/3 with ground* | 50 |
| 53-OWEC | 14.0 | For Non-Metallic Cable, 2¾" deep x 3" long x 2" wide Two ½" KOs in each side, two Loom KOs and one ½" KO in each end and one ½" KO in bottom. Furnished with plaster ears. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled. With old-work swing brackets* | 50 |
| 53-OWE | 14.0 | 2¾" deep x 3" long x 2" wide Two ½" KOs in each side, one ½" KO in each end and two ½" KOs in bottom. Furnished with plaster ears. With old-work swing brackets* | 50 |
| 53-OWE-MXN | 14.0 | For Metal-Clad Cable, 2¾" deep x 3" long x 2" wide Two ½" KOs in each side. Two Loom KOs and one ½" KO in each end and one ½" KO in bottom. One MXN clamp for MC, AC/BX and non-metallic sheathed cable (NM) included with 10/32 deep-slotted screw. Clamp is UL Listed for use with cable sizes 14/2 through 10/3 with ground. Furnished with plaster ears. With old-work swing brackets* | 50 |


*Uses Steel City® 100 series covers.

Switch Boxes and Accessories


Gangable Switch Boxes — 3½" Deep



54-LC



54-FBC




54-FB-MXN


| CAT. NO. | CU. IN. CAPACITY | DESCRIPTION | STD. CTN. |
|-----------|------------------|--|-----------|
| 54-LC | 18.0 | For Non-Metallic Cable 3½" deep x 3" long x 2" wide Two ½" KO in each side, two Loom KOs and one ½" KO in each end and one ½" KO in bottom. Two Loom clamps for use on non-metallic sheathed cable with 10/32 deep-slotted screws assembled. Furnished with plaster ears. Four nail holes in sides* | 50 |
| 54-FBC | 18.0 | For Non-Metallic Cable 3½" deep x 3" long x 2" wide Two ½" KOs in one side, flat bracket and two ½" KOs in other side, two Loom KOs and one ½" KO in each end and one ½" KO in bottom. Two Loom clamps for use on non-metallic sheathed cable with 10/32 deep-slotted screws assembled. Flat bracket offset ⅜" from face* | 50 |
| 54-FB-MXN | 18.0 | For Metal Cable, 3½" deep x 3" long x 2" wide Two ½" KOs in one side, flat bracket and two ½" KOs in other side, two Loom KOs and one ½" KO in each end and one ½" KO in bottom. Two MXN clamps for MC, AC/BX, and non-metallic sheathed cable (NM) included with 10/32 deep-slotted screws. Clamps are UL Listed for use with cable sizes 14/2 through 10/3 with ground. Flat bracket offset ⅜" from face* | 50 |

*Uses Steel City® 100 series covers.


Welded Non-Gangable Switch Boxes — 2½" Deep




72




72-C




72-OC



72-OWE



72-ONS-MXN



72-FB-MXN

| CAT. NO. | CU. IN. CAPACITY | DESCRIPTION | STD. CTN. |
|------------|------------------|---|-----------|
| 72 | 12.5 | 2½" deep x 3" long x 2" wide Two Loom KOs and one ½" KO in each end and one ½" KO in bottom. Four nail holes included* | 50 |
| 72-C | 12.5 | For Non-Metallic Cable 2½" deep x 3" long x 2" wide Two Loom KOs and one ½" KO in each end and one ½" KO in bottom. Four nail holes included. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled* | 50 |
| 72-OC | 12.5 | For Non-Metallic Cable 2½" deep x 3" long x 2" wide Two Loom KOs and one ½" KO in each end and one ½" KO in bottom. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled. Four nail holes included. Provisions for external nails included* | 50 |
| 72-OWE | 12.5 | 2½" deep x 3" long x 2" wide Two Loom KOs and one ½" KO in each end and one ½" KO in bottom. With old-work swing brackets* | 50 |
| 72-ONS-MXN | 12.5 | For Metal-Clad Cable 2½" deep x 3" long x 2" wide Two Loom KOs and one ½" KO in each end and one ½" KO in bottom. One MXN clamp for MC, AC/BX and nonmetallic sheathed cable (NM) included with 10/32 deep-slotted screw. Clamp is UL Listed for use with cable sizes 14/2 through 10/3 with ground. Four nail holes included. Two 16-penny nails swaged at an angle in box* | 50 |
| 72-FB-MXN | 12.5 | For Metal-Clad Cable 2½" deep x 3" long x 2" wide Two Loom KOs and one ½" KO in each end, one ½" KO in bottom and flat bracket on one side offset ⅜" from face. Two MXN clamps for MC, AC/BX and non-metallic sheathed cable (NM) included with 10/32 deep-slotted screws. Clamps are UL Listed for use with cable sizes 14/2 through 10/3 with ground. Four nail holes included* | 50 |


*Uses Steel City® 100 series covers.

Switch Boxes and Accessories

Welded Non-Gangable Switch Boxes — 2¹³/₁₆" Deep


| CAT. NO. | CU. IN. CAPACITY | DESCRIPTION | STD. CTN. |
|-----------|------------------|---|-----------|
| 73-ONCS | 15.8 | For Non-metallic Cable, 2¹³/₁₆" deep x 3" long x 2⁹/₁₆" wide Two Loom KOs and one 1/2" KO in each end and one 1/2" KO in bottom. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled. Two 16-penny nails swaged at an angle in box* | 50 |
| 73-FBC | 15.8 | For Non-metallic Cable, 2¹³/₁₆" deep x 3" long x 2⁹/₁₆" wide Two Loom KOs and one 1/2" KO in each end, one 1/2" KO in bottom and flat bracket on one side offset 3/16" from face. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled. Four nail holes included* | 50 |
| 73-FB-MXN | 15.8 | For Metal-Clad Cable, 2¹³/₁₆" deep x 3" long x 2⁹/₁₆" wide Two Loom KOs and one 1/2" KO in each end, one 1/2" KO in bottom and flat bracket on one side offset 3/16" from face. One MXN clamp for MC, AC/BX and non-metallic sheathed cable (NM) included with 10/32 deep-slotted screw. Clamp is UL Listed for use with cable sizes 14/2 through 10/3 with ground. Four nail holes included* | 50 |

*Uses Steel City® 100 series covers.



73-ONCS

73-FBC




73-FB-MXN

Welded Non-Gangable Switch Boxes — 3" Deep


| CAT. NO. | CU. IN. CAPACITY | DESCRIPTION | STD. CTN. |
|----------|------------------|---|-----------|
| 74-CE | 18 | For Non-metallic Cable, 3/4" deep x 3" long x 2 1/4" wide Two Loom KOs and one 1/2" KO in each end and one 1/2" KO in bottom. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled. Furnished with ears. Four nail holes included* | 50 |
| 74-ONCS | 18 | For Non-metallic Cable, 3/4" deep x 3" long x 2 1/4" wide Two Loom KOs and one 1/2" KO in each end and one 1/2" KO in bottom. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled. Two 16-penny nails swaged at an angle in box* | 50 |
| 74-FBC | 18 | For Non-metallic Cable, 3/4" deep x 3" long x 2 1/4" wide Two Loom KOs and one 1/2" KO in each end, one 1/2" KO in bottom and flat bracket on one side offset 3/16" from face. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled. Four nail holes included* | 50 |

*Uses Steel City® 100 series covers.



74-CE

74-ONCS




74-FBC

Welded Non-Gangable Switch Box — 3¹³/₃₂" Deep

| CAT. NO. | CU. IN. CAPACITY | DESCRIPTION | STD. CTN. |
|----------|------------------|---|-----------|
| 75-ONCS | 20.0 | For Non-metallic Cable, 3¹³/₃₂" deep x 3" long x 2 1/4" wide Two Loom KOs and one 1/2" KO in each end and one 1/2" KO in bottom. Two Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled. Four nail holes included. Two 16-penny nails swaged at angle in box*. | 50 |

*Uses Steel City® 100 series covers.




75-ONCS

Switch Boxes and Accessories


Welded Multi-Gangable Switch Boxes — 2½" Deep

| CAT. NO. | CAPACITY | DESCRIPTION | STD. CTN. |
|------------|----------|--|-----------|
| 271-FBC | 25.0 | A Two-Gang Box — For Non-Metallic Cable, 2½" deep x 3" long x 4" wide Two Loom KOs and two ½" KOs in each end, flat bracket on one side and one ½" KO in bottom. Two Loom clamps for use on non-metallic sheathed cable with 10/32 deep-slotted screws assembled. Flat bracket offset ⅜" from face* | 25 |
| 271-FB-MXN | 25.0 | A Two-Gang Box — For Metal-Clad Cable, 2½" deep x 3" long x 4" wide Two Loom KOs and two ½" KOs in each end, flat bracket on one side and one ½" KO in bottom. Two MXN clamps for MC, AC/BX and non-metallic sheathed cable (NM) included with 10/32 deep-slotted screws. Clamps are UL Listed for use with cable sizes 14/2 through 10/3 with ground. Flat bracket offset ⅜" from face* | 25 |

*Uses Steel City® SB-2 covers.



271-FBC



271-FB-MXN

Boxes & Covers — Steel City® Metallic Boxes

4" x 2½" Thru-Wall Box

| CAT. NO. | CU. IN. CAPACITY | DESCRIPTION | BOX DEPTH (IN.) | STD. CTN. |
|---|------------------|--|-----------------|-----------|
| With Conduit KOs for Plaster or Dry Wall | | | | |
| CTDW | 32.0 | Drywall, partition type; one ½" and one ¾" KO both ends; one ½" KO on one side, V bracket other side | 4⅞ | 25 |



CTDW

Switch Box Extension

| CAT. NO. | DESCRIPTION | STD. CTN. |
|----------|--|-----------|
| SBEX | Cubic content 3.5 inches; fits snugly inside of all single-gang switch boxes; maximum adjustable depth ⅞"; furnished with 1¼"-long screws for mounting | 50 |

UL Listing not applicable — subject to approval by local inspector.



SBEX

Switch Boxes and Accessories

Old-Work Box Support

- Quickly attaches box through finished drywall
- For up to 1½" thick drywall
- New 820D shipped in one-piece break-apart design
- Easy to install

| CAT. NO. | FIG. NO. | DESCRIPTION | STD. CTN. |
|----------|----------|---|-----------|
| 820D | 1 | Old-work switch box steel-mounting holder | 500 sets |





Fig. 1




Steel Low-Voltage Bracket

- Fixes to the switch box easily with the screws provided
- Works with any Steel City® switch box, regardless of depth
- Single-screw fixing as well as two-screw fixing
- Low-voltage cable support is provided by fitting location tabs
- UL Listed for low-voltage support



| CAT. NO. | DESCRIPTION | BOX DEPTH (IN.) | STD. CTN. |
|----------|--|-----------------|-----------|
| LVB | Bracketed to T&B boxes; provides means of installing a low-voltage device alongside a regular switch or outlet | 1 1/8 | 25 |




LVB

Old-Work Box Support Clips


- Adapts to any wall thickness up to ¾"

| CAT. NO. | DESCRIPTION | STD. CTN. |
|--------------|---|--------------|
| OWC | Clips lock old-work steel switch boxes tightly to wall plaster, drywall, concrete block, brick or concrete. 2 required per box, (1 set) | 250 sets |
| OW SWING EAR | Swing ears only (for field installations) with self-threading screws | 50 (25 pair) |



OWC

OW Swing Ear



Switch Boxes and Accessories

Steel City® Super Deep 4" Square Wall Boxes

- Increased capacity accommodates large devices in commercial and industrial applications, such as fire alarm systems
- Red-painted version available for quick and easy identification of life safety electrical systems
- Available with or without integrally mounted support bracket

NEW!



Boxes & Covers — Steel City® Metallic Boxes

| CAT. NO. | DESCRIPTION | EARS | BRACKETS | EACH SIDE KO | EACH END KO | BOTTOM KO | CU. IN. CAPACITY | STD. CTN. |
|---------------|--|------|----------|-------------------|-------------------|-------------------|------------------|-----------|
| 521911234RD | 3½"-Deep, 4"-Square Red Box | — | — | (4) ½" & ¾" Combo | (2) ½" & ¾" Combo | (4) ½" & ¾" Combo | 46 | 24 |
| 521911234CVRD | 3½"-Deep, 4"-Square Red Box with Side Mounting Bracket | — | CV | (4) ½" & ¾" Combo | (2) ½" & ¾" Combo | (4) ½" & ¾" Combo | 46 | 10 |
| 521911234 | 3½"-Deep, 4"-Square Box | — | — | (4) ½" & ¾" Combo | (2) ½" & ¾" Combo | (4) ½" & ¾" Combo | 46 | 24 |
| 521911234CV | 3½"-Deep, 4"-Square Box with Side Mounting Bracket | — | CV | (4) ½" & ¾" Combo | (2) ½" & ¾" Combo | (4) ½" & ¾" Combo | 46 | 10 |

Switch Boxes and Accessories

Easy Depth Adjustment After Wall Covering Installation.

Adjust-A-Box®


The Adjust-A-Box System adapts to a variety of wall coverings. Its unique design enables the installer to adjust the box to various depths with the turn of a screw.

Features:

- Unique design allows for adjustment of depth after the wall covering has been installed
- Adjusts to any wall covering
- Mounts square and secure every time
- Removes easily to enable inner-wall access
- Accommodates high- and low-voltage applications
- Pre-installed ground screw
- Accommodates non-metallic cable, flexible metal cable and EMT



MB120ADJ



MB238ADJ

Installation:

Screw bracket to stud



Single-Gang



Two-Gang

Adjust box in or out to any wall thickness



Single-Gang



Two-Gang



| CAT. NO. | VOLUME (CU. IN.) | DESCRIPTION | KNOCKOUTS | SIZE (IN.) | STD. CTN. | STD. WT. (LBS.) |
|----------|------------------|------------------------------|-----------|-----------------------|-----------|-----------------|
| MB120ADJ | 20 | One-Gang Adjustable Wall Box | ½" (5) | 2.20W x 3.28H x 3.52D | 18 | 19.25 |
| MB238ADJ | 38 | Two-Gang Adjustable Wall Box | ½" (8) | 4.01W x 3.28H x 3.52D | 12 | 17.60 |

3¾" x 2" Switch Boxes

| CAT. NO. | DEPTH (IN.) | CU. IN. CAPACITY | CLAMPS | EARS | BRKTS. | KNOCKOUTS | STD. CTN. |
|---------------------|-------------|------------------|--------|------|--------|---|-----------|
| Non-Gangable | | | | | | | |
| SSV | 1 | 6.5 | — | — | Flat | 2 pry-outs one end | 25 |
| SSQV | 1 | 6.5 | Yes | — | Flat | 2 pry-outs one end with non-metallic cable clamps | 25 |

Not UL Listed.




SSV

Switch Boxes and Accessories

3" x 2" Switch Boxes



SWB-25
Ears flush
for old work



811-SW-25
S bracket recessed 3/8"



LXMWOW-25
Ears flush
for old work



LCOW-25
Ears flush
old work




LCOWC
Adapts to any wall
thickness up to 3/4"




LCLE-25



LCV-25
CV bracket
recessed 3/4"



LCNOW-25
Ears flush
for old work




802-S
S bracket recessed 3/8"



A12-25



A12E-25
Ears flush



A16-25
With nails



LXWOW-25
Ears flush
for old work



LXWOWP



LXWLE-25



LXWOWC-25
Adapts to any wall
thickness up to 3/4"



LXWSV
SV bracket
recessed 1/8"



LXWV-25
CV bracket
recessed 3/8"


With Non-Metallic Sheathed Cable Clamps

| CAT. NO. | DEPTH (IN.) | GANGABLE | CU. IN. CAPACITY | CLAMPS | EARS | BRKTS. | KNOCKOUTS (IN.) | | | | | STD. CTN. |
|-----------|-------------|----------|------------------|--------|------|--------|-----------------|---------------|-------|--------------|----------------|-----------|
| | | | | | | | EA. END CONDUIT | EA. END CABLE | CABLE | BOTTOM CABLE | BOTTOM CONDUIT | |
| SWB-25 | 1 1/2 | — | 7.5 | C-5 | Yes | — | — | 2 | — | 2 | — | 25 |
| 811 SW-25 | 1 1/2 | — | 7.5 | C-5 | — | S | — | 2 | — | 2 | — | 50 |
| LXMWOW-25 | 2 | Yes | 10.5 | C-5 | Yes | — | — | 2 | — | — | 1-1/2 | 25 |
| LCOW-25* | 2 1/4 | Yes | 10.5 | C-1 | Yes | — | 1-1/2 | — | 2 | — | 1-1/2 | 25 |
| LCOWC* | 2 1/4 | Yes | 10.5 | C-1 | Yes | — | 1-1/2 | — | 2 | — | 1-1/2 | 25 |
| LCLE-25* | 2 1/4 | Yes | 10.5 | C-1 | — | — | 1-1/2 | — | 2 | — | 1-1/2 | 25 |
| LCV-25* | 2 1/4 | Yes | 10.5 | C-1 | — | CV | 1-1/2 | — | 2 | — | 1-1/2 | 25 |
| LCNOW-25* | 2 1/4 | Yes | 10.5 | C-1 | Yes | — | 1-1/2 | — | 2 | — | 1-1/2 | 25 |
| 802 S* | 2 1/4 | Yes | 10.5 | C-1 | — | S | 1-1/2 | — | 2 | — | 1-1/2 | 25 |
| A12-25 | 2 1/4 | — | 10.5 | C-1 | — | — | 1-1/2 | — | 2 | — | 1-1/2 | 25 |
| A12E-25 | 2 1/4 | — | 10.5 | C-1 | Yes | — | 1-1/2 | — | 2 | — | 1-1/2 | 25 |
| A16-25 | 2 1/4 | — | 10.5 | C-1 | — | — | 1-1/2 | — | 2 | — | 1-1/2 | 25 |
| LXWOW-25 | 2 1/2 | Yes | 12.5 | C-5 | Yes | — | 1-1/2 | — | 2 | — | 1-1/2 | 25 |
| LXWOWP | 2 1/2 | Yes | 12.5 | C-5 | Yes | — | 1-1/2 | — | 2 | — | 1-1/2 | 25 |
| LXWLE-25 | 2 1/2 | Yes | 12.5 | C-5 | — | — | 1-1/2 | 1-1/2 | 2 | — | 1-1/2 | 25 |
| LXWOWC-25 | 2 1/2 | Yes | 12.5 | C-5 | Yes | — | 1-1/2 | — | 2 | — | 1-1/2 | 25 |
| LXWSV | 2 1/2 | Yes | 12.5 | C-5 | — | SV | 1-1/2 | 1-1/2 | 2 | — | 1-1/2 | 25 |
| LXWV-25 | 2 1/2 | Yes | 12.5 | C-5 | — | CV | 1-1/2 | 1-1/2 | 2 | — | 1-1/2 | 25 |

* Beveled corners.

Switch Boxes and Accessories


3" x 2" Switch Boxes (continued)




LXWV 2G
2-gang with CV
bracket recessed 7/8"




806 SW
S bracket recessed 5/8"




806 SW 1/4
S bracket recessed 1/4"



A254-25



A257-25
With nails slanted
for easy drive-in




A-258
Without nails




CWN-25
Ears flush



CWNLE




CWNV-25
CV bracket
recessed 7/8"




CXWLE



CXWOW
Ears flush
for old work



CXWOWP



CXWV
CV bracket
recessed 1/8"



CXWVP

With Non-Metallic Sheathed Cable Clamps (continued)

| CAT. NO. | DEPTH (IN.) | GANGABLE | CU. IN. CAPACITY | CLAMPS | EARS | BRKTS. | KNOCKOUTS (IN.) | | | | | STD. CTN. |
|------------|----------------|----------|---------------------|--------|------|--------|--------------------|------------------|-------|-----------------|-------------------|--------------|
| | | | | | | | EA. END CONDUIT | EA. END CABLE | CABLE | BOTTOM CABLE | BOTTOM CONDUIT | |
| LXWV 2G | 2½ | Yes | 12.5 | C-5 | — | CV | 1-½ | 2-½ | 4 | — | 2-½ | 25 |
| 806 SW | 2½ | Yes | 12.5 | C-5 | — | S | 1-½ | 1-½ | 2 | — | 1-½ | 25 |
| 806 SW 1/4 | 2½ | Yes | 12.5 | C-5 | — | S | 1-½ | 1-1½ | 2 | — | 1-½ | 25 |
| A254-25 | 2½ | — | 12.5 | C-5 | — | — | — | 1-½ | 2 | — | 1-½ | 25 |
| A257-25 | 2½ | — | 12.5 | C-5 | — | — | — | 1-½ | 2 | — | 1-½ | 25 |
| A-258 | 2½ | — | 12.5 | C-5 | — | — | — | 1-½ | 2 | — | 1-½ | 25 |
| CWN-25 | 2¾ | Yes | 14.0 | C-5 | Yes | — | 1-½ | — | 2 | — | 1-½ | 25 |
| CWNLE | 2¾ | Yes | 14.0 | C-5 | — | — | 1-½ | — | 2 | — | 1-½ | 25 |
| CWNV-25 | 2¾ | Yes | 14.0 | C-5 | — | CV | 1-½ | — | 2 | — | 1-½ | 25 |
| CXWLE | 3½ | Yes | 18.0 | C-5 | — | — | 2-½ | 1-½ | 2 | — | 1-½ | 25 |
| CXWOW | 3½ | Yes | 18.0 | C-5 | Yes | — | 2-½ | 1-½ | 2 | — | 1-½ | 25 |
| CXWOWP | 3½ | Yes | 18.0 | C-5 | Yes | — | 2-½ | 1-½ | 2 | — | 1-½ | 25 |
| CXWV | 3½ | Yes | 18.0 | C-5 | — | CV | 2-1½ | 1-½ | 2 | — | 1-½ | 25 |
| CXWVP | 3½ | Yes | 18.0 | C-5 | — | CV | 2-½ | 1-½ | 2 | — | 1-1½ | 25 |

Switch Boxes and Accessories

3" x 2" Switch Boxes (continued)




CDOW
Ears flush




CDOWTG-25
Ears flush



CDLE-25



CDV-25
CV bracket
recessed 1/8"



804 S
S bracket recessed 3/8"



CW 1/2
Ears flush



CW3/4-25
Ears flush



CWLE1/2-25




CWLE 3/4




CWV 1/2
CV bracket
recessed 1/8"




CY 1/2
Ears flush



CY 3/4
Ears flush



CYLE 1/2



CYLE 3/4

With Conduit KOs

| CAT. NO. | DEPTH (IN.) | GANGABLE | CU. IN. CAPACITY | EARS | BRKTS. | KNOCKOUTS (IN.) | | | STD. CTN. |
|------------|-------------|----------|------------------|------|--------|-----------------|---------------|----------------|-----------|
| | | | | | | EA. END CONDUIT | EA. END CABLE | BOTTOM CONDUIT | |
| CDOW | 2½ | Yes | 12.5 | Yes | — | 1½ | 1½ | 2½ | 50 |
| CDOWTG-25 | 2½ | Yes | 12.5 | Yes | — | 1½ | 1½ | 2½ | 25 |
| CDLE-25 | 2½ | Yes | 12.5 | — | — | 1½ | 1½ | 2½ | 25 |
| CDV-25 | 2½ | Yes | 12.5 | — | CV | 1½ | 1½ | 2½ | 25 |
| 804 S | 2½ | Yes | 12.5 | — | S | 1½ | 1½ | 2½ | 25 |
| CW 1/2 | 2¾ | Yes | 14.0 | Yes | — | 1-½ | 1-½ | 1-½ | 50 |
| CW3/4-25 | 2¾ | Yes | 14.0 | Yes | — | 1-¾ | 1-¾ | 1-¾ | 25 |
| CWLE1/2-25 | 2¾ | Yes | 14.0 | — | — | 1-½ | 1-½ | 1-½ | 25 |
| CWLE 3/4 | 2¾ | Yes | 14.0 | — | — | 1-¾ | 1-¾ | 1-¾ | 25 |
| CWV 1/2 | 2¾ | Yes | 14.0 | — | CV | 1-½ | 1-½ | 1-½ | 25 |
| CY 1/2 | 3½ | Yes | 18.0 | Yes | — | 2-½ | 2-½ | 1-½ | 25 |
| CY 3/4 | 3½ | Yes | 18.0 | Yes | — | 2-¾ | 2-¾ | 1-½ | 25 |
| CYLE 1/2 | 3½ | Yes | 18.0 | — | — | 2-½ | 2-½ | 1-½ | 25 |
| CYLE 3/4 | 3½ | Yes | 18.0 | — | — | 2-¾ | 2-¾ | 1-½ | 25 |

Switch Boxes and Accessories

3" x 2" Switch Boxes (continued)



LXMOV-25
Ears flush
for old work



LXOW-25
Ears flush
for old work




LXOWC-25
Adapts to 3/4"
wall thickness




LXLE




LXV-25
CV bracket
recessed 1/8"



LXVP




806 S
S bracket recessed 3/8"



A-256
With nails slanted
for easy drive-in




CWX-25
Ears flush




CWXV-25
CV bracket
recessed 1/2"



CX
Ears flush



CXLE-SSX
For metal stud



CXP



CXV
CV bracket
recessed 1/8"

With Armored Cable/Metal Clad Clamps


| CAT. NO. | DEPTH (IN.) | GANGABLE | CU. IN. CAPACITY | CLAMPS | EARS | BRKTS. | KNOCKOUTS (IN.) | | | | STD. CTN. |
|----------|-------------|----------|------------------|--------|------|--------|-----------------|---------------|-------|----------------|-----------|
| | | | | | | | EA. END CONDUIT | EA. END CABLE | CABLE | BOTTOM CONDUIT | |
| LXMOV-25 | 2 | Yes | 10.5 | C-3 | Yes | — | — | 2 | — | 1-1/2 | 25 |
| LXOW-25 | 2 1/2 | Yes | 12.5 | C-3 | Yes | — | 1-1/2 | — | 2 | 1-1/2 | 25 |
| LXOWC-25 | 2 1/2 | Yes | 12.5 | C-3 | Yes | — | 1-1/2 | — | 2 | 1-1/2 | 25 |
| LXLE | 2 1/2 | Yes | 12.5 | C-3 | — | — | 1-1/2 | 1-1/2 | 2 | 1-1/2 | 25 |
| LXV-25 | 2 1/2 | Yes | 12.5 | C-3 | — | CV | 1-1/2 | 1-1/2 | 2 | 1-1/2 | 25 |
| LXVP | 2 1/2 | Yes | 12.5 | C-3 | — | CV | 1-1/2 | 1-1/2 | 2 | 1-1/2 | 25 |
| 806 S | 2 1/2 | Yes | 12.5 | C-3 | — | S | 1-1/2 | 1-1/2 | 2 | 1-1/2 | 25 |
| A-256 | 2 1/2 | — | 12.5 | C-3 | — | — | — | 1-1/2 | 2 | 1-1/2 | 25 |
| CWX-25 | 2 3/4 | Yes | 14.0 | C-3 | Yes | — | 1-1/2 | — | 2 | 1-1/2 | 25 |
| CWXV-25 | 2 3/4 | Yes | 14.0 | C-3 | — | CV | 1-1/2 | — | 2 | 1-1/2 | 25 |
| CX | 3 1/2 | Yes | 18.0 | C-3 | Yes | — | 2-1/2 | 1-1/2 | 2 | 1-1/2 | 25 |
| CXLE-SSX | 3 1/2 | Yes | 18.0 | C-3 | No | SSX | 2-1/2 | 1-1/2 | 2 | 1-1/2 | 25 |
| CXP | 3 1/2 | Yes | 18.0 | C-3 | Yes | — | 2-1/2 | 1-1/2 | 2 | 1-1/2 | 25 |
| CXV | 3 1/2 | Yes | 18.0 | C-3 | — | CV | 2-1/2 | 1-1/2 | 2 | 1-1/2 | 25 |

Switch Boxes and Accessories


Gangable Switch Boxes — 2" Deep




51



51-NE



51-LC




51-FB


| CAT. NO. | CU. IN. CAPACITY | DESCRIPTION | STD. CTN. |
|----------|------------------|---|-----------|
| 51 | 10.0 | 2" deep x 3" long x 2" wide Two ½" KOs in each of two sides, one ½" KO in each end and two ½" KOs in bottom. Two nail holes in sides. Furnished with plaster ears* | 50 |
| 51-NE | 10.0 | 2" deep x 3" long x 2" wide Two ½" KOs in each of two sides, one ½" KO in each end and two ½" KOs in bottom. Two nail holes in sides* | 50 |
| 51-LC | 10.0 | For Non-Metallic Cable, 2" deep x 3" long x 2" wide Two ½" KOs in each of two sides, two Loom KOs in each end and one ½" KO in bottom. Furnished with plaster ears. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled. Two nail holes in sides* | 50 |
| 51-FB | 10.0 | 2" deep x 3" long x 2" wide Two ½" KOs in one side, flat bracket on other side, one ½" KO in each end and two ½" KOs in bottom. Bracket offset ⅜" from face* | 50 |

*Uses Steel City® 100 series covers.


Gangable Switch Boxes — 2½" Deep




52




52-3/4-BW




52-NE




52-NE-3/4



52-LCNE



52-FB-3/4




52-FBC

| CAT. NO. | CU. IN. CAPACITY | DESCRIPTION | STD. CTN. |
|-----------|------------------|---|-----------|
| 52 | 12.5 | 2½" deep x 3" long x 2" wide Two ½" KOs in each of two sides, one ½" KO in each end and two ½" KOs in bottom. Furnished with plaster ears. Four nail holes in sides* | 50 |
| 52-3/4-BW | 12.5 | 2½" deep x 3" long x 2" wide Two ½" KOs in each of two sides, one ¾" KO in each end and two ½" KOs in bottom. Furnished with plaster ears. Four nail holes in sides* | 50 |
| 52-NE | 12.5 | 2½" deep x 3" long x 2" wide Two ½" KOs in each of two sides, one ½" KO in each end and two ½" KOs in bottom. Four nail holes in sides* | 50 |
| 52-NE-3/4 | 12.5 | 2½" deep x 3" long x 2" wide Two ½" KOs in each of two sides, one ¾" KO in each end and two ½" KOs in bottom. Four nail holes in sides* | 50 |
| 52-LCNE | 12.5 | For Non-Metallic Cable, 2½" deep x 3" long x 2" wide Two ½" KOs in each side, two Loom KOs and one ½" KO in each end. One ½" KO in bottom. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled. Four nail holes in sides* | 50 |
| 52-FB-3/4 | 12.5 | 2½" deep x 3" long x 2" wide Two ½" KOs in one side, flat bracket on other side, one KO in each end and two ¾" KOs in bottom. Flat bracket offset ⅜" from face* | 50 |
| 52-FBC | 12.5 | For Non-Metallic Cable, 2½" deep x 3" long x 2" wide Two ½" KOs in one side, flat bracket on other side, two Loom KOs and one ½" KO in each end and one ½" KO in bottom. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled. Flat bracket offset ⅜" from face* | 50 |

*Uses Steel City® 100 series covers.

Switch Boxes and Accessories

Gangable Switch Boxes — 2¾" Deep




| CAT. NO. | CU. IN. CAPACITY | DESCRIPTION | STD. CTN. |
|------------|------------------|--|-----------|
| 53 | 14.0 | 2¾" deep x 3" long x 2" wide Two ½" KOs in each side, one ½" KO in each end and two ½" KOs in bottom. Furnished with plaster ears. Four nail holes in sides* | 50 |
| 53-3/4-BW | 14.0 | 2¾" deep x 3" long x 2" wide Two ½" KOs in each side, one ¾" KO in each end and two ½" KOs in bottom. Furnished with plaster ears. Four nail holes in sides* | 50 |
| 53-NE | 14.0 | 2¾" deep x 3" long x 2" wide Two ½" KOs in each side, one ½" KO in each end and two ½" KOs in bottom. Four nail holes in sides* | 50 |
| 53-NE-3/4 | 14.0 | 2¾" deep x 3" long x 2" wide Two ½" KOs in each side, one ¾" KO in each end and two ½" KOs in bottom. Four nail holes in sides* | 50 |
| 53-LCNE | 14.0 | For Non-Metallic Cable, 2¾" deep x 3" long x 2" wide Two ½" KOs in each side, two Loom KOs and one ½" KO in each end and one ½" KO in bottom. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled. Four nail holes in sides* | 50 |
| 53-FB | 14.0 | 2¾" deep x 3" long x 2" wide Two ½" KOs in one side, flat bracket on other side, one ½" KO in each end and two ½" KOs in bottom. Flat bracket offset ⅞" from face* | 50 |
| 53-FBC | 14.0 | For Non-Metallic Cable, 2¾" deep x 3" long x 2" wide Two ½" KOs in one side, flat bracket on other side, two Loom KOs and one ½" KO in each end and one ½" KO in bottom. Flat offset ⅞" from face. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled* | 50 |
| 53-FB-MXN | 14.0 | For Metal Clad Cable, 2¾" deep x 3" long x 2" wide Two ½" KOs in one side, flat bracket on other side, two Loom KOs and one ½" KO in each end, and one ½" KO in bottom. One MXN clamp for MC, AC/BX, and non-metallic sheathed cable (NM) included with 10/32 deep-slotted screw. Clamp is UL Listed for use with cable sizes 14/2 through 10/3 with ground* | 50 |
| 53-OWEC | 14.0 | For Non-Metallic Cable, 2¾" deep x 3" long x 2" wide Two ½" KOs in each side, two Loom KOs and one ½" KO in each end and one ½" KO in bottom. Furnished with plaster ears. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled. With old-work swing brackets* | 50 |
| 53-OWE | 14.0 | 2¾" deep x 3" long x 2" wide Two ½" KOs in each side, one ½" KO in each end and two ½" KOs in bottom. Furnished with plaster ears. With old-work swing brackets* | 50 |
| 53-OWE-MXN | 14.0 | For Metal-Clad Cable, 2¾" deep x 3" long x 2" wide Two ½" KOs in each side. Two Loom KOs and one ½" KO in each end and one ½" KO in bottom. One MXN clamp for MC, AC/BX and non-metallic sheathed cable (NM) included with 10/32 deep-slotted screw. Clamp is UL Listed for use with cable sizes 14/2 through 10/3 with ground. Furnished with plaster ears. With old-work swing brackets* | 50 |


*Uses Steel City® 100 series covers.

Switch Boxes and Accessories


Gangable Switch Boxes — 3½" Deep



54-LC



54-FBC




54-FB-MXN


| CAT. NO. | CU. IN. CAPACITY | DESCRIPTION | STD. CTN. |
|-----------|------------------|---|-----------|
| 54-LC | 18.0 | For Non-Metallic Cable 3½" deep x 3" long x 2" wide Two ½" KO's in each side, two Loom KO's and one ½" KO in each end and one ½" KO in bottom. Two Loom clamps for use on non-metallic sheathed cable with 10/32 deep-slotted screws assembled. Furnished with plaster ears. Four nail holes in sides* | 50 |
| 54-FBC | 18.0 | For Non-Metallic Cable 3½" deep x 3" long x 2" wide Two ½" KO's in one side, flat bracket and two ½" KO's in other side, two Loom KO's and one ½" KO in each end and one ½" KO in bottom. Two Loom clamps for use on non-metallic sheathed cable with 10/32 deep-slotted screws assembled. Flat bracket offset ⅜" from face* | 50 |
| 54-FB-MXN | 18.0 | For Metal Cable, 3½" deep x 3" long x 2" wide Two ½" KO's in one side, flat bracket and two ½" KO's in other side, two Loom KO's and one ½" KO in each end and one ½" KO in bottom. Two MXN clamps for MC, AC/BX, and non-metallic sheathed cable (NM) included with 10/32 deep-slotted screws. Clamps are UL Listed for use with cable sizes 14/2 through 10/3 with ground. Flat bracket offset ⅜" from face* | 50 |

*Uses Steel City® 100 series covers.


Welded Non-Gangable Switch Boxes — 2½" Deep




72




72-C




72-OC



72-OWE



72-ONS-MXN



72-FB-MXN

| CAT. NO. | CU. IN. CAPACITY | DESCRIPTION | STD. CTN. |
|------------|------------------|--|-----------|
| 72 | 12.5 | 2½" deep x 3" long x 2" wide Two Loom KO's and one ½" KO in each end and one ½" KO in bottom. Four nail holes included* | 50 |
| 72-C | 12.5 | For Non-Metallic Cable 2½" deep x 3" long x 2" wide Two Loom KO's and one ½" KO in each end and one ½" KO in bottom. Four nail holes included. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled* | 50 |
| 72-OC | 12.5 | For Non-Metallic Cable 2½" deep x 3" long x 2" wide Two Loom KO's and one ½" KO in each end and one ½" KO in bottom. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled. Four nail holes included. Provisions for external nails included* | 50 |
| 72-OWE | 12.5 | 2½" deep x 3" long x 2" wide Two Loom KO's and one ½" KO in each end and one ½" KO in bottom. With old-work swing brackets* | 50 |
| 72-ONS-MXN | 12.5 | For Metal-Clad Cable 2½" deep x 3" long x 2" wide Two Loom KO's and one ½" KO in each end and one ½" KO in bottom. One MXN clamp for MC, AC/BX and nonmetallic sheathed cable (NM) included with 10/32 deep-slotted screw. Clamp is UL Listed for use with cable sizes 14/2 through 10/3 with ground. Four nail holes included. Two 16-penny nails swaged at an angle in box* | 50 |
| 72-FB-MXN | 12.5 | For Metal-Clad Cable 2½" deep x 3" long x 2" wide Two Loom KO's and one ½" KO in each end, one ½" KO in bottom and flat bracket on one side offset ⅜" from face. Two MXN clamps for MC, AC/BX and non-metallic sheathed cable (NM) included with 10/32 deep-slotted screws. Clamps are UL Listed for use with cable sizes 14/2 through 10/3 with ground. Four nail holes included* | 50 |


*Uses Steel City® 100 series covers.

Switch Boxes and Accessories

Welded Non-Gangable Switch Boxes — 2¹³/₁₆" Deep


| CAT. NO. | CU. IN. CAPACITY | DESCRIPTION | STD. CTN. |
|-----------|------------------|---|-----------|
| 73-ONCS | 15.8 | For Non-metallic Cable, 2¹³/₁₆" deep x 3" long x 2⁹/₁₆" wide Two Loom KOs and one 1/2" KO in each end and one 1/2" KO in bottom. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled. Two 16-penny nails swaged at an angle in box* | 50 |
| 73-FBC | 15.8 | For Non-metallic Cable, 2¹³/₁₆" deep x 3" long x 2⁹/₁₆" wide Two Loom KOs and one 1/2" KO in each end, one 1/2" KO in bottom and flat bracket on one side offset 3/16" from face. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled. Four nail holes included* | 50 |
| 73-FB-MXN | 15.8 | For Metal-Clad Cable, 2¹³/₁₆" deep x 3" long x 2⁹/₁₆" wide Two Loom KOs and one 1/2" KO in each end, one 1/2" KO in bottom and flat bracket on one side offset 3/16" from face. One MXN clamp for MC, AC/BX and non-metallic sheathed cable (NM) included with 10/32 deep-slotted screw. Clamp is UL Listed for use with cable sizes 14/2 through 10/3 with ground. Four nail holes included* | 50 |

*Uses Steel City® 100 series covers.



73-ONCS

73-FBC




73-FB-MXN

Welded Non-Gangable Switch Boxes — 3" Deep


| CAT. NO. | CU. IN. CAPACITY | DESCRIPTION | STD. CTN. |
|----------|------------------|---|-----------|
| 74-CE | 18 | For Non-metallic Cable, 3/4" deep x 3" long x 2 1/4" wide Two Loom KOs and one 1/2" KO in each end and one 1/2" KO in bottom. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled. Furnished with ears. Four nail holes included* | 50 |
| 74-ONCS | 18 | For Non-metallic Cable, 3/4" deep x 3" long x 2 1/4" wide Two Loom KOs and one 1/2" KO in each end and one 1/2" KO in bottom. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled. Two 16-penny nails swaged at an angle in box* | 50 |
| 74-FBC | 18 | For Non-metallic Cable, 3/4" deep x 3" long x 2 1/4" wide Two Loom KOs and one 1/2" KO in each end, one 1/2" KO in bottom and flat bracket on one side offset 3/16" from face. One Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled. Four nail holes included* | 50 |

*Uses Steel City® 100 series covers.



74-CE

74-ONCS




74-FBC

Welded Non-Gangable Switch Box — 3¹³/₃₂" Deep

| CAT. NO. | CU. IN. CAPACITY | DESCRIPTION | STD. CTN. |
|----------|------------------|---|-----------|
| 75-ONCS | 20.0 | For Non-metallic Cable, 3¹³/₃₂" deep x 3" long x 2 1/4" wide Two Loom KOs and one 1/2" KO in each end and one 1/2" KO in bottom. Two Loom clamp for use on non-metallic sheathed cable with 10/32 deep-slotted screw assembled. Four nail holes included. Two 16-penny nails swaged at angle in box*. | 50 |

*Uses Steel City® 100 series covers.




75-ONCS

Switch Boxes and Accessories


Welded Multi-Gangable Switch Boxes — 2½" Deep

| CAT. NO. | CAPACITY | DESCRIPTION | STD. CTN. |
|------------|----------|--|-----------|
| 271-FBC | 25.0 | A Two-Gang Box — For Non-Metallic Cable, 2½" deep x 3" long x 4" wide Two Loom KOs and two ½" KOs in each end, flat bracket on one side and one ½" KO in bottom. Two Loom clamps for use on non-metallic sheathed cable with 10/32 deep-slotted screws assembled. Flat bracket offset ⅜" from face* | 25 |
| 271-FB-MXN | 25.0 | A Two-Gang Box — For Metal-Clad Cable, 2½" deep x 3" long x 4" wide Two Loom KOs and two ½" KOs in each end, flat bracket on one side and one ½" KO in bottom. Two MXN clamps for MC, AC/BX and non-metallic sheathed cable (NM) included with 10/32 deep-slotted screws. Clamps are UL Listed for use with cable sizes 14/2 through 10/3 with ground. Flat bracket offset ⅜" from face* | 25 |

*Uses Steel City® SB-2 covers.



271-FBC



271-FB-MXN

Boxes & Covers — Steel City® Metallic Boxes

4" x 2½" Thru-Wall Box

| CAT. NO. | CU. IN. CAPACITY | DESCRIPTION | BOX DEPTH (IN.) | STD. CTN. |
|---|------------------|--|-----------------|-----------|
| With Conduit KOs for Plaster or Dry Wall | | | | |
| CTDW | 32.0 | Drywall, partition type; one ½" and one ¾" KO both ends; one ½" KO on one side, V bracket other side | 4⅞ | 25 |



CTDW

Switch Box Extension

| CAT. NO. | DESCRIPTION | STD. CTN. |
|----------|--|-----------|
| SBEX | Cubic content 3.5 inches; fits snugly inside of all single-gang switch boxes; maximum adjustable depth ⅞"; furnished with 1¼"-long screws for mounting | 50 |

UL Listing not applicable — subject to approval by local inspector.



SBEX

Switch Boxes and Accessories

Old-Work Box Support

- Quickly attaches box through finished drywall
- For up to 1½" thick drywall
- New 820D shipped in one-piece break-apart design
- Easy to install

| CAT. NO. | FIG. NO. | DESCRIPTION | STD. CTN. |
|----------|----------|---|-----------|
| 820D | 1 | Old-work switch box steel-mounting holder | 500 sets |





Fig. 1

Steel Low-Voltage Bracket

- Fixes to the switch box easily with the screws provided
- Works with any Steel City® switch box, regardless of depth
- Single-screw fixing as well as two-screw fixing
- Low-voltage cable support is provided by fitting location tabs
- UL Listed for low-voltage support



| CAT. NO. | DESCRIPTION | BOX DEPTH (IN.) | STD. CTN. |
|----------|--|-----------------|-----------|
| LVB | Bracketed to T&B boxes; provides means of installing a low-voltage device alongside a regular switch or outlet | 1 7/8 | 25 |




LVB

Old-Work Box Support Clips

- Adapts to any wall thickness up to ¾"

| CAT. NO. | DESCRIPTION | STD. CTN. |
|--------------|---|--------------|
| OWC | Clips lock old-work steel switch boxes tightly to wall plaster, drywall, concrete block, brick or concrete. 2 required per box, (1 set) | 250 sets |
| OW SWING EAR | Swing ears only (for field installations) with self-threading screws | 50 (25 pair) |



OW Swing Ear