

### Bus drop

#### Product description

Closed mesh  
Single eye & locking bale grips

#### Features & applications

- Bus drop grips are woven of galvanized steel wire
- Relieve any direct tension from the critical connection and absorb vibration and flexing
- Offered with either the single eye or locking bale attachment
- Bus drop grips are used as cable support from bus duct
- Optional bus drop safety spring can be used with single eye type of disassembling draw bar from coil, placing through eye loop and replacing draw bar
- Single eye for use when cable is vertical and for applications where cable bends
- Locking bale attachment fits around beam or pipe and can be locked in place




BDS53




BDU53

#### Single eye grips

| Cord diameter            | Bale length  | Mesh length     | Approx. break strength† | Catalog no.*                   |  |
|--------------------------|--------------|-----------------|-------------------------|--------------------------------|---|
| 0.22-0.32" (5.6-8.1mm)   | 9" (228.6mm) | 3.5" (88.9mm)   | 1,100 lbs.              | <input type="checkbox"/> BDS22 | •   |
| 0.30-0.43" (7.6-10.9mm)  | 9" (228.6mm) | 4.5" (114.3mm)  | 1,100 lbs.              | <input type="checkbox"/> BDS30 | •   |
| 0.41-0.56" (10.4-14.2mm) | 9" (228.6mm) | 5.0" (127.0mm)  | 1,100 lbs.              | <input type="checkbox"/> BDS41 | •   |
| 0.53-0.73" (13.5-18.5mm) | 9" (228.6mm) | 6.5" (165.1mm)  | 1,100 lbs.              | <input type="checkbox"/> BDS53 | •   |
| 0.70-0.85" (17.8-21.6mm) | 9" (228.6mm) | 8.5" (215.9mm)  | 1,900 lbs.              | <input type="checkbox"/> BDS70 | •   |
| 0.82-1.00" (20.8-25.4mm) | 9" (228.6mm) | 8.5" (215.9mm)  | 1,900 lbs.              | <input type="checkbox"/> BDS82 | •   |
| 0.96-1.25" (24.4-31.8mm) | 9" (228.6mm) | 11.0" (279.4mm) | 1,900 lbs.              | <input type="checkbox"/> BDS96 | •   |

#### Locking bale grips


| Cord diameter            | Bale length   | Mesh length     | Approx. break strength† | Catalog no.*                   |  |
|--------------------------|---------------|-----------------|-------------------------|--------------------------------|---|
| 0.22-0.32" (5.6-8.1mm)   | 12" (304.8mm) | 3.5" (88.9mm)   | 1,100 lbs.              | <input type="checkbox"/> BDU22 | •   |
| 0.30-0.43" (7.6-10.9mm)  | 12" (304.8mm) | 4.5" (114.3mm)  | 1,100 lbs.              | <input type="checkbox"/> BDU30 | •   |
| 0.41-0.56" (10.4-14.2mm) | 12" (304.8mm) | 5.0" (127.0mm)  | 1,100 lbs.              | <input type="checkbox"/> BDU41 | •   |
| 0.53-0.73" (13.5-18.5mm) | 15" (381.0mm) | 6.5" (165.1mm)  | 1,100 lbs.              | <input type="checkbox"/> BDU53 | •   |
| 0.70-0.85" (17.8-21.6mm) | 16" (406.4mm) | 8.5" (215.9mm)  | 1,900 lbs.              | <input type="checkbox"/> BDU70 | •   |
| 0.82-1.00" (20.8-25.4mm) | 16" (406.4mm) | 8.5" (215.9mm)  | 1,900 lbs.              | <input type="checkbox"/> BDU82 | •   |
| 0.96-1.25" (24.4-31.8mm) | 17" (431.8mm) | 11.0" (279.4mm) | 1,900 lbs.              | <input type="checkbox"/> BDU96 | •   |

#### Accessories for support grips: service drop & bus drop, closed mesh grips

| Description                 | <input type="checkbox"/>       |  |
|-----------------------------|--------------------------------|---|
| Safety spring, 40 lbs. load | <input type="checkbox"/> B2001 | •   |
| Safety spring, 80 lbs. load | <input type="checkbox"/> B2002 | •   |



B2001



B2002

\*Contact the factory for stainless steel support grips.

† To determine workload safety factor, divide approximate break strength by 10. See page N-34 for strength information. Consult factory for price and availability.

**Compliances, specifications and availability are subject to change without notice.**

 Indicates NAFTA compliant - Page Q-30

### Bus drop

#### Product description

Closed mesh  
Single eye & locking bale grips

#### Features & applications

- Bus drop grips are woven of galvanized steel wire
- Relieve any direct tension from the critical connection and absorb vibration and flexing
- Offered with either the single eye or locking bale attachment
- Bus drop grips are used as cable support from bus duct
- Optional bus drop safety spring can be used with single eye type of disassembling draw bar from coil, placing through eye loop and replacing draw bar
- Single eye for use when cable is vertical and for applications where cable bends
- Locking bale attachment fits around beam or pipe and can be locked in place




BDS53




BDU53

#### Single eye grips

| Cord diameter            | Bale length  | Mesh length     | Approx. break strength <sup>†</sup> | Catalog no.*                   |  |
|--------------------------|--------------|-----------------|-------------------------------------|--------------------------------|---|
| 0.22-0.32" (5.6-8.1mm)   | 9" (228.6mm) | 3.5" (88.9mm)   | 1,100 lbs.                          | <input type="checkbox"/> BDS22 | •   |
| 0.30-0.43" (7.6-10.9mm)  | 9" (228.6mm) | 4.5" (114.3mm)  | 1,100 lbs.                          | <input type="checkbox"/> BDS30 | •   |
| 0.41-0.56" (10.4-14.2mm) | 9" (228.6mm) | 5.0" (127.0mm)  | 1,100 lbs.                          | <input type="checkbox"/> BDS41 | •   |
| 0.53-0.73" (13.5-18.5mm) | 9" (228.6mm) | 6.5" (165.1mm)  | 1,100 lbs.                          | <input type="checkbox"/> BDS53 | •   |
| 0.70-0.85" (17.8-21.6mm) | 9" (228.6mm) | 8.5" (215.9mm)  | 1,900 lbs.                          | <input type="checkbox"/> BDS70 | •   |
| 0.82-1.00" (20.8-25.4mm) | 9" (228.6mm) | 8.5" (215.9mm)  | 1,900 lbs.                          | <input type="checkbox"/> BDS82 | •   |
| 0.96-1.25" (24.4-31.8mm) | 9" (228.6mm) | 11.0" (279.4mm) | 1,900 lbs.                          | <input type="checkbox"/> BDS96 | •   |

#### Locking bale grips

| Cord diameter            | Bale length   | Mesh length     | Approx. break strength <sup>†</sup> | Catalog no.*                   |  |
|--------------------------|---------------|-----------------|-------------------------------------|--------------------------------|---|
| 0.22-0.32" (5.6-8.1mm)   | 12" (304.8mm) | 3.5" (88.9mm)   | 1,100 lbs.                          | <input type="checkbox"/> BDU22 | •   |
| 0.30-0.43" (7.6-10.9mm)  | 12" (304.8mm) | 4.5" (114.3mm)  | 1,100 lbs.                          | <input type="checkbox"/> BDU30 | •   |
| 0.41-0.56" (10.4-14.2mm) | 12" (304.8mm) | 5.0" (127.0mm)  | 1,100 lbs.                          | <input type="checkbox"/> BDU41 | •   |
| 0.53-0.73" (13.5-18.5mm) | 15" (381.0mm) | 6.5" (165.1mm)  | 1,100 lbs.                          | <input type="checkbox"/> BDU53 | •   |
| 0.70-0.85" (17.8-21.6mm) | 16" (406.4mm) | 8.5" (215.9mm)  | 1,900 lbs.                          | <input type="checkbox"/> BDU70 | •   |
| 0.82-1.00" (20.8-25.4mm) | 16" (406.4mm) | 8.5" (215.9mm)  | 1,900 lbs.                          | <input type="checkbox"/> BDU82 | •   |
| 0.96-1.25" (24.4-31.8mm) | 17" (431.8mm) | 11.0" (279.4mm) | 1,900 lbs.                          | <input type="checkbox"/> BDU96 | •   |

#### Accessories for support grips: service drop & bus drop, closed mesh grips

| Description                 | <input type="checkbox"/>       |  |
|-----------------------------|--------------------------------|---|
| Safety spring, 40 lbs. load | <input type="checkbox"/> B2001 | •   |
| Safety spring, 80 lbs. load | <input type="checkbox"/> B2002 | •   |



B2001



B2002

\*Contact the factory for stainless steel support grips.

† To determine workload safety factor, divide approximate break strength by 10. See page N-34 for strength information.

Consult factory for price and availability.

**Compliances, specifications and availability are subject to change without notice.**

 Indicates NAFTA compliant - Page Q-30