



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ADR25 250 Al/Cu 1 Conduct Lug

*Abb Installation Products, Inc*

|                  |  |
|------------------|--|
| Catalog Number   | ADR25  |
| Manufacturer     | Abb Installation Products, Inc   |
| Description      | Mechanical Connector Lug, #6 Awg (Stranded) Conductor Size, 250 Kcmil Conductor Size, Non-Insulated, Aluminum/Copper Conductor Material, 1 Conductor, 2 In Overall Length, Screw Terminal, 0.1 LB/Ea |
| Weight per unit  | 0.1050 (lbs/each)  |
| Product Category | Large Terminals & Connectors   |

### Features

|                          |          |
|--------------------------|----------|
| insulation               | None     |
| Material                 | Aluminum |
| Number of Conductors     | 1        |
| Number of Mounting Holes | 1        |

### Material, Color, and Finish

|        |        |
|--------|--------|
| Finish | Tinned |
|--------|--------|

### Descriptions

|                        |                                     |
|------------------------|-------------------------------------|
| Description            | 250 AL/CU 1 CONDUCT LUG             |
| extra long description | ABB ADR25 AL 1CNDTR 1HOLE MOUNT 250 |

### Manufacturer Information

|       |                      |
|-------|----------------------|
| Brand | Blackburn Mechanical |
| GTIN  | 00783786610105       |
| UPC   | 783786610105         |

### Taxonomies, Classifications, and Categories

|                      |                                   |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type                 | Dual-Rated Mechanical Connector   |

### Packaging

|                 |       |
|-----------------|-------|
| Carton          | 25    |
| Weight Per each | 0.105 |

### Uses, Certifications, and Standards

|          |                     |
|----------|---------------------|
| standard | UL E9809 / UL E9809 |
|----------|---------------------|