

Specifications



Photo is representative

Eaton BR816N200RF

Eaton BR convertible loadcenter, Feed-through lug, Convertible main, 200 A, C3r, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, BWH, 16 Circuits, 8 Spaces, Three-wire, Single-phase, 120/240 V, Determined by circuit breaker installed

General specifications

PRODUCT NAME	Eaton BR convertible loadcenter
CATALOG NUMBER	BR816N200RF
UPC	786676448451
PRODUCT LENGTH/DEPTH	5.19 in
PRODUCT HEIGHT	25 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	40 lb
WARRANTY	10 year
CERTIFICATIONS	UL 50 UL 67
CATALOG NOTES	The maximum rating of the panel is the main breaker rating when used as service entrance equipment.



Product specifications

SPECIAL FEATURES

Feed-through lug

Resources

TYPE	Convertible main
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BWH
NUMBER OF CIRCUITS	16
NUMBER OF SPACES	8
PHASE	Single-phase
VOLTAGE RATING	120/240 V
WIRE SIZE	Determined by circuit breaker installed
BOX SIZE	C3R
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BR816N200RF
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

